





LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			M7	REVISED PER ECR-13-011067	16JUL13	KH	PD

- 1 ALL DIMENSIONS APPLY TO A MOISTURIZED HOUSING.
- 2 PRELIMINARY – NOT FOR PRODUCTION
- 3 OFFERED FOR CONSIDERATION IN "NON-DRIP" HOUSING MATERIAL APPLICATIONS.
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING I PER D.RENAUD/D.SINIS
- 5 PREPRODUCTION-FASR REQUIRED

SUGGESTED MATING TAB



- 1 – MATL: ½ H BRASS OR NICKEL PL STEEL.
- 2 – NO BURRS PERMISSIBLE AT HOLE.
- 3 – MUST BE FLAT WITHIN 0.076 [.003] OVER THIS LENGTH.
- 4 – TIN PLATING IS REQUIRED ON BRASS WHEN TERMINAL TEMP. IS OVER 225° F
- 5 – HOLE MUST BE SYMMETRICAL ABOUT TAB Q WITHIN 0.076 [.003]
- * TO BE USED ONLY WHEN SHOULDER IS ELIMINATED.



3D VIEW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96		 TE Connectivity			
		CHK MS FEHER 7/3/96					
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J GILLISPIE 7/3/96		NAME	
		0 PLC ± -		PRODUCT SPEC		HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES -	
		1 PLC ± -		-			
		2 PLC ± 0.25 [.010]		APPLICATION SPEC			
		3 PLC ± -		-			
		4 PLC ± -				SIZE	
		ANGLES ± -				CAGE CODE	
MATERIAL		FINISH		WEIGHT -		DRAWING NO	
SEE TABLE		SEE TABLE				RESTRICTED TO	
				A2		00779	
				CUSTOMER DRAWING		C=521120	
						SCALE 5:1	
						SHEET 1 of 2	
						REV M7	


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	- , -
© COPYRIGHT - By -	ALL RIGHTS RESERVED.	

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			-	SEE SHEET 1	-	-	-

BROWN	66/6 NYLON, V0		2-521120-5
YELLOW	66/6 NYLON, V0		2-521120-4
GREEN	66/6 NYLON, V0		2-521120-3
RED	66/6 NYLON, V0		2-521120-2
BLUE	66/6 NYLON, V0		2-521120-1
BROWN	6/6 NYLON, V2		2-521120-0
YELLOW	6/6 NYLON, V2		1-521120-9
GREEN	6/6 NYLON, V2		1-521120-8
NATURAL	6/6 NYLON, V2		1-521120-7
BLACK	66/6 NYLON, V0		1-521120-6
NATURAL	 66/6 OR 66 NYLON, V0		1-521120-5
NATURAL	6/6 NYLON, V0		1-521120-4
NATURAL	66/6 OR 66 NYLON, V0		1-521120-3
YELLOW	6/6 NYLON		1-521120-2
BLUE	6/6 NYLON		1-521120-1
GREEN	6/6 NYLON		1-521120-0
RED	6/6 NYLON		-521120-9-
BLACK	6/6 NYLON		521120-8
NATURAL	6/6 NYLON		521120-7
BLACK	4/6 NYLON		521120-6
RED	6/6 NYLON		521120-5
BLUE	6/6 NYLON		521120-4
PUTTY	6/6 NYLON		-521120-2-
NATURAL	6/6 NYLON		521120-1
COLOR	MATERIAL		PART NO

4
OBSOLETE

4 OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 7/3/96		 TE Connectivity									
		CHK MS FEHER 7/3/96											
DIMENSIONS: mm [INCHES]		TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD J GILLISPIE 7/3/96		NAME							
		0 PLC ± -		HOUSING, RECEPTACLE, POSITIVE-LOCK, MKIII, 6.35 [.250] SERIES -									
		1 PLC ± -											
		2 PLC ± 0.25 [.010]											
		3 PLC ± -											
		4 PLC ± -											
ANGLES ± ±		PRODUCT SPEC		SIZECAGE CODEDRAWING NORESTRICTED TO									
		APPLICATION SPEC											
MATERIAL		FINISH		WEIGHT -		A200779C=521120-							
SEE TABLE		SEE TABLE		CUSTOMER DRAWING				SCALE 5:1		SHEET 2 of 2		REV M7	