



INCANDESCENT BULB				
PARAMETERS	SYMBOL	MAX.	UNITS	
LAMP VOLTAGE (AC/DC)	V	12	V	
POWER DISSIPATION	P _d	2	Watts	
CURRENT	I	100	mA	



PANEL THICKNESS	X dimension
0.75-1.25 [0.030-0.049]	19.2-01 [0.7561]
1.25-2.0 [0.049-0.079]	19.4-01 [0.764]
2.0-3.0 [0.079-0.118]	19.8-01 [0.7801]



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. RATING:
6A @250VAC;9A @125VAC (UL, CSA, VDE)
4(1)A @250VAC
4. LAMP VOLTAGE: 12VDC (INCANDESCENT BULB)
5. MATERIAL:
CONTACT SURFACE: Coin Silver, Silver Plate
TERMINAL: Copper Alloy W/ Silver Plate.
6. CONTACT RESISTANCE: 20MILLIOHMS TYP. INITIAL
7. INSULATION RESISTANCE: 1000Megaohms
8. DIELECTRIC STRENGTH:
>1500V RMS min. @SEA LEVEL
>3000V RMS @SEA LEVEL
9. MECHANICAL LIFE: 50,000 CYCLES.
10. ELECTRICAL LIFE: 10,000 CYCLES.

E-SWITCH®

TITLE			
A	12568	RELEASED FOR PRODUCTION	11/15/02
REV.	ECN No.	DESCRIPTION	DATE
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED			
SCALE			
1.5:1			
DATE			
11/15/02			
DR			
CJB			
DWG			
M400066			
REV			
A			