

121110987654321

1.00mm CENTER FLAT FLEX CABLE (FFC) (105°C, Sn PLATED)

"L" DIM. →	30 ± 2 MM		51 ± 2 MM		76 ± 3 MM		102 ± 3 MM		127 ± 4 MM		152 ± 4 MM		178 ± 4 MM		203 ± 4 MM		229 ± 5 MM		254 ± 5 MM		305 ± 5 MM	
REF DIM →	(1.18 INCH)		(2 INCHES)		(3 INCHES)		(4 INCHES)		(5 INCHES)		(6 INCHES)		(7 INCHES)		(8 INCHES)		(9 INCHES)		(10 INCHES)		(12 INCHES)	
CABLE TYPE →	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D	A	D
CIRCUITS "N" ↓																						
4	152670701	152670700	152670703	152670702	152670705	152670704	152670707	152670706	152670709	152670708	152670711	152670710	152670713	152670712	152670715	152670714	152670717	152670716	152670719	152670718	152670721	152670720
6	152670201	152670202	152670203	152670204	152670205	152670206	152670207	152670208	152670209	152670210	152670211	152670212	152670213	152670214	152670215	152670216	152670217	152670218	152670219	152670220	152670221	152670222
8	152670223	152670224	152670225	152670226	152670227	152670228	152670229	152670230	152670231	152670232	152670233	152670234	152670235	152670236	152670237	152670238	152670239	152670240	152670241	152670242	152670243	152670244
10	152670245	152670246	152670247	152670248	152670249	152670250	152670251	152670252	152670253	152670254	152670255	152670256	152670257	152670258	152670259	152670260	152670261	152670262	152670263	152670264	152670265	152670266
12	152670267	152670268	152670269	152670270	152670271	152670272	152670273	152670274	152670275	152670276	152670277	152670278	152670279	152670280	152670281	152670282	152670283	152670284	152670285	152670286	152670287	152670288
14	152670289	152670290	152670291	152670292	152670293	152670294	152670295	152670296	152670297	152670298	152670299	152670300	152670301	152670302	152670303	152670304	152670305	152670306	152670307	152670308	152670309	152670310
16	152670311	152670312	152670313	152670314	152670315	152670316	152670317	152670318	152670319	152670320	152670321	152670322	152670323	152670324	152670325	152670326	152670327	152670328	152670329	152670330	152670331	152670332
18	152670333	152670334	152670335	152670336	152670337	152670338	152670339	152670340	152670341	152670342	152670343	152670344	152670345	152670346	152670347	152670348	152670349	152670350	152670351	152670352	152670353	152670354
20	152670355	152670356	152670357	152670358	152670359	152670360	152670361	152670362	152670363	152670364	152670365	152670366	152670367	152670368	152670369	152670370	152670371	152670372	152670373	152670374	152670375	152670376
22	152670377	152670378	152670379	152670380	152670381	152670382	152670383	152670384	152670385	152670386	152670387	152670388	152670389	152670390	152670391	152670392	152670393	152670394	152670395	152670396	152670397	152670398
24	152670399	152670400	152670401	152670402	152670403	152670404	152670405	152670406	152670407	152670408	152670409	152670410	152670411	152670412	152670413	152670414	152670415	152670416	152670417	1526		

12

11

10

9

8

7

6

5

4

3

2

1

1.00mm CENTER FLAT FLEX CABLE (FFC) (105°C, Sn PLATED)

"L" DIM. →

REF DIM →

CABLE TYPE →

CIRCUITS "N" ↓

30 ± 2 MM

(1.18 INCH)

51 ± 2 MM

(2 INCHES)

76 ± 3 MM

(3 INCHES)

102 ± 3 MM

(4 INCHES)

127 ± 4 MM

(5 INCHES)

152 ± 4 MM

(6 INCHES)

178 ± 4 MM

(7 INCHES)

203 ± 4 MM

(8 INCHES)

229 ± 5 MM

(9 INCHES)

254 ± 5 MM

(10 INCHES)

305 ± 5 MM

(12 INCHES)

3

5

7

9

11

13

15

17

19

21

23

25

27

29

31

33

35

37

39

152670679

152670678

152670681

152670680

152670683

152670682

152670685

152670684

152670687

152670686

152670689

152670688

152670691

152670690

152670693

152670692

152670695

152670694

152670697

152670696

152670699

152670698

152670723

152670722

152670725

152670724

152670727

152670726

152670729

152670728

152670731

152670730

152670733

152670732

152670735

152670734

152670737

152670736

152670739

152670738

152670741

152670740

152670743

152670742

152670745

152670744

152670747

152670746

152670749

152670748

152670751

152670750

152670753

152670752

152670755

152670754

152670757

152670756

152670759

152670758

152670761

152670760

152670763

152670762

152670765

152670764

152670767

152670766

152670769

152670768

152670771

152670770

152670773

152670772

152670775

152670774

152670777

152670776

152670779

152670778

152670781

152670780

152670783

152670782

152670785

152670784

152670787

152670786

152670789

152670788

152670791

152670790

152670793

152670792

152670795

152670794

152670797

152670796

152670799

152670798

152670801

152670800

152670803

152670802

152670805

152670804

152670807

152670806

152670809

152670808

152670811

152670810

152670813

152670812

152670815

152670814

152670817

152670816

152670819

152670818

152670821

152670820

152670823

152670822

152670825

152670824

152670827

152670826

152670829

152670828

152670831

152670830

152670833

152670832

152670835

152670834

152670837

152670836

152670839

152670838

152670841

152670840

152670843

152670842

152670845

152670844

152670847

152670846

152670849

152670848

152670851

152670850

152670853

152670852

152670855

152670854

152670857

152670856

152670859

152670858

152670861

152670860

152670863

152670862

152670865

152670864

152670867

152670866

152670869

152670868

152670871

152670870

152670873

152670872

152670875

152670874

152670877

152670876

152670879

152670878

152670881

152670880

152670883

152670882

152670885

152670884

152670887

152670886

152670889

152670888

152670891

152670890

152670893

152670892

152670895

152670894

152670897

152670896

152670899

152670898

152670901

152670900

152670903

152670902

152670905

152670904

152670907

152670906

152670909

152670908

152670911

152670910

152670913

152670912

152670915

152670914

152670917

152670916

152670919

152670918

152670921

152670920

152670923

152670922

152670925

152670924

152670927

152670926

152670929

152670928

152670931

152670930

152670933

152670932

152670935

152670934

152670937

152670936

152670939

152670938

152670941

152670940

152670943

152670942

152670945

152670944

152670947

152670946

152670949

152670948

152670951

152670950

152670953

152670952

152670955

152670954

152670957

152670956

152670959

152670958

152670961

152670960

152670963

152670962

152670965

152670964

152670967

152670966

152670969

152670968

152670971

152670970

152670973

152670972

152670975

152670974

152670977

152670976

152670979

152670978

152670981

152670980

152670983

152670982

152670985

152670984

152670987

152670986

152670989

152670988

152670991

152670990

152670993

152670992

152670995

152670994

152670997

152670996

152670999

152670998

152671001

152671000

152671003

152671002

152671005

152671004

152671007

152671006

152671009

152671008

152671011

152671010

152671013

152671012

152671015

152671014

152671017

152671016

152671019

152671018

152671021

152671020

152671023

152671022

152671025

152671024

152671027

152671026

152671029

152671028

152671031

152671030

152671033

152671032

152671035

152671034

152671037

152671036

152671039

152671038

152671041

152671040

152671043

152671042

152671045

152671044

152671047

152671046

152671049

152671048

152671051

152671050

152671053

152671052

152671055

152671054

152671057

152671056

152671059

152671058

152671061

152671060

152671063

152671062

152671065

152671064

152671067

152671066

152671069

152671068

152671071

152671070

152671073

152671072

152671075

152671074

152671077

152671076

152671079

152671078

152671081

152671080

152671083

152671082

152671085

152671084

152671087

152671086

152671089

152671088

152671091

152671090

152671093

152671092

152671095

152671094

152671097

152671096

152671099

152671098

152671101

152671100

152671103

152671102

152671105

152671104

152671107

152671106

152671109

152671108

152671111

152671110

152671113

152671112

152671115

152671114

152671117

152671116

0.086 mm POLYESTER + ADHESIVE

0.10 mm COPPER

0.086 mm POLYESTER + ADHESIVE

0.155 mm POLYESTER

CROSS-SECTION

4.00±0.80

1.00±0.20

1.00±0.08

0.70±0.03

1.00 (N-1) ± 0.15

1.00 (N+1) ± 0.10

END TAIL DETAIL
SCALE 5:1

NOTES:

1. NO PRINTING ON JUMPER CABLE UNLESS OTHERWISE SPECIFIED. IF PRINTING IS REQUIRED, THEN IT WOULD BE CONSIDERED A SPECIAL JUMPER CABLE.

PENDING APPROVAL

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
	DIMENSION UNITS		SCALE		CURRENT REV DESC: PN CORRECTION 152670298						
	MM		2:1								
	GENERAL TOLERANCES (UNLESS SPECIFIED)										
		mm	INCH								
	4 PLACES	±----	±----								
	3 PLACES	±----	±----								
	2 PLACES	±----	±----								
	1 PLACE	±----	±----								
	0 PLACES	±----	±----								
ANGULAR TOL ± 0.5 °				STATUS:Production DRWN: DIEGO GOMEZ 2025-05-19 CHK'D: DIEGO GOMEZ 2025-05-19 APPR: DAVID FALLA 2025-05-20							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											
THIRD ANGLE PROJECTION		DRAWING C-SIZE								SERIES 15267	
DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION					
SD-15267-001				PSD		001		E			
MATERIAL NUMBER				CUSTOMER				SHEET NUMBER			
				GENERAL MARKET				2 OF 2			