


Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51763-ABB00000EF..
Note: ①
SEE NOTE 1



mat'l code				SEE NOTE 2		tolerances unless otherwise specified		CUSTOMER		FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear		.XX±.01/.XX±.3		COPY		projection	title
A	V02389	JRW	10/5/00			.XXX±.005/.XX±.13					RIGHT ANGLE RECEPTACLE w/GUIDE PIN POWER
B	V21511	CGD	09/23/02			.XXX±.0020/.XX±.051					
C	V03-0769	TAB	07/16/03	angles		0°±2°					
D	DG05-0132	SJ	06/02/05	dr	LEV4	10/14/99		INCH/MM		product family	code
E	DG05-0175	SJ	06/20/05	engr	J. BROWN	10/14/99		scale	3:2	PWRBLADE	213
				chr	J. BROWN	10/14/99				size	dwg no
				appd	J. BROWN	10/14/99				51763	sheet
											1 of 3
sheet index	revision	E	E	E							
	sheet	1	2	3							

Pro/E

cage code **22526**

PDM: Rev:E

STATUS: Released

Printed: Dec 20, 2010

Tous droits strictement réservés. Reproduction ou communication à des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51763-ABB00000EF..
Note: ①
SEE NOTE 1

1 | 2

DIM	LENGTH FORMULAS (SEE NOTE 9)
DIM "A"	.250 [6.35] x BB + .650 [16.51] (NOTE 9)
DIM "B"	.250 [6.35] x BB + .350 [8.89]
DIM "C"	.250 [6.35] x BB + .300 [7.62]
DIM "F"	.250 [6.35] x BB + .680 [17.27]

3 |

4

CONNECTOR NOTES:

- ①. PRODUCT NUMBER CODE:
51763 - A BB 000 00 E F LF

NO THIS SUFFIX: 100u"/2.54um SnPb ON PCB INTERFACE
ADD THIS SUFFIX: 78u"/2.00um Sn OR 5u" Au ON PCB INTERFACE
RETENTION TO PCB (NOTE 7)
TAIL OPTIONS (NOTE 6)
ALWAYS '00' (ZERO, ZERO)
ALWAYS '000' (ZERO, ZERO, ZERO) (NOTE 5)
NUMBER OF POWER CONTACTS (NOTE 4)
PLATING (NOTE 3)
BASE NUMBER

- ②. HOUSING MATERIAL: GLASS FILLED V-0 HIGH TEMP THERMO PLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY

- ③. PLATING OPTION:
1 = SIGNAL CONTACTS: 50u" / 1.27um Ni UNDER ALL; 30u" / 0.76um Au ON THE CONTACT AREA AND WITH 100u"/2.54um SnPb OR 78u"/2.00um Sn ON PCB INTERFACE
POWER CONTACTS: 50u" / 1.27um Ni UNDER ALL; WITH 30u" / 76um Au ON CONTACT AREA WITH 100u"/2.54um SnPb OR 78u"/2.00um Sn ON PCB INTERFACE

3 = SIGNAL CONTACTS: 50u" / 1.27um Ni UNDER ALL; 30u" / 0.76um Au ON THE CONTACT AREA AND WITH 5u"/0.13um Au ON PCB INTERFACE
POWER CONTACTS: 50u" / 1.27um Ni UNDER ALL; WITH 30u" / 76um Au ON CONTACT AREA WITH 5u"/0.13um Au ON PCB INTERFACE

- ④. POWER CONTACTS, 01 TO 20 AVAILABLE.
MAXIMUM OF 20 POWER CONTACTS PER CONNECTOR
- ⑤. THIS PART IS NOT AVAILABLE WITH SIGNAL CONTACTS.
- ⑥. TAIL OPTIONS:
A = .135±0.010 [3.43±0.25] SOLDER TO BOARD
B = .090 +.005/- .010 [2.29 +0.13/-0.25] SOLDER TO BOARD
C = .154 ±0.010 [3.91 ±0.25] PRESS-FIT TO BOARD

- ⑦. RETENTION TO PCB OPTIONS:
A = BOARD LOCK (REQUIRES .098±.002/- .001 [2.49±0.05/-0.03] THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: .220[5.59]
NOT AVAILABLE FOR PRESS-FIT
B = .150 [3.81] THRU HOLE (REQUIRES .158 ± .003 [4.01±0.08] THRU HOLE IN PCB).
MOUNTING FOOT THICKNESS: .160[4.06]
ALWAYS AVAILABLE FOR PRESS-FIT
- ⑧. MANUFACTURE'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
- ⑨. THE MAXIMUM OVERALL LENGTH (DIM A) OF A PART IS 8.00 [203.2].

10. PRODUCT SPECIFICATION GS-12-149.

11. APPLICATION SPECIFICATION BUS -20-067.
12. FOR PRESS-FIT CONNECTORS USE FCI CAM TOOL 430140-XXX TO APPLY CONNECTOR TO PCB.

PCB NOTES:

13. ALL DIMENSIONS ARE BASIC UNLESS OTHERWISE SPECIFIED.
14. ALL THROUGH HOLES ARE LOCATED WITH A TRUE POSITION OF 0.004 [0.10].
15. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
16. Ø0.0453±0.001 [1.151±0.02] DRILLED HOLES PLATED WITH 0.0003 [0.007] MIN SnPb OVER 0.001 [0.03] TO 0.003 [0.08] PLATING TO ACHIEVE A 0.040±0.003 [1.02±0.08] HOLE.

mat'l code				tolerances unless otherwise specified				CUSTOMER		FCI www.fciconnect.com	
ltr	ecn no.	dr	date	linear	.XX±.01/.X±.3			COPY		title	
E				linear	.XXX±.005/.XX±.13			projection		RIGHT ANGLE RECEPTACLE w/GUIDE PIN POWER	
				angles	.XXX±.0020/.XXX±.051					product family	
				dr	0°±2°					PWRBLADE	
				enr	LEV4 10/14/99			scale		code	
				chr	J. BROWN 10/14/99			3:2		213	
				appd	J. BROWN 10/14/99			A		sheet	
sheet index				revision				cage code			
sheet				sheet				22526			

Pro/E

3 |

4


PDM: Rev:E

STATUS: Released


Printed: Dec 20, 2010

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

AFCI



SECTION B-B

mat'l code				- tolerances unless otherwise specified				CUSTOMER		A FCI www.fciconnect.com					
ltr	ecn no.	dr	date	linear	.XX±.01/.XX±.3				projection		title	RIGHT ANGLE RECEPTACLE w/GUIDE PIN POWER			
€					.XXX±.005/.XX±.13										
					.XXX±.0020/.XX±.051										
				angles	0°±2°				INCH/MM 	scale	product family	PWRBLADE		code	
				dr	LEV4		10/14/99					size	dwg no	213	sheet 3
				engr	J. BROWN		10/14/99								
				chr	J. BROWN		10/14/99								
				appd	J. BROWN		10/14/99		3:2	A	51763				
sheet index		revision sheet													
Pro/E								3	cage code				22526	4	

Pro/E

PDM: Rev:E

STATUS: **Released**

Printed: Dec 20, 2010