


Automotive MLCC

General Specifications



GENERAL DESCRIPTION

KYOCERA AVX has supported the Automotive Industry requirements for Multilayer Ceramic Capacitors consistently for more than 25 years. Products have been developed and tested specifically for automotive applications and all manufacturing facilities are QS9000 and VDA 6.4 approved.

KYOCERA AVX is using AECQ200 as the qualification vehicle for this transition. A detailed qualification package is available on request and contains results on a range of part numbers.

HOW TO ORDER

0805	5	A	104	K	4	T	2	A
Size	Voltage	Dielectric	Capacitance Code (In pF)	Capacitance Tolerance	Failure Rate	Terminations	Packaging	Special Code
0402 0603 0805 1206 1210 1812	6.3V = 6 10V = Z 16V = Y 25V = 3 35V = D 50V = 5 100V = 1 200V = 2 500V = 7	NP0 = A X7R = C X8R = F	2 Sig. Digits + Number of Zeros e.g. 10 F = 106	B = ± 0.1pF (<10pF)* C = ± 0.25pF (<10pF)* D = ± 0.5pF (<10pF)* F = ± 1%* G = ± 2%* J = ± 5% (<=1µF) K = ± 10% M = ± 20%	4=Automotive	T = Plated Ni and Sn Z = FLEXITERM®** U = Conductive Epo **X7R X8R only	2 = 7" Reel 4 = 13" Reel	A = Std.Product
					Contact factory for availability of Tolerance Options for Specific Part Numbers.			
					NOTE: Contact factory for non-specified capacitance values 0402 case size available in T termination only.			
					*NPO only			

COMMERCIAL VS AUTOMOTIVE MLCC PROCESS COMPARISON

	Commercial	Automotive
Administrative	Standard Part Numbers. No restriction on who purchases these parts.	Specific Automotive Part Number. Used to control supply of product to Automotive customers.
Lot Qualification (Destructive Physical Analysis - DPA)	As per EIA RS469	Increased sample plan stricter criteria.
Visual/Cosmetic Quality	Standard process and inspection	100% inspection
Application Robustness	Standard sampling for accelerated wave solder on X7R dielectrics	Increased sampling for accelerated wave solder on X7R and NP0 followed by lot by lot reliability testing.


All Tests have Accept/Reject Criteria 0/1

Automotive MLCC
NP0/X7R Dielectric



FLEXITERM FEATURES

- a) Bend Test
The capacitor is soldered to the PC Board as shown:



Typical bend test results are shown below:

Style	Conventional	Soft Term
0603	>2mm	>5
0805	>2mm	>5
1206	>2mm	>5

- a) Temperature Cycle testing
FLEXITERM® has the ability to withstand at least 1000 cycles between -55°C and +125°C

Automotive MLCC-NP0

Capacitance Range



Case Size		0402				0603					0805							1206							1210							
Length (L)	mm (in.)	1.00 ± 0.10 (0.040 ± 0.004)				1.60 ± 0.15 (0.063 ± 0.006)					2.01 ± 0.20 (0.079 ± 0.008)							3.20 ± 0.20 (0.126 ± 0.008)							3.20 ± 0.20 (0.126 ± 0.008)							
Width (W)	mm (in.)	0.50 ± 0.10 (0.020 ± 0.004)				0.81 ± 0.15 (0.032 ± 0.006)					1.25 ± 0.20 (0.049 ± 0.008)							1.60 ± 0.20 (0.063 ± 0.008)							2.50 ± 0.20 (0.098 ± 0.008)							
Terminal (t)	mm (in.)	0.25 ± 0.15 (0.010 ± 0.006)				0.35 ± 0.15 (0.014 ± 0.006)					0.50 ± 0.25 (0.020 ± 0.010)							0.50 ± 0.25 (0.020 ± 0.010)							0.50 ± 0.25 (0.020 ± 0.010)							
CAP	CAP Code	25	50	100	25	50	100	200	250	25	50	100	200	250	500	630	25	50	100	200	250	500	630	1000	50	100	200	250	500	630	1000	
0.5	0R5	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
1	1R0	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
5	5R0	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
10	100	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
12	120	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
15	150	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
18	180	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
22	220	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
27	270	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
33	330	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
39	390	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
47	470	C	C	C	G	G	G	G	G	J	J	J	J	J	J	J	J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
56	560	C	C	C	G	G	G	G	G	J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
68	680	C	C	C	G	G	G	G	G	J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	J	J	J	J	J	J	J	
82	820	C	C	C	G	G	G	G	G	J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	N	N	N	
100	101	C	C	C	G	G	G	G	G	J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	N	N	N	
120	121				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	P	P	P	
150	151				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	P	P	P	
180	181				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	P	P	P	
220	221				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q	Q	N	N	N	N	P	P	P	
270	271				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q		N	N	N	N	P	P	P	
330	331				G	G	G			J	J	J	J	J	N		J	J	J	J	J	J	Q		N	N	N	N	P	P	P	
390	391				G	G	G			J	J	J	J	J			J	J	J	J	J	J	Q		N	N	N	N	P	P	P	
430	431				G	G				J	J	J	J	J			J	J	J	J	J	J	Q		N	N	N	N	P	P	P	
470	471				G	G				J	J	J	J	J			J	J	J	J	J	J	Q		N	N	N	N	P	P	P	
560	561				G	G				J	J	J	J				J	J	J	J	M	Q	Q		N	N	N	N	P	P	P	
680	681				G	G				J	J	J	J				J	J	J	J	M	Q	Q		N	N	N	N	P	P	P	
1,000	102				G	G				J	J	J	J				N	J	J	J	M	Q	Q		N	N	N	N	P	P	X	
1,200	122				G	G				J	J						N	N	N	N					N	N	N	N	P	P		
1,500	152				G	G				J	J						N	N	N	N					N	N	N	N	P	P		
2,200	222				G					J	J						J	J	J	J	J	J	J		N	N	N	N	P	K	K	
2,700	272				G												J	J	J	J	J	J	J						K	K		
3,300	332				G												M	M	M	M	M	M	M						K	K		
3,900	392				G												M	M	M	M	M	M	M						M	M		
4,700	472				G												P	P	P	P	P	P	P						M	M		
5,600	562				G																								M	M		
6,800	682				G																								N	N		
8,200	822				G																								P	P		
10,000	103				G																								X	X	X	
12,000	123																												X			
15,000	153																												X			
18,000	183																												X			
22,000	223																												X			
27,000	273																												X			
33,000	333																												X			
39,000	393																															
47,000	473																															
56,000	563																															
68,000	683																															
82,000	823																															
100,000	104																															
CAP	CAP Code	25	50	100	25	50	100	200	250	25	50	100	200	250	500	630	25	50	100	200	250	500	630	1000	50	100	200	250	500	630	1000	
Case Size		0402				0603					0805							1206							1210							

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSSED							

[illegible]

Automotive MLCC - X8R

Capacitance Range

SIZE			0603			0805			1206	
Soldering			Reflow/Wave			Reflow/Wave			Reflow/Wave	
WVDC	WVDC		25V	50V	100V	25V	50V	100V	25V	50V
472	pF	4700	G	G	G	J	J	J	J	J
562		5600	G	G	G	J	J	J	J	J
682		6800	G	G	G	J	J	J	J	J
822		8200	G	G	G	J	J	J	J	J
103	uF	0.01	G	G	G	J	J	J	J	J
123		0.012	G	G		J	J	N	J	J
153		0.015	G	G		J	J	N	J	J
183		0.018	G	G		J	J	N	J	J
223		0.022	G	G		J	J	N	J	J
273		0.027	G	G		J	J		J	J
333		0.033	G	G		J	J		J	J
393		0.039	G	G		J	J		J	J
473		0.047	G	G		J	J		J	J
563		0.056	G			N	N		M	M
683		0.068	G			N	N		M	M
823		0.082				N	N		M	M
104		0.1				N	N		M	M
124		0.12				N	N		M	M
154		0.15				N	N		M	M
184		0.18				N			M	M
224		0.22				N			M	M
274		0.27							M	M
334		0.33							M	M
394		0.39							M	M
474		0.47							M	Q
684		0.68							Q	Q
824		0.82							Q	Q
105		1							Q	Q
WVDC	WVDC		25V	50V	100V	25V	50V	100V	25V	50V
SIZE			0603			0805			1206	

Letter	A	C	E	G	J	K	M	N	P	Q	X	Y	Z
Max. Thickness	0.33 (0.013)	0.56 (0.022)	0.71 (0.028)	0.90 (0.035)	0.94 (0.037)	1.02 (0.040)	1.27 (0.050)	1.40 (0.055)	1.52 (0.060)	1.78 (0.070)	2.29 (0.090)	2.54 (0.100)	2.79 (0.110)
PAPER						EMBOSSED							