

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190170074](#)
Status: **Active**
Overview: [Standard Quick-Disconnect Terminals](#)
Description: InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm²) Wire, Metal Strip, Tab 6.35 x 0.81mm

Documents:
[3D Model](#) [Product Specification PS-19902-008-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E79133


General
Product Family Quick Disconnects
Series [19017](#)
Crimp Quality Equipment Yes
Insulated Partial
Overview [Standard Quick-Disconnect Terminals](#)
Product Name InsulKrimp
Type Quick Disconnect
UPC 800753036772

Physical
Barrel Type Closed
Color - Resin Blue
Flammability 94V-0
Gender Female
Glow-Wire Capable No
Insulation PVC
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.778/g
Orientation Straight
Packaging Type Reel
Polarized to Mating Part No
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating -50° to +105°C
Wire Insulation Diameter 3.70mm max.
Wire Size AWG 14, 16
Wire Size mm² 1.30-2.00

Electrical
Voltage - Maximum 600V

Material Info
Engineering Number BBZ-2141

Reference - Drawing Numbers
Product Specification PS-19902-008-001, PS-19902-011-001
Sales Drawing SD-19017-003-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19017 Series](#)

Application Tooling | [FAQ](#)
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	Product #
Description	
Mini-Mac Applicator	638814600
Mechanical Feed-Metal Strip	

This document was generated on 11/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION