



Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NO.	ROWS										
		SIGNAL			POWER						
51711-004-- NOTE ③	D C B A	E1	1	2	3	P1	P2	P3	P4	E2	



CODE	DIM "M" MATING LENGTH	CONTACT TYPE
PA	[N/A]	POWER
E	[6.86]	SIGNAL
HA	[N/A]	HOLD-DOWN
H	[5.59]	SIGNAL
L	[7.82]	SIGNAL

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.5	COPY		www.fciconnect.com	
A	DG09-0106	WD	04/08/09		0.XX ±0.25	projection		title	
				angles	0.XXX ±0.1			12S + 4P	
					0° ±2°	MIM		VERTICAL SOLDER HEADER	
				dr	Warren Du 03/28/09	product family		PwrBlade	code
				enrg	Warren Du 03/28/09	size		dwg no	213
				chr	PM ZHENG 03/28/09	scale		51711-004	sheet
				appd	JOSEPH HSIA 03/28/09	1:1		A	1 of 4
sheet index	revision sheet	A	A	A	A				
		1	2	3	4				

Pro/E


cage code 22526

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.




All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
51711-004--
NOTE 3



SECTION A-A
SCALE 2:1



SECTION B-B
SCALE 2:1




SECTION C-C
SCALE 2:1

mat'l code				tolerances unless otherwise specified		CUSTOMER		FCI	
ltr	ecn no.	dr	date	linear	0.X ±0.5	COPY		www.fciconnect.com	
A				linear	0.XX ±0.25	projection		title 12S + 4P	
				angles	0.XXX ±0.1			VERTICAL SOLDER HEADER	
				angles	0° ±2°			product family PwrBlade code	
				dr	Warren Du 03/28/09	MIM		size 213	
				enr	Warren Du 03/28/09			dwg no 51711-004	
				chr	PM ZHENG 03/28/09	scale		sheet 2 of 4	
				appd	JOSEPH HSIA 03/28/09	1:1			
sheet index	revision sheet							cage code 22526	

Pro/E

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor.
Property of FCI. Copyright FCI.

mat'l code				tolerances unless otherwise specified				CUSTOMER		 www.fciconnect.com					
lfr	ecn no.	dr	date	linear	0.X ±0.5				COPY		title	12S + 4P VERTICAL SOLDER HEADER			
A					0.XX ±0.25				projection						
					0.XXX ±0.1										
				angles	0° ±2°						product family		PwrBlade	code	
				dr	Warren Du	03/28/09			scale	size	dwg no		213		
				engr	Warren Du	03/28/09				A	51711-004		sheet		
				chr	PM ZHENG	03/28/09							3 of 4		
				appd	JOSEPH HSIA	03/28/09			1:1						
sheet index		revision sheet													
Pro/E				3				cage code				22526		4	

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.



All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

PRODUCT NUMBER
51711-004-- NOTE 3

NOTES:

1. DIMENSIONS AND TOLERANCES ARE IN ACCORDANCE WITH ASME Y14.5M, 1994 UNLESS OTHERWISE SPECIFIED.

CONNECTOR NOTES:

- ② HOUSING MATERIAL: UL 94 V-0 GLASS FILLED HIGH-TEMP THERMOPLASTIC
POWER CONTACT MATERIAL: COPPER ALLOY
SIGNAL PIN MATERIAL: COPPER ALLOY
3. SEE ITEM 1 & 2 IN PRINT 10064183 FOR PLATING SPEC OF 51711-004 AND 51711-004LF RESPECTIVELY.
- ④ MANUFACTURER'S NAME, P/N, AND DATE CODE TO APPEAR ON THIS SURFACE.
5. PRODUCT SPECIFICATION GS-12-149.
APPLICATION SPECIFICATION BUS-20-067.
6. PACKAGED IN TRAYS.
- PCB NOTES:
7. ALL HOLE DIAMETERS ARE FINISHED HOLE SIZE.
8. MOUNTING HOLES, WHERE APPLICABLE, ARE UNPLATED.

- ⑨ $\varnothing 1.151 \pm 0.025$ DRILLED HOLES PLATED WITH
0.008 MIN SnPb OR Sn OVER .001 [0.03]
TO 0.08 Cu PLATING TO ACHIEVE
 $\varnothing 1.02 \pm .07$ HOLE.
- ⑩ "DIM XXX" TO BE DETERMINED BY THE CUSTOMER.
- ⑪ CONNECTOR KEEP-OUT ZONE.

mat'l code				tolerances unless otherwise specified				CUSTOMER				FCI www.fciconnect.com									
ltr	ecn no.	dr	date	linear	0.X ± 0.5				COPY				title 12S + 4P VERTICAL SOLDER HEADER								
A					0.XX ± 0.25				projection												
					0.XXX ± 0.1																
				angles	0° ± 2°								product family PwrBlade								
				dr	Warren Du	03/28/09		MM				size					dwg no		213		
				enrg	Warren Du	03/28/09		1:1				A					51711-004		sheet		
				chr	PM ZHENG	03/28/09		scale				A		51711-004		4 of 4					
				appd	JOSEPH HSIA	03/28/09															
sheet index		revision sheet																			

cage code 22526