


REV.	DATE	DESCRIPTION
NC	06/25/98	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex													
8						DRAWN	G.R.S.								07/20/05						
7						CHECKED										PART DESCRIPTION					
6									SMB R/A CRIMP PLUG (FOR RG-178/U, 196/U CABLE)												
5	HEAT SHRINK TUBE			1					PART NO.												
4	FERRULE	BRASS	GOLD	1					142195												
3	CONTACT PIN	BER. COPPER	GOLD	1				1 OF 1													
2	INSULATOR	TEFLON	NATURAL	1					CAD FILE	DWG. NO.				142195.DWG	REV.	A	SIZE	A	SCALE	NA	
1	BODY	BRASS	GOLD	1				C:/142/142195.DWG													
	DESCRIPTION	MATERIAL	FINISH	QTY																	