






Recommended
Panel Cut-Out

Note:

- *  Important Dimension.
- * Waterproof Rate: IP68.
IP68: 1M Depth of Water in 24hours.
- * Housing: Nylon+GF, Black.
- * Female Pin: Copper Alloy, Gold Plated.
- * Shell: Metal, Nickel Plated.
- * Ground Lug: Copper Alloy, Nickel Plated.
- * Screw Nut: Copper Alloy, Nickel Plated.
- * Panel O-Ring: Viton, Green.
- * Housing O-Ring: Viton, Green.
- * Rated Voltage: 3Pin 60V dc. or ac.
4Pin 30V dc. or ac.
- * Rated Current: 3 & 4Pin 4A
- * Operating Temperature: -40~105°C
- * For Panel Thickness: Min=2.0mm, Max=4.5mm.
- * For PCB Thickness: Max=1.6mm.
- * Recommended Nut Torque: 4~6 Kgf.cm.

UNIT: mm				TITLE M8 Female Conn. Panel 90° PCB Type (Shielded) SCALE 2:1 SIZE A4 SHEET 1 OF 2 REV. A WC-REV. A.1.1 QC: Inspection item				Amphenol LTW 安費諾亮泰企業股份有限公司				ITEM NO		DRAWN BY Yulong_wang		DATE 2016-01-20	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		DWG NO M8S-XXPFFR-SF8001										CHECKED BY Cary		DATE 2016-01-20			
		CUSTOMER ALTW										APPROVED BY Jerry		DATE 2016-01-20			
		2		3		4		5		6		7		8			




FWW10702-01-02

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

M 8S - XX P F F R - S F 8 001

8:M8 Sensor Shielded
03:3Pin
04:4Pin
P:Panel(板端)
F:Female Connector(母座)
F:Female Pin(母Pin)

001:Phantom(虛擬料號)
8:IP68(防水等級68)
F:Front Fasten(前鎖式/Enclosure Rear Mount)
S:Screw(螺紋式)
R:90° PCB THT/DIP Type(90°基板插件式)



UNIT:mm				TITLE M8 Female Conn. Panel 90° PCB Type (Shielded)		ITEM NO		DRAWN BY Yulong_wang		DATE 2016-01-20	
TOLERANCE .X XX XXX ANGLES		SCALE 2:1		SIZE A4		DWG NO M8S-XXPFFR-SF8001		CHECKED BY Cary		DATE 2016-01-20	
±0.25 ±0.1 ±0.05 ±1°		REV. A		WC-REV. A.11		CUSTOMER ALTW		APPROVED BY Jerry		DATE 2016-01-20	
				SHEET 2 OF 2							
				QC: Inspection item							

Amphenol LTW
安費諾亮泰企業股份有限公司