

# Non EMC DIN-Based VectorPak™ Subracks

Rack Components  
& Accessories




## Adapter Plates (Z-Rail Type)

| Part No.            | Description                                                                                                                            |
|---------------------|----------------------------------------------------------------------------------------------------------------------------------------|
| AS1/2<br>(Pkg of 2) | Adapter plate for mounting DIN connectors directly onto subrack, 84 tapped holes (2.5mm x 4.5mm pitch)<br>To be used without backplane |

## Insulation Strips

Mounted between backplane and rear extrusion


| Part No.   | HP | Width            |
|------------|----|------------------|
| 5250998-84 | 84 | 17.00" (431.8mm) |




## Nut Strips

Threaded mounting holes spaced at 0.2" centers slide into extrusion grooves, can be used to anchor panels, cards or other components. Used on front & rear extrusions on all Vector DIN based metric subracks.

| Part No.   | HP | Width           |
|------------|----|-----------------|
| 5250268-84 | 84 | 17" (431.8mm)   |
| 5250268-63 | 63 | 12.8" (325.1mm) |
| 5250268-42 | 42 | 8.6" (218.4mm)  |
| 5250268-21 | 21 | 4.4" (111.8mm)  |




# Extrusions



All extrusions available in any length


| Part No.   | HP | A              |
|------------|----|----------------|
| 5250236-84 | 84 | 17.00" (431.8) |
| 5250236-63 | 63 | 12.80" (325.8) |
| 5250236-42 | 42 | 8.60" (218.4)  |
| 5250236-21 | 21 | 4.40" (11.8)   |

Pack of 12 8-32 screws, P/N HD94




| Part No.   | HP | A              |
|------------|----|----------------|
| 5250238-84 | 84 | 17.00" (431.8) |
| 5250238-63 | 63 | 12.80" (325.8) |
| 5250238-42 | 42 | 8.60" (218.4)  |
| 5250238-21 | 21 | 4.40" (11.8)   |

Pack of 12 8-32 screws, P/N HD94



| Part No.   | HP | A              |
|------------|----|----------------|
| 5250237-84 | 84 | 17.00" (431.8) |
| 5250237-63 | 63 | 12.80" (325.8) |
| 5250237-42 | 42 | 8.60" (218.4)  |
| 5250237-21 | 21 | 4.40" (11.8)   |


Pack of 12 8-32 screws, P/N HD94




| Part No.   | HP | A              |
|------------|----|----------------|
| 5250229-84 | 84 | 17.00" (431.8) |
| 5250229-63 | 63 | 12.80" (325.8) |
| 5250229-42 | 42 | 8.60" (218.4)  |
| 5250229-21 | 21 | 4.40" (11.8)   |

Pack of 12 8-32 screws, P/N HD94




















#8-32 TAP x .600 DEEP  
4 PL.  
NOTE: TAP THRU FOR  
P/N # -03, -04, -05

| REVISIONS |      |                   |      |          |
|-----------|------|-------------------|------|----------|
| ZONE      | REV. | DESCRIPTION       | DATE | APPROVED |
| ALL       | A    | REVISED & REDRAWN |      |          |
|           |      |                   |      |          |
|           |      |                   |      |          |

| TABULATION |       |
|------------|-------|
| PART NO. 7 | "A"   |
| 5250229-03 | 0.800 |
| 5250229-04 | 1.000 |
| 5250229-05 | 1.200 |
| 5250229-06 | 1.400 |
| 5250229-07 | 1.600 |
| 5250229-08 | 1.800 |
| 5250229-09 | 2.000 |
| 5250229-10 | 2.200 |
| 5250229-11 | 2.400 |
| 5250229-12 | 2.600 |
| 5250229-13 | 2.800 |
| 5250229-14 | 3.000 |
| 5250229-15 | 3.200 |
| 5250229-16 | 3.400 |
| 5250229-17 | 3.600 |
| 5250229-18 | 3.800 |
| 5250229-19 | 4.000 |
| 5250229-20 | 4.200 |
| 5250229-21 | 4.400 |

| TABULATION |       |
|------------|-------|
| PART NO. 7 | "A"   |
| 5250229-22 | 4.600 |
| 5250229-23 | 4.800 |
| 5250229-24 | 5.000 |
| 5250229-25 | 5.200 |
| 5250229-26 | 5.400 |
| 5250229-27 | 5.600 |
| 5250229-28 | 5.800 |
| 5250229-29 | 6.000 |
| 5250229-30 | 6.200 |
| 5250229-31 | 6.400 |
| 5250229-32 | 6.600 |
| 5250229-33 | 6.800 |
| 5250229-34 | 7.000 |
| 5250229-35 | 7.200 |
| 5250229-36 | 7.400 |
| 5250229-37 | 7.600 |
| 5250229-38 | 7.800 |
| 5250229-39 | 8.000 |
| 5250229-40 | 8.200 |
| 5250229-41 | 8.400 |
| 5250229-42 | 8.600 |

| TABULATION |        |
|------------|--------|
| PART NO. 7 | "A"    |
| 5250229-43 | 8.800  |
| 5250229-44 | 9.000  |
| 5250229-45 | 9.200  |
| 5250229-46 | 9.400  |
| 5250229-47 | 9.600  |
| 5250229-48 | 9.800  |
| 5250229-49 | 10.000 |
| 5250229-50 | 10.200 |
| 5250229-51 | 10.400 |
| 5250229-52 | 10.600 |
| 5250229-53 | 10.800 |
| 5250229-54 | 11.000 |
| 5250229-55 | 11.200 |
| 5250229-56 | 11.400 |
| 5250229-57 | 11.600 |
| 5250229-58 | 11.800 |
| 5250229-59 | 12.000 |
| 5250229-60 | 12.200 |
| 5250229-61 | 12.400 |
| 5250229-62 | 12.600 |
| 5250229-63 | 12.800 |

| TABULATION |        |
|------------|--------|
| PART NO. 7 | "A"    |
| 5250229-64 | 13.000 |
| 5250229-65 | 13.200 |
| 5250229-66 | 13.400 |
| 5250229-67 | 13.600 |
| 5250229-68 | 13.800 |
| 5250229-69 | 14.000 |
| 5250229-70 | 14.200 |
| 5250229-71 | 14.400 |
| 5250229-72 | 14.600 |
| 5250229-73 | 14.800 |
| 5250229-74 | 15.000 |
| 5250229-75 | 15.200 |
| 5250229-76 | 15.400 |
| 5250229-77 | 15.600 |
| 5250229-78 | 15.800 |
| 5250229-79 | 16.000 |
| 5250229-80 | 16.200 |
| 5250229-81 | 16.400 |
| 5250229-82 | 16.600 |
| 5250229-83 | 16.800 |
| 5250229-84 | 17.000 |

7. DASH NO(S). INDICATE RACK SPACE IN "HP" UNITS (HOLE PITCH OF .200)  
6. FINISH: SATIN ETCH, 7 MIN., CHEM FILM, CLEAR, CLASS 1A, IAW MIL-C-5541  
5. DEGREASE  
4. REMOVE ALL BURS & SHARP EDGES  
3. FINE GRAIN FINISH ON SURFACES INDICATED (3 PL.)  
2. ENDS TO BE SQUARE WITHIN: .0025 PER INCH OF WIDTH  
1. MAT'L: MAKE FROM P/N # 5280220

NOTES: UNLESS OTHERWISE SPECIFIED.

PROPRIETARY AND CONFIDENTIAL  
THE INFORMATION CONTAINED IN THIS  
DRAWING IS THE SOLE PROPERTY OF  
VECTOR ELECTRONICS & TECH., INC. ANY  
REPRODUCTION IN PART OR AS A WHOLE  
WITHOUT THE WRITTEN PERMISSION OF  
VECTOR ELECTRONICS & TECH., INC. IS  
PROHIBITED.

|                                                                                                                                                                           |  |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED:                                                                                                                                               |  |
| DIMENSIONS ARE IN INCHES<br>TOLERANCES:<br>FRACTIONAL ±<br>ANGULAR: ±5°<br>TWO PLACE DECIMAL ±.XX<br>THREE PLACE DECIMAL ±.005<br>INTERPRET GEOMETRIC<br>TOLERANCING PER: |  |
|                                                                                                                                                                           |  |
|                                                                                                                                                                           |  |
|                                                                                                                                                                           |  |
|                                                                                                                                                                           |  |
| MATERIAL 1                                                                                                                                                                |  |
| FINISH 6                                                                                                                                                                  |  |
| DO NOT SCALE DRAWING                                                                                                                                                      |  |

|                        |         |          |
|------------------------|---------|----------|
|                        | NAME    | DATE     |
| DRAWN                  | TRUSHAR | 01/12/09 |
| CHECKED                |         |          |
| ENG APPR.              |         |          |
| MFG APPR.              |         |          |
| Q.A.                   |         |          |
| THIRD ANGLE PROJECTION |         |          |
|                        |         |          |

|                                                  |          |                                                    |              |
|--------------------------------------------------|----------|----------------------------------------------------|--------------|
| <b>VECTOR</b>                                    |          | 11115 VANOWEN ST.,<br>NORTH HOLLYWOOD,<br>CA 91605 |              |
| ELECTRONICS & TECHNOLOGY, INC                    |          |                                                    |              |
| <b>EXTRUSION CENTER NARROW<br/>VME CARD CAGE</b> |          |                                                    |              |
| SIZE                                             | DWG. NO. |                                                    | REV          |
| B                                                | 5250229  |                                                    | A            |
| SCALE: 1:1                                       |          | WEIGHT:                                            | SHEET 1 OF 1 |