


PART NUMBER	ITEM ① UMC TO SMA JACK CONVERSION ADAPTER
134-1019-361	BODY - STAINLESS STEEL - GOLD PLATED CONTACT - BRASS - GOLD PLATED NUT - STAINLESS STEEL - PASSIVATED INSULATOR - FLUORINE PLASTICS GASKET - RUBBER



NOTES:

1. SPECIFICATIONS:

IMPEDANCE: 50 OHMS
FREQUENCY RANGE: 0-6 GHz
VSWR: 1.30 MAX AT 0-6 GHz

MECHANICAL (UMC):

COMPATIBILITY: MATES WITH U.FL SERIES
DISENGAGEMENT FORCE (MIN): 0.15 N (FEMALE CONTACT)
DURABILITY: 3000 CYCLES

ENVIRONMENTAL:

TEMPERATURE RANGE: -40° C TO +90° C

2. APPLICATION:

PLEASE USE THIS CONNECTOR FOR
MEASURING THE PROPAGATION
PERFORMANCE.

DRAWING NO.									
B - 134-1019-361/370									
0		REVISIONS							
ENGINEERING RELEASE									
1	12-1-06	P A T	S B D	R J B	P D W			12-27-06	ECN 50793

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED
PER ASME Y 14.5M - 1994

"μSTATION"

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY SBD	DATE 11/29/06	 Connectivity Solutions P.O. Box 1732 Waseca, MN 56093 1-800-247-8256	
DECIMALS	mm	CHECKED BY RJB	DATE 12-13-06		
.XX	_____			TITLE UMC JACK TO SMA PLUG CONVERSION JACK ADAPTER	
.XXX REF	_____	APPROVED BY PDW	DATE 12-22-06		
MATL _____		RELEASE DATE 12-27-06		SHEET 2 OF 2	DRAWING NO. B- 134-1019-361/370
FINISH _____		U/M INCH/mm	SCALE 3:1		