




TML-108-02-G-D-SM



TML-120-01-L-D-RA



TML-132-02-L-D-SM



(1,27 mm) .050"

TML SERIES

SHROUDED MICRO HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/TML

Insulator Material:

Black Liquid Crystal Polymer

Insulation Resistance:

5000 MΩ min

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50μ" (1,27 μm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes



SMT Lead Coplanarity:

(0,15 mm) .006" max

Mates with:

SMS, RSM

APPLICATIONS



RECOGNITIONS


For complete scope of recognitions see www.samtec.com/quality





ALSO AVAILABLE (MOQ Required)

- Other sizes
 - Other platings
- Contact Samtec.

TML	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	TAIL OPTION	OTHER OPTION
			Specify LEAD STYLE from chart	-L = 10μ" (0,25 μm) Gold on post, Matte Tin on tail -G = 10μ" (0,25 μm) Gold on post, Gold flash on tail		-RA = Right Angle -SM = Surface Mount (For locking clip add -LC)	- "XXX" = Polarized position (Specify position of omitted pin)



LEAD STYLE	POST HEIGHT (A)
-01	(3,05) .120
-02	(5,84) .230
-03	(4,32) .170



Note: Some sizes, styles and options are non-standard, non-returnable.