



[About Us](#)
[Products](#)
[Services](#)
[Support](#)
[Projects](#)
[Web Shop](#)

Products

[» Board Comparison Chart](#)
[» Developer's Kits](#)
[» OEM Boards](#)
[↓ QuickStart Boards](#)
[» LPC1343](#)
[» LPC2106 RS232](#)
[» LPC2129 CAN](#)
[» LPC2148 USB](#)
[» Prototype board](#)
[» Christmas Tree](#)
[» Color LCD Bluetooth Game](#)
[» Education Boards](#)
[» LPCXpresso & mbed](#)
[» Displays](#)
[» Tools](#)
[» Accessories](#)

QuickStart Prototype Board



Price Information

EUR

Art.no: **EA-QSB-100** [Buy](#)

[Overview](#)
[Specification](#)
[Related Products](#)
[Resources](#)
[FAQ](#)

QuickStart Prototype Board

- Large prototype area (100 mil hole spacing)
- Smaller prototype area with 50 mil hole spacing
- SMD area for 50 mil SO circuits
- SMD area for 0.65 mm SSOP circuits
- MMC/SD connector, connected to SPI bus
- 7-segment display connected to SPI bus
- 16 LEDs
- 4 switches
- Reset button
- JTAG connector
- 9-pol DSUB connector for UART #1
- Power supply 5VDC (center pin negative) or 9VDC (any polarity) or 6VAC
- Two 9-pol DSUB connectors for CAN board (not mounted)
- RS232 circuit for LPC2106 board (not mounted)
- 196 x 125 mm in size

© Embedded Artists

[Legal Information](#)

[Privacy Statement](#)

The Art of Embedded Systems Development - made Easy™