


T6A40

ROW DRIVER FOR A DOT MATRIX LCD

The T6A40 is a 68-channel-output row driver for an STN dot matrix LCD. The T6A40 features -28V LCD drive voltage. The T6A40 is able to drive LCD panels with a duty ratio of up to $1/240$. It is recommended for use with the T6A39.


FEATURES

- Display duty application : to $1/240$
- LCD drive signal : 68
- Data transfer : 1-bit bidirectional
 - ① $O68 \leftarrow O1$
 - ② $O68 \rightarrow O1$
 - ③ $O1 \rightarrow O34, O35 \leftarrow O68$
- LCD drive voltage : -8 to -28V (max -30V)
- Operating voltage : 4.5 to 5.5V
- Operating temperature : -20 to 75°C
- LCD drive output resistance : $1.5\text{k}\Omega$ (max) (12.8V , $1/9$ bias)
- LCD drive output timing : Change on falling edge of LP



Weight : 1.45g (typ.)


BLOCK DIAGRAM



961001EBA2

- TOSHIBA is continually working to improve the quality and the reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to observe standards of safety, and to avoid situations in which a malfunction or failure of a TOSHIBA product could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent products specifications. Also, please keep in mind the precautions and conditions set forth in the TOSHIBA Semiconductor Reliability Handbook.
- The products described in this document are subject to foreign exchange and foreign trade control laws.
- The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA CORPORATION for any infringements of intellectual property or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any intellectual property or other rights of TOSHIBA CORPORATION or others.
- The information contained herein is subject to change without notice.

PIN ASSIGNMENT



PIN FUNCTIONS

PIN NAME	I/O	FUNCTIONS	LEVEL
O1 to O68	Output	Output for LCD drive signal	V_{DD} to V_5
DIO1, DIO2	I/O	Input/output for shift data	V_{DD} to V_{SS}
LP	Input	(Shift Clock Pulse) Input for shift clock pulse	
FR	Input	(Frame) Input for frame signal	
DUAL	Input	(Dual Mode) Terminal for dual input mode or single input mode select	
DIR	Input	(Direction) Input for data flow direction select	
TSW	Input	(Terminal Switch) When tied to V_{SS} : (O1 to O68) output on the rising edge of LP When tied to V_{DD} : (O1 to O68) output on the falling edge of LP	
V_{DD}	—	Power supply for internal logic (5V)	—
V_{SS}	—	Power supply for internal logic (0V)	
V_1	—	Power supply for LCD drive circuit	
V_4	—	Power supply for LCD drive circuit	
V_5	—	Power supply for LCD drive circuit	

RELATION BETWEEN FR, DATA INPUT AND OUTPUT LEVEL

FR	DATA INPUT (DIO1, DIO2)	OUTPUT LEVEL
L	L	V_1
L	H	V_5
H	L	V_4
H	H	V_{DD}

DATA INPUT FORMAT

DUAL	DIR	DATA FLOW	DATA INPUT	
			DIO1	DIO2
V_{DD}	V_{DD}	O1→O34	IN	IN
		O68→O35		
V_{SS}	V_{DD}	O1→O68	IN	OUT
V_{DD}	V_{SS}	O68→O1	OUT	IN
V_{SS}	V_{SS}			

ABSOLUTE MAXIMUM RATINGS(Ensure that the following conditions are maintained, $V_{DD} \geq V_1 \geq V_4 \geq V_5$, $V_{SS} = 0V$)

ITEM	SYMBOL	PIN NAME	RATING	UNIT
Supply Voltage 1	V_{DD}	V_{DD}	- 0.3 to 7.0	V
Supply Voltage 2	V_1	V_1	$V_{DD} - 30.0$ to $V_{DD} + 0.3$	V
Supply Voltage 3	V_4	V_4	$V_{DD} - 30.0$ to $V_{DD} + 0.3$	V
Supply Voltage 4	V_5	V_5	$V_{DD} - 30.0$ to $V_{DD} + 0.3$	V
Input Voltage	V_{IN}	(*1)	- 0.3 to $V_{DD} + 0.3$	V
Operating Temperature	T_{opr}	—	- 20 to 75	°C
Storage Temperature	T_{stg}	—	- 55 to 125	°C


(*1) FR, DIR, DIO1, DIO2, DUAL, TSW, LP

ELECTRICAL CHARACTERISTICS**DC CHARACTERISTICS**TEST CONDITIONS (Unless otherwise noted, $V_{SS} = 0V$, $V_{DD} = 4.5V$ to $5.5V$, $V_5 = (V_{DD} - 23)V \pm 10\%$, $T_a = -20$ to $75^\circ C$)

ITEM	SYMBOL	TEST CIR- CUIT	TEST CONDITION	MIN	TYP.	MAX	UNIT	PIN NAME
Supply Voltage 1	V_{DD}	—	—	4.5	5.0	5.5	V	V_{DD}
Supply Voltage 2	V_5	—	—	$V_{DD} - 28$	—	$V_{DD} - 8.0$	V	V_5
Input Voltage	H Level	V_{IH}	(*2)	$V_{DD} - 0.8$	—	V_{DD}	V	FR, DIR, DIO1, DIO2, DUAL, LP, TSW
	L Level	V_{IL}		0	—	0.8		
Output Voltage	H Level	V_{OH}	$I_{OH} = -0.5mA$	$V_{DD} - 0.5$	—	V_{DD}	V	DIO1, DIO2
	L Level	V_{OL}		—	—	0.5		
Output Resistance	H Level	R_{OH}	$V_{OUT} = V_{DD} - 0.5V$ (*3)	—	—	1.2	k Ω	O1 to O68
	M Level	R_{OM}	$V_{OUT} = V_1 \pm 0.5V$ (*3)	—	—	1.2		
		R_{OM}	$V_{OUT} = V_4 \pm 0.5V$ (*3)	—	—	1.2		
	L Level	R_{OL}	$V_{OUT} = V_5 + 0.5V$ (*3)	—	—	1.2		
Current Consumption	I_{SS}	—	$V_{DD} = 5.5V$ $V_5 = -22.5V$ $f_{FR} = 35.5Hz$ $f_{LP} = 7.1kHz$ O1 to O68 : no load	—	2.0	4.0	μA	V_{SS}

(*2) $R_L = 3k\Omega$, $C_L = 1500pF$ (*3) $V_{DD} = 5.0V$, $V_5 = -7.8V$, $V_1 = V_{DD} - 1/9(V_{DD} - V_5)$, $V_4 = V_{DD} - 8/9(V_{DD} - V_5)$

AC CHARACTERISTICS



TEST CONDITIONS ($V_{SS} = 0V$, $V_{DD} = 4.5$ to $5.5V$, $V_5 = (V_{DD} - 23)V \pm 10\%$, $T_a = -20$ to $75^\circ C$)

ITEM	SYMBOL	TEST CONDITION	MIN	MAX	UNIT
SCP Pulse Width H	t_{CWH}	LP	30	—	ns
SCP Pulse Width L	t_{CWL}	LP	1	—	μs
Input Rise / Fall Time	t_r, t_f	LP, FR, DIO1, DIO2	—	50	ns
Data Set-up Time	t_{DSU}	DIO1, DIO2	30	—	ns
Data Hold Time	t_{DHD}	DIO1, DIO2	50	—	ns
Output Data Delay Time A (*4)	t_{pdA}	DIO1, DIO2	80	—	ns
Output Data Delay Time B (*4)	t_{pdB}	DIO1, DIO2	—	1	μs

(*4) $C_L = 10pF$


NOTE

Insert the bypass capacitor ($0.1\mu F$) between V_{DD} and V_{SS} to decrease power supply noise.
Place the bypass capacitor as close to the LSI as possible.

OUTLINE DRAWING

QFP92-P-1818-0.70B

Unit : mm



Weight : 1.45g (Typ.)