



Material:

- Terminal body
- (metal housing): Steel Zinc plated
- Terminal screw: Steel Zinc plated "-slot type.
- Wire guard: PhBz (CuSn) Tin plated
- Insulator(housing): Thermoplastic (UL94V-0)

Electrical:

- Voltage rating: 300V
- Current rating: 20A
- Wire range:
 - Solid wire(AWG): 12-22
 - Stranded wire(AWG): 12-22
- Torque: 3.5Lb-In
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -30°C to $+105^{\circ}\text{C}$
- Safety Approval:
- RoHS Compliant

PART NUMBER:

OSTVMXX5551

No. of Poles
02 2 Poles
03 3 Poles
...
24 24 Poles

COLOR
0: Black
5: Green (Standard)
6: Blue
8: Grey



ON-SHORE TECHNOLOGY, INC.

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.

TITLE		OSTVM 5.08mm Low Profile Type Series				
PART NO.	OSTVMXX5551			DWG NO.	OSTVMXX5551.DWG	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance	
Shi Jun 2006.10.30	Shi Jun 2006.10.30	Tony 2005.11.08	Tony 2005.05.16		UNIT: mm	X. ± 0.50
					SCALE: NONE	X.X ± 0.30
					REV: C	X.XX ± 0.10
						X° $\pm 1^{\circ}$

SHEET: 01/01