




LOC		DIST		REVISIONS					
HM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			D	REV PER ECO-12-020239			03DEC2012	JM	MS

- 1

DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 2

CABLE ASSEMBLY IS WIRED PER WIRING DIAGRAM.
- 3

MATERIAL:

CONNECTOR HOUSINGS- POLYCARBONATE, UL 94V-0 RATED, NEMA GRAY.

STRAIN RELIEFS- CARBON STEEL WITH NICKEL PLATING 5.08µm [0.000200] MINIMUM THICK.

CONTACTS- COPPER ALLOY WITH SILVER PLATED STRIP 3.81µm [0.000150] MINIMUM THICK.
- 4

DIMENSION A SHALL BE MEASURED WITH CONDUIT IN THE RELAXED POSITION.
- 5

DESIGNATIONS IN PARENTHESES () ARE FOR REFERENCE ONLY.
- 6

MANUFACTURING LOCATION, DATE CODE, PART NUMBER AND LENGTH SHALL BE INK STAMPED APPROXIMATELY WHERE INDICATED.
- 7

APPLICATION: AMPINERGY (TM) - MODULAR POWER DISTRIBUTION SYSTEM, A MANUFACTURED WIRING SYSTEM.
- 8

CABLE CONNECTOR MATES WITH DEDICATED NEUTRAL (3-3-2) POWER AND LINE CONNECTOR CABLE ASSEMBLIES, JUNCTION BOXES, POWERSTRIPS AND PDMS. KEYING FEATURE MAINTAINS CORRECT POLARITY OF MATING POWER OR LINE CONNECTORS.
- 9

TABS FOR POSITIVE LATCHING TO MATING COMPONENTS.
- 10

USE GROUND WIRE INSPECTION WINDOW TO VERIFY BONDING AND GROUNDING CONDUCTOR.

15240.0-15316.2 [600.00-603.00]	5-1933401-0	15.24 [50.00]
12192.0-12268.2 [480.00-483.00]	4-1933401-0	12.19 [40.00]
9144.0-9220.2 [360.00-363.00]	3-1933401-0	9.14 [30.00]
7620.0-7696.2 [300.00-303.00]	2-1933401-5	7.62 [25.00]
6096.0-6146.8 [240.00-242.00]	2-1933401-0	6.10 [20.00]
4572.0-4622.8 [180.00-182.00]	1-1933401-5	4.57 [15.00]
3048.0-3073.4 [120.00-121.00]	1-1933401-0	3.05 [10.00]
1524.0-1543.0 [60.00-60.75]	1933401-5	1.52 [5.00]
1219.2-1231.9 [48.00-48.50]	1933401-4	1.22 [4.00]
914.4-927.1 [36.00-36.50]	1933401-3	0.91 [3.00]
609.6-622.3 [24.00-24.50]	1933401-2	0.61 [2.00]
A DIM 	PART NUMBER	REF DIM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J MCNEAL 03JAN2008	TE Connectivity	
DIMENSIONS: mm [INCHES]		CHK S JONES 03JAN2008		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S JONES 03JAN2008	NAME	
0 PLC ±		PRODUCT SPEC	CABLE ASSEMBLY, POWER TO LINE 3-3-2	
1 PLC ±		108-1234		
2 PLC ±		APPLICATION SPEC	SIZE	
3 PLC ±		114-6039	CAGE CODE	
4 PLC ±		WEIGHT	DRAWING NO	
MATERIAL		CUSTOMER DRAWING	A100779C=1933401	
FINISH		SCALE 1:1	SHEET 1 OF 1	
			REV D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity Divested:](#)

[TFP-2TT00-000B](#)