





PRODUCT NO.

10126116-XYHLF

LEAD FREE OPTION
NOTE 6, 7 & 8
NO. OF POSITIONS
SEE TABLE
PIN PLATING
BASE P/N



mat'l. code			surface	tolerance	projection	product family		
ISO 1302			ISO 1302	ISO 406	ISO 1101	HEADER		
l	tr	ec	n	o	d	r	date	tolerances unless otherwise specified
A	NEW	ZK	06/14/13	angles	linear	ISO 1101	06/14/13	INCH/MM
				0°±2'		scale 3:1		
				dr	ZK HU	06/14/13		
				enr	ZK HU	06/14/13		
				chr	RICK BIAN	06/14/13		
				app	RICK BIAN	06/14/13		
sheet	revision	A	A					
index	sheet	1	2					

title
FRICTION LATCH HEADER
SINGLE ROW, R/A

dwg no 10126116 sheet 1 of 2 size A3

type Product Customer Drawing



FCIconnect.com

Copyright FCI

PRODUCT NO.	NO.OF POS.	DIM K	DIM L	TAIL LENGTH DIM M
10126116-X03	1 X 3	.300/7.62	.200/5.08	.120/3.05
-X04	1 X 4	.400/10.16	.300/7.62	
-X05	1 X 5	.500/12.70	.400/10.16	
-X06	1 X 6	.600/15.24	.500/12.70	
-X07	1 X 7	.700/17.78	.600/15.24	
-X08	1 X 8	.800/20.32	.700/17.78	
-X09	1 X 9	.900/22.86	.800/20.32	
-X10	1 X 10	1.000/25.40	.900/22.86	
-X11	1 X 11	1.100/27.94	1.000/25.40	
-X12	1 X 12	1.200/30.48	1.100/27.94	
-X13	1 X 13	1.300/33.02	1.200/30.48	
-X14	1 X 14	1.400/35.56	1.300/33.02	
10126116-X15	1 X 15	1.500/38.10	1.400/35.56	.120/3.05
10126116-X43	1 X 3	.300/7.62	.200/5.08	.190/4.83

PIN PLATING CODES	
-1YY	30u"/.76u Au MIN. ON 50u"/1.27u Ni
-2YY	15u/.38u Au MIN. ON 50u"/1.27u Ni

NOTES:

1. MOLDING MAT'L: GLASS REINFORCED PCT OR MINRAL FILLED LCP, COLOR: BLACK
FLAME RETARDANT PER UL-94V-0
MAXIMUM OPERATING TEMPERATURE 130° C.
2. PIN MATERIAL: 3/4 HD PHOS. BRZ.
3. NO SLOTS ON 1 X 5 POSITION OR SMALLER PRODUCT. THE CENTER KEY SLOT WILL BE ON ALL HEADERS REGARDLESS OF SIZE.
4. TWO NON-CRITICAL SIDES OF PIN TIP NOT PLATED, BOTH ENDS.
5. COMPANY LOGO MAY APPEAR IN THIS AREA.
6. ADD "HLF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
7. PART NUMBERS WITH "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 20 SECONDS IN WAVE SOLDER, INFRA-RED OR VAPOR PHASE SOLDER PROCESS.

PART NUMBERS WITHOUT "H" SUFFIX WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR WAVE SOLDER PROCESS.
8. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATION AS DESCRIBED IN GS-22-008.

mat'l. code		surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADER	
ltr ecn nldr date		tolerances unless otherwise specified						title	
A		angles		linear		INCH/MM		FRICTION LATCH HEADER	
		0°±2'		XXX±.01/XXX±.03 XXX±.005/XXX±.013 XXX±.0020/XXX±.005		scale 3:1		SINGLE ROW, R/A	
		dr		ZK HU		06/14/13		dwg no	
		engr		ZK HU		06/14/13		sheet 2 of 2	
		chr		RICK BIAN		06/14/13		size	
		appd		RICK BIAN		06/14/13		A3	
sheet index		revision sheet						type Product Customer Drawing	