



- 1 ASSEMBLY MAY BE BROKEN TO THE DESIRED NUMBER OF POSITIONS.
- 2 TRUE POSITION TOLERANCE OF THE POST TIPS APPLIES WHEN,
THE HEADERS ARE HELD FLAT AGAINST THE PRINTED CIRCUIT BOARD.
- 3 0.00254–0.00504 [.000100–.000200] MATTE TIN–LEAD ON SOLDER TAIL
ALL OVER 0.00127 [.000050] NICKEL.
- 4 PARTS PACKAGED IN TUBES.
- 5 HOUSING: LCP, COLOR–BLACK.
POSTS: COPPER ALLOY.
- 6 0.00254–0.00504 [.000100–.000200] MATTE TIN ON SOLDER TAIL,
ALL OVER 0.00127 [.000050] NICKEL.
- 7 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI.



RECOMMENDED PC BOARD MOUNTING DIMENSIONS
FOR .063 [1.60] THICK PC BOARD AND
.012 [.305] STENCIL THICK.

[illegible]

7 4	3	7.21 [.284]	5.08 [.200]	2	3	4-146282-1	
	3	101.19 [3.984]	99.06 [3.906]	39	40	4-146282-0	
7 OBSOLETE	3	98.65 [3.884]	96.52 [3.800]	38	39	3-146282-9	
	3	96.11 [3.784]	93.98 [3.700]	37	38	3-146282-8	
SUP BY 8-146282-7	3	93.57 [3.684]	91.44 [3.600]	36	37	3-146282-7	
A	3	91.03 [3.584]	88.90 [3.500]	35	36	3-146282-6	
	3	88.49 [3.484]	86.36 [3.400]	34	35	3-146282-5	
	3	85.95 [3.384]	83.82 [3.300]	33	34	3-146282-4	
	3	83.41 [3.284]	81.28 [3.200]	32	33	3-146282-3	
	3	80.87 [3.184]	78.74 [3.100]	31	32	3-146282-2	
	3	78.33 [3.084]	76.20 [3.000]	30	31	3-146282-1	
	3	75.79 [2.984]	73.66 [2.900]	29	30	3-146282-0	
	3	73.25 [2.884]	71.12 [2.800]	28	29	2-146282-9	
	3	70.71 [2.784]	68.58 [2.700]	27	28	2-146282-8	
	3	68.17 [2.684]	66.04 [2.600]	26	27	2-146282-7	
	3	65.63 [2.584]	63.5 [2.500]	25	26	2-146282-6	
	3	63.09 [2.484]	60.96 [2.400]	24	25	2-146282-5	
	3	60.55 [2.384]	58.42 [2.300]	23	24	2-146282-4	
	3	58.01 [2.284]	55.88 [2.200]	22	23	2-146282-3	
	3	55.47 [2.184]	53.34 [2.100]	21	22	2-146282-2	
	3	52.93 [2.084]	50.80 [2.000]	20	21	2-146282-1	
	3	50.39 [1.984]	48.26 [1.900]	19	20	2-146282-0	
	A	3	47.85 [1.884]	45.72 [1.800]	18	19	1-146282-9
3		45.31 [1.784]	43.18 [1.700]	17	18	1-146282-8	
3		42.77 [1.684]	40.64 [1.600]	16	17	1-146282-7	
3		40.23 [1.584]	38.10 [1.500]	15	16	1-146282-6	
3		37.69 [1.484]	35.56 [1.400]	14	15	1-146282-5	
3		35.15 [1.384]	33.02 [1.300]	13	14	1-146282-4	
7 OBSOLETE		3	32.61 [1.284]	30.48 [1.200]	12	13	1-146282-3
		3	30.07 [1.184]	27.94 [1.100]	11	12	1-146282-2
		3	27.53 [1.084]	25.40 [1.000]	10	11	1-146282-1
3		24.99 [.984]	22.86 [.900]	9	10	1-146282-0	
SUP BY 5-146282-9	3	22.45 [.884]	20.32 [.800]	8	9	146282-9	
SUP BY 5-146282-8	3	19.91 [.784]	17.78 [.700]	7	8	146282-8	
SUP BY 5-146282-7	3	17.37 [.684]	15.24 [.600]	6	7	146282-7	
SUP BY 5-146282-6	3	14.83 [.584]	12.70 [.500]	5	6	146282-6	
SUP BY 5-146282-5	3	12.29 [.484]	10.16 [.400]	4	5	146282-5	
SUP BY 5-146282-4	3	9.75 [.384]	7.62 [.300]	3	4	146282-4	
A	3	7.21 [.284]	5.08 [.200]	2	3	146282-3	
	3	4.67 [.184]	2.54 [.100]	1	2	146282-2	
	3	2.13 [.084]	- [-]	0	1	146282-1	
	PLATING	C	B	A	NO. OF POSITIONS	PART NUMBER	