

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

38720-7508

Status:


Active

Overview:

Beau™ Barrier Strips

Description:

9.53mm Pitch Beau™ PCB Terminal Strip, without Mounting Ends, 8 Circuits, with Screw Clamp Washer



Documents:

3D Model

Drawing (PDF)

Product Specification PS-38710-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Terminal Blocks
Series	38720
Application	N/A
Component Type	One Piece
Overview	Beau™ Barrier Strips
Product Name	Fixed Mount Barrier
Type	Barrier Strip
UPC	800756177274

Physical	
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	27.900/g
Number of Rows	1
Orientation	Horizontal
PC Tail Length	4.80mm
PCB Retention	None
PCB Thickness - Recommended	3.18mm
Panel Mount	No
Pitch - Mating Interface	9.53mm
Pitch - Termination Interface	9.53mm
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Shrouded	Dual-Barrier
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +130°C
Wire Size AWG	12, 14, 16, 18, 20, 22
Wire Size mm²	0.50 - 2.50

Electrical	
Current - Maximum per Contact	25A
Voltage - Maximum	300V

Solder Process Data	
Lead-free Process Capability	Wave Capable (TH only)

Material Info

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

38720Series

Mates With

N/A

Old Part Number	72508-C-50
Reference - Drawing Numbers	
Product Specification	PS-38710-001
Sales Drawing	SD-38720-002

This document was generated on 09/02/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION