











APPLICABLE P.C.B DIMENSION (REF.)
適合基板寸法 (参考)

4. EX. NUMBER TO MARKED AS INDICATED.

(EX) 5 5 14 1

YEAR (END OF ONE DIGIT AT CHRISTIAN ERA)

MONTH (JAN. TO SEP. :1 TO 9, OCT. :0, NOV. :X, DEC. :Y)

DAY (TWO-DIGITS NUMBER)

EQUIPMENT No. (NUMBER OR ALPHABET)

Pin No.	A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
	GND	TX1+	TX1-	V _{BUS}	CC1	D+	D-	SBU1	V _{BUS}	RX2-	RX2+	GND
	GND	RX1+	RX1-	V _{BUS}	SBU2	D-	D+	CC2	V _{BUS}	TX2-	TX2+	GND
Pin No.	B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

	FINISH	PLATING THICKNESS
CONTACT AREA	GOLD FLASH OVER PALLADIUM-NICKEL OVER NICKEL	NICKEL: $2\text{ }\mu\text{m}$ MIN. PALLADIUM-NICKEL: $0.75\text{ }\mu\text{m}$ MIN. GOLD FLASH: $0.05\text{ }\mu\text{m}$ MIN.
SOLDER TAILS	GOLD FLASH OVER NICKEL	NICKEL: $2\text{ }\mu\text{m}$ MIN. GOLD FLASH: $0.03\text{ }\mu\text{m}$ MIN.

7	INSULATOR 2	1	HEAT RESISTING PLASTIC	COLOR:BLACK	
6	SHELL	1	STAINLESS STEEL	NICKEL PLATING	
5	GND PLATE	2	STAINLESS STEEL	NICKEL PLATING	
4	MID PLATE	1	STAINLESS STEEL	NICKEL PLATING	
3	INSULATOR 1	1	HEAT RESISTING PLASTIC	COLOR:BLACK	
2	CONTACT B	12	COPPER ALLOY	TABLE 1 	
1	CONTACT A	12	COPPER ALLOY	TABLE 1 	
符号	名称 DESCRIPTION	個数 QTY	材料 MATERIAL	仕上 FINISH	備考 REMARKS

仕様書 (SPECIFICATION)		第1版 (ORIGINAL DATE) 14/MAY/2015		尺度 (SCALE) 5:1 シリーズ (SERIES) DX07		日本航空電子工業株式会社  JAPAN AVIATION ELECTRONICS INDUSTRY, LTD.		版数 (VER.) 3
JACS-30353 JAHL-30353-1 		製図 DR. 担当 CHK. K. UEDA		名称 (TITLE) DX07B024JJ2		図面番号 (DRAWING NO.) SJ115996		
一般公差 (GENERAL TOLERANCE)		查閱 APPD. 承認 APPD. Y. SAITOU		質量 (MASS) 				
寸法 (DIMENSION)		角度 (ANGLES) ×° ± ×°×' ±						
±0.8 × ±0.4 ×× ±0.1 ××× ±		単位 (UNIT) : mm						