

PART NUMBER LIST

Microcomputer / Microcomputer Development System

PART NUMBER LIST

Microcomputer / Microcomputer Development System

Microcomputer Selection Guide 5

Microcomputer Development System Selection Guide .. 23

Microcomputer Selection Guide

Microcomputer Development System Selection Guide

Part Number Decoding

ex.

TMP 47 c r xx y z p G

Lead-free product

Package

- P: Plastic standard dual in-line package (DIP)
- N: Plastic shrink dual in-line package (SDIP)
- M, DM: Plastic small-outline package (SOP), Dry-packed product
- F, DF, U, DU: Plastic quad flat package (QFP), Dry-packed product

Automotive quality grade

- R: Grade A, -40°C to +85°C
- T: Grade A, -40°C to +125°C
- I: Grade B, -40°C to +85°C
- S: Grade B, -40°C to +125°C

Microcontroller revision

Microcontroller Subtype

ROM size

	1	2	3	4	6	8	C	H
KB	1	2	3	4	6	8	12	16

	K	M	N	P	S	U	W	Y	Z
KB	24	32	40	48	60	96	128	256	288

ROM Type

- C: Mask
- E: EEPROM
- F: Flash
- P: OTP

Microcontroller Core

- 47: 47E
- 86: 870/C
- 87: 870
- 88: 870/X
- 91: 900/L1
- 92, 94: 900/H1
- 93: 900/L
- 95: 900/H
- 96: 900

Toshiba Micro Processor

Microcomputers Selection Guide

Microcomputers

- 4-Bit Microcontrollers ● 6
- 8-Bit Microcontrollers ● 7
- 16-Bit Microcontrollers ● 12
- 32-Bit Microcontrollers ● 15

Automotive Microcomputer Selection Guide

- 8-Bit Microcontrollers for Automotive ● 16
- 16-Bit Microcontrollers for Automotive ● 18
- 32-Bit Microcontrollers for Automotive ● 18

TX System RISC Selection Guide

- 32-Bit Microcontrollers ● 19
- 32-Bit Microprocessors ● 20
- 64-Bit Microprocessors ● 20
- 64-Bit Superscalar Microprocessors ● 21

Microcomputer Selection Guide

4-Bit Microcontrollers

TLCS-47 Family: TLCS-47E Series (CMOS)

Part Number	ROM (Bytes)	RAM (Nibbles)	Minimum Instruction Execution Times (μs)	LED Driver (Ch)	LCD Driver (Ch)	SIO (Ch)	AD Converter (Ch)	Pulse Generator (Ch)	Watchdog Timer	Dual Clocks	Standby Mode	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP Version	Package
TMP47C101PG/MG	1K	64	1.3	4							●	11	2.2 to 5.5 (Note 1)	-30 to 70	TMP47P201VPG	DIP16/SOP16 (Note 5)
TMP47C102PG/MG				4					●		●	15			TMP47P202VPG/MG	DIP20/SOP20
TMP47C103NG/MG				8	1				●		●	23			TMP47P403VNG/MG	SDIP28/SOP28
TMP47C201PG/MG				4							●	11			TMP47P201VPG	DIP16/SOP16 (Note 5)
TMP47C202PG/MG				4					●		●	15			TMP47P202VPG/MG	DIP20/SOP20
TMP47C203NG/MG				8	1				●		●	23			TMP47P403VNG/MG	SDIP28/SOP28
TMP47C206PG/MG	2K	128	1.0	5			1	1		●	●	15	4.0 to 5.7	-40 to 85	TMP47P206VPG/MG	DIP20/SOP20
TMP47C241NG/MG			1.3	5	1	4		●		●	●	21	2.7 to 6.0		TMP47P241VNG/MG	SDIP28/SOP28
TMP47C243NG/MG/DMG (Note 3)				8		1	8	1	●		●	23			TMP47P443VNG/MG/DMG	SDIP28/SOP28/ SSOP30
TMP47C222NG/FG/UG (Note 3)		192	1.0 (244) (Note 2)	20	1	4	1	●	●	●	(Note 4) 20/22		2.7 to 5.5 (2.2 to 5.5) (Note 2)	-30 to 70	TMP47P422VNG/FG/UG	SDIP42/ QFP44 (14 x 14 mm)/ LQFP44 (10 x 10 mm)
TMP47C422NG/FG/UG (Note 3)	4K	256		20	1	4	1	●	●	●						
TMP47C443NG/MG/DMG (Note 3)				8		1	8	1	●		●	23				

Note 1: When CR oscillation is used (2.7 V to 5.5 V when a resonator is used)

Note 2: Numbers in parentheses indicate the minimum instruction execution time and power supply voltage when operating with the slower clock.

Note 3: Contains the CPU core for the 470 Series.

Note 4: 20 for SDIP; 22 for QFP

Note 5: An OTP version is available only in DIP16.

◆ Not recommended for automotive applications.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

8-Bit Microcontrollers

TLCS-870 Family: TLCS-870/C Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 4)	Flash Version	LED Driver (Ch)	VFT Driver (fluor. tube) (Ch)	SEI (Ch)	SIO (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	16-Bit Timer/Counter (Ch)	10-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Program Patch Logic	Watchdog Timer	Dual Clocks	Clock Gear	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP/Flash Version	Package
TMP86P202PG/MG	2K	128	0.50		2				4				2	●				14	3.3 to 5.5		—	DIP20/SOP20
TMP86P203PG/MG					2				4				2	●								
TMP86C407MG/NG			(1)0.25/122 (2)0.50/122		8		1	(Note2) 1	6		1		2	●	●			22	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP86P807MG/NG TMP86F807MG/NG	SOP28/SDIP28
TMP86C408DMG/NG	4K				8		1	(Note2) 1	6		1		2	●	●			24			TMP86P808DMG/NG TMP86F808DMG/NG	SSOP30/SDIP30
TMP86C420UG/FG			(1)0.25/122 (2)0.50/122 (3)0.95/122		4	32		1	8		1		2	●	●			39	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86P820UG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)
TMP86C807MG/NG					8		1	(Note2) 1	6		1		2	●	●			22			TMP86P807MG/NG TMP86F807MG/NG	SOP28/SDIP28
TMP86F807MG/NG		256	(1)0.25/122 (2)0.50/122		●																	
TMP86C808DMG/NG					8		1	(Note2) 1	6		1		2	●	●			24	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP86P808DMG/NG TMP86F808DMG/NG	SSOP30/SDIP30
TMP86F808DMG/NG					●																	
TMP86C809NG	**				8		1		6		1		2	●	●			26			TMP86FH09NG	SDIP32
TMP86C820UG/FG			(1)0.25/122 (2)0.50/122 (3)0.95/122		4	32		1	8		1		2	●	●			39	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86P820UG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)
TMP86C845UG	8K		0.50/122		19			1	8				2	●	●			35	2.7 to 5.5		TMP86PM47AUG TMP86PH47UG TMP86FH47AUG/DUG	LQFP44 (10 x 10 mm)
TMP86C822UG	◇				3	23		1 (Note2) 1	4		1		2	●	●			33			TMP86PH22UG	◇
TMP86C829BUG/FG					4	32		1	8		1		4	●	●			39			TMP86PM29BUG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)
TMP86C846NG			(1)0.25/122 (2)0.50/122 (3)0.95/122		19			1 (Note2) 1	8		1		2	●	●			33	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PH46NG TMP86PM46NG TMP86FH46ANG	SDIP42
TMP86C847UG					19			1 (Note2) 1	8		1		2	●	●			35		-40 to 85	TMP86PM47AUG TMP86PH47UG TMP86FH47AUG/DUG	LQFP44 (10 x 10 mm)
TMP86CH06NG/UG					8			(Note3) 2			1		2	●	●	●					TMP86PH06NG/UG	SDIP42/ LQFP44 (10 x 10 mm)
TMP86CH06AUG	◇																				TMP86PH06UG	LQFP44 (10 x 10 mm)
TMP86CH09NG	**				8		1		6		1		2	●	●			26			TMP86FH09NG	SDIP32
TMP86FH09NG	△ **				●	8			6		1		2	●	●						—	
TMP86CH12MG	**		(1)0.25/122 (2)0.50/122		8			1 (Note2) 1	8		1		2	●	●			24	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP86FH12MG	△
TMP86FH12MG	△				●	8		1 (Note2) 1	8		1		2	●	●						—	SSOP30
TMP86CH21UG/FG		512			4	32		1	8		1		4	●	●			39			TMP86PM29BUG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)
TMP86CH21AUG	◇		(1)0.25/122 (2)0.50/122 (3)0.95/122																(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5			LQFP64 (10 x 10 mm)
TMP86CH22UG	◇				3	23		1 (Note2) 1	4		1		2	●	●						TMP86PH22UG	◇
TMP86CH46ANG	◇	16K			19			1 (Note2) 1	8		1		2	●	●			33			TMP86PH46NG TMP86PM46NG TMP86FH46ANG	SDIP42
TMP86FH46ANG	△		(1)0.25/122 (2)0.50/122		●														(1)4.5 to 5.5 (2)2.7 to 5.5		—	
TMP86CH47AUG	◇		(1)0.25/122 (2)0.50/122 (3)0.95/122		19			1 (Note2) 1	8		1		2	●	●			35	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM47AUG TMP86PH47UG TMP86FH47AUG/DUG	LQFP44 (10 x 10 mm)
TMP86FH47AUG/DUG	△		(1)0.25/122 (2)0.50/122		●														(1)4.5 to 5.5 (2)2.7 to 5.5		—	LQFP44 (10 x 10 mm)/ LQFP48 (7 x 7 mm)
TMP86CH49UG/FG/NG			(1)0.25/122 (2)0.50/122 (3)0.95/122		13			2 (Note2) 2	1	16	2		4	●	●			56	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM49UG/FG/NG TMP86FS49AUG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)/ SDIP64
TMP86CH72FG		1K	(1)0.25/122 (2)0.50/122			32		1 (Note2) 1	6		1		2	●	●	●		54	(1)4.5 to 5.5 (2)2.7 to 5.5	-30 to 70	TMP86PM72FG	** QFP64 (14 x 14 mm)

◇: Guaranteed over the ambient temperature (Topr) range of -20 to 85°C at 1.8 V ≤ VDD < 2.0 V.

△: Guaranteed over the ambient temperature (Topr) range of -20 to 85°C at 2.7 V ≤ VDD < 3.0 V.

Note 1: Configurable as UART via software.

Note 2: UART only

Note 3: Either one or both of UART channels can be configured as SIO channels via software.

Note 4: Minimum instruction execution times (1) to (3) correspond to power supply voltages (1) to (3).

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 3)	Flash Version	LED Driver (Ch)	V/F Driver (flux tube) (Ch)	SEI (Ch)	SIO (Ch)	UART (Ch)	SI/UART (Ch) (Note 1)	I ² C (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	8-Bit DA Converter (Ch)	18-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	10-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Program Patch Logic	Multiply-Accumulate (MAC)	Watchdog Timer	Dual Clocks	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP/Flash Version	Package
TMP86CH29BUG/FG	16K	1.5K	(1)0.25/122 (2)0.50/122 (3)0.95/122		4	32				1		8		1		4			●	●		39	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5	−40 to 85	TMP86PM29BUG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)	
TMP86CK74AFG	24K	1K	(1)0.25/122 (2)0.50/122		2	37		1			8			2	2				●	●		70	(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70	TMP86PM74AFG	QFP80 (14 x 20 mm)	
TMP86CM23AUG ◇			(1)0.25/122 (2)0.50/122 (3)0.95/122		5	32		1	1			8		1		4			●	●	●	48	(1)3.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM23UG	LQFP64 (10 x 10 mm)	
TMP86CM29BUG/FG		1.5K			4	32				1		8		1		4			●	●		39	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM29BUG/FG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)	
TMP86FM29UG/FG					●	4	32			1		8		1		4			●	●			(1)2.7 to 3.6 (2)1.8 to 3.6		—		
TMP86FM26UG			(1)0.25/122 (2)0.50/122		●	23	32		1	1				1		4			●	●	●	41	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5	−40 to 85	TMP86PS27FG TMP86FS27FG	QFP80 (14 x 20 mm)	
TMP86CM27FG					8	40		1	1			8			1	2			●	●		55	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP86PM46NG	SDIP42	
TMP86CM46ANG					19			1	1			8		1	2				●	●		33			TMP86PM47AUG	LQFP44 (10 x 10 mm)	
TMP86CM47AUG		1K	(1)0.25/122 (2)0.50/122 (3)0.95/122		19			1	1			8		1	2				●	●		35	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM49UG/FG/NG TMP86FS49AUG/FG Δ	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)/ SDIP64	
TMP86CM49UG/FG/NG	32K				13		2	2		1	16			2	4				●	●		56					
TMP86CM72FG			(1)0.25/122 (2)0.50/122			32		1	1		1	6			1	2			●	●	●	54	(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70	TMP86PM72FG	** QFP64 (14 x 14 mm)	
TMP86CM25FG			(1)0.25/122 (2)0.50/122 (3)0.95/122		4	Note2 60		1		1		8		1		4			●	●		42	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PS25FG	QFP100 (14 x 20 mm)	
TMP86CM25AFG					●	4	Note2 60		1		1	8		1		4			●	●			(1)2.7 to 3.6 (2)1.8 to 3.6	−40 to 85	TMP86FM25FG		
TMP86FM48UG/FG		2K	(1)0.25/122 (2)0.50/122		●	11			1	1	1	16		2	2				●	●		54			—	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)	
TMP86CM74AFG					2	37	1				8			2	2				●	●		70	(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70	TMP86PM74AFG	QFP80 (14 x 20 mm)	
TMP86CP23AUG ◇			(1)0.25/122 (2)0.50/122 (3)0.95/122		5	32		1	1			8		1		4			●	●	●	48	(1)3.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PS23UG TMP86FS23UG Δ	LQFP64 (10 x 10 mm)	
TMP86FP24FG	48K		(1)0.25/122 (2)0.50/122		●	12	24		1	1		8		2	2				●	●	●	54	(1)2.7 to 3.6 (2)1.8 to 3.6	−40 to 85	—	LQFP80 (12 x 12 mm)	
TMP86CP27AFG		1K	(1)0.25/122 (2)0.50/122		8	40		1	1			8			1	2			●	●		55	(1)4.5 to 5.5 (2)2.7 to 5.5	−40 to 70	TMP86PS27FG TMP86FS27FG	QFP80 (14 x 20 mm)	
TMP86FS27FG					●	8	40		1	1		8		1	2				●	●	●				—		
TMP86CS44UG					19			1	1			8		1	2				●	●	●	35			TMP86PS44UG	LQFP44 (10 x 10 mm)	
TMP86FS23UG Δ					●	5	32		1	1		8		1	4				●	●	●	48			—	LQFP64 (10 x 10 mm)	
TMP86CS25AFG ◇					4	Note2 60		1		1		8		1		4			●	●	●	42	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PS25FG	QFP100 (14 x 20 mm)	
TMP86CS25ADFG ◇						40			1	1		8		2	4				●	●	●	62	(1)4.0 to 5.5 (2)2.7 to 5.5	−40 to 85	TMP86FS28FG/DFG Δ	QFP80 (14 x 20 mm)/ LQFP80 (12 x 12 mm)	
TMP86FS28FG/DFG Δ **	60K	2K	(1)0.25/122 (2)0.50/122 (3)0.95/122		●	40			1	1		8		2	4				●	●	●				—		
TMP86CS49UG/FG ◇					13		2	2		1	16			2	4				●	●		56	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86FS49AUG/FG Δ	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)	
TMP86FS49AUG/FG Δ					●	13		2	2		1	16		2	4				●	●					—		
TMP86CS64AFG			(1)0.25/122 (2)0.50/122		16			2	1			16		2	4				●	●		91	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP86PS64FG TMP86FS64FG Δ	QFP100 (14 x 20 mm)	
TMP86FS64FG Δ					●	16		2	1			16		2	4				●	●					—		

◇: Guaranteed over the ambient temperature (Topr) range of –20 to 85°C at 1.8 V ≤ VDD < 2.0 V.

Δ: Guaranteed over the ambient temperature (Topr) range of –20 to 85°C at 2.7 V ≤ VDD < 3.0 V.

Note 1: Configurable as UART via software.

Note 2: Up to 960 LCD segments (60 seg. x 16 com.)

Note 3: Minimum instruction execution times (1) to (3) correspond to power supply voltages (1) to (3).

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

TLCS-870 Family: TLCS-870 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 3)	LED Driver (Ch)	LCD Driver (Ch)	V/F/T Driver (fluc. tube) (Ch)	SIO (Ch)	UART (Ch)	I ² C (Ch) (Note 1)	High-Speed Serial Output (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	AD Converter Input (Ch)	18-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Watchdog Timer	Dual Clocks	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP Version	Package		
TMP87C405AMG	4K	256	(1)0.50	6										2		●	●		22	(1)4.5 to 5.5		TMP87P808MG	SOP28		
TMP87C408MG/NG/DMG (Note 2)			(2)0.95	6		1			6					2		●	●			(2)2.7 to 5.5		TMP87P808NG/MG	SOP28/SDIP28/ SSOP30		
TMP87C408LMG/NG			0.95	6		1			6					2		●	●			1.8 to 4.0		TMP87P808LMG/NG	SOP28/SDIP28		
TMP87C409BMG/NG			(1)0.50 (2)0.95	6				1		8			1	2		●				(1)4.5 to 5.5 (2)2.2 to 5.5		TMP87P809MG/NG			
TMP87C446NG		512	(1)0.50/122	8		1		1	8				2	2	●	●			35			-30 to 70	TMP87PH46NG	SDIP42	
TMP87C447UG			(2)0.95/122	8		1		1					2	2	●	●			37	(1)4.5 to 5.5 (2)2.7 to 5.5			TMP87PH47UG	QFP44 (10 x 10 mm)	
TMP87C807UG				8		1		1						2	2	●	●								
TMP87C808MG/NG			(1)0.50 (2)0.95	6		1			6				2		●		●		22				TMP87P808MG/NG	SOP28/SDIP28	
TMP87C808LMG/NG			0.95	6		1			6				2		●	●				1.8 to 4.0		TMP87P808LMG/NG			
TMP87C809BMG/NG			(1)0.50 (2)0.95	6				1		8			1	2		●				(1)4.5 to 5.5 (2)2.2 to 5.5		TMP87P809MG/NG			
TMP87C840NG/FG			8K		(1)0.50/122 (2)0.95/122	8		2			8				2	2	●	●				(1)4.5 to 6.0 (2)2.7 to 6.0		TMP87PH40ANG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP87C841NG/FG/UG		8				2				16			2	2		●	●			56		-40 to 85	TMP87PM41NG/FG/UG	SDIP64/ QFP64 (14 x 20 mm)/ LQFP64 (10 x 10 mm)	
TMP87C814NG/FG			(1)0.50/122 (2)122		16	1			8				2	2	●	●			55	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP87PM14NG/FG	SDIP64/ QFP64 (14 x 20 mm)		
TMP87C846NG			(1)0.50/122	8		1		1	8				2	2	●	●			35				TMP87PH46NG	SDIP42	
TMP87C847UG			(2)0.95/122	8		1		1	8					2	2	●	●			37		-30 to 70	TMP87PH47UG	QFP44 (10 x 10 mm)	
TMP87C847LUG			0.95/122	8		1		1	8					2	2	●	●				1.8 to 4.0		TMP87PH47LUG		
TMP87CC40NG/FG	12K		(1)0.50/122 (2)0.95/122	8		2			8				2	2	●	●				(1)4.5 to 6.0 (2)2.7 to 6.0		TMP87PH40ANG/FG	SDIP64/ QFP64 (14 x 20 mm)		
TMP87CC41NG/FG/UG				8		2				16				2	2	●	●			56	(1)4.5 to 5.5		-40 to 85	TMP87PM41NG/FG/UG	SDIP64/ QFP64 (14 x 20 mm)/ LQFP64 (10 x 10 mm)
TMP87CC78FG			(1)0.50/122 (2)122		40	2			8					2	2	●	●			89	(2)2.7 to 5.5		TMP87PM78FG	QFP100 (14 x 20 mm)	
TMP87CH14NG/FG		512	(1)0.50/122 (2)122		16	1			8					2	2	●	●			55		-30 to 70	TMP87PM14NG/FG	SDIP64/ QFP64 (14 x 20 mm)	
TMP87CH40NG/FG				8		2			8					2	2	●	●				(1)4.5 to 6.0 (2)2.7 to 6.0		TMP87PH40ANG/FG	SDIP64/ QFP64 (14 x 20 mm)	
TMP87CH41NG/FG/UG			(1)0.50/122 (2)0.95/122	8		2				16				2	2	●	●			56	(1)4.5 to 5.5 (2)2.7 to 5.5		-40 to 85	TMP87PM41NG/FG/UG	SDIP64/ QFP64 (14 x 20 mm)/ LQFP64 (10 x 10 mm)
TMP87CH46NG	16K			8		1		1	8				2	2	●	●			35				TMP87PH46NG	SDIP42	
TMP87CH47UG				8		1		1	8					2	2	●	●			37		-30 to 70	TMP87PH47UG	QFP44 (10 x 10 mm)	
TMP87CH47LUG			0.95/122	8		1		1	8					2	2	●	●				1.8 to 4.0		TMP87PH47LUG		
TMP87CH48UG/DFG			(1)0.50/122 (2)0.95/122	8			1	1		16				2	2	●	●		56			-40 to 85	TMP87PH48UG/DFG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)	
TMP87CH74AFG			(1)0.50/122 (2)122	16	37	1		1	12					2	2	●	●			71				TMP87PM74FG	QFP80 (14 x 20 mm)
TMP87CH75FG				16	51	1		1	16					2	2	●	●			89	(1)4.5 to 5.5 (2)2.7 to 5.5		TMP87PM75FG	QFP100 (14 x 20 mm)	
TMP87CH78FG					40	2			8					2	2	●	●					-30 to 70	TMP87PM78FG		
TMP87CH21CFG/DFG		1K	(1)0.50/122 (2)0.95/122	1	32		2		8				2	2	●	●			52			-30 to 70	TMP87PP21FG/DFG	QFP80 (14 x 20 mm)/ LQFP80 (12 x 12 mm)	
TMP87CH29NG/UG				3	24		1		5		1		4	●	●					43				TMP87PM29NG/UG	SDIP64/ LQFP64 (10 x 10 mm)

Note 1: Either I²C bus or SIO module can be selected via software.
 Note 2: A 125°C version is available for the TMP87C408DM. For further information, please contact your nearest Toshiba sales representative.
 Note 3: Minimum instruction execution times (1) to (2) correspond to power supply voltages (1) to (2).
 ◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 2)	LED Driver (Ch)	V-F Driver (fluor. tube) (Ch)	SIO (Ch)	UART (Ch)	I ² C (Ch) (Note 1)	High-Speed Serial Output (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	AD Converter Input (Ch)	18-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Watchdog Timer	Dual Clocks	Clock Gear	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP Version	Package
TMP87CK14NG/FG			(1)0.50/122 (2)122		16	1			8				2	2	•	•		55				TMP87PM14NG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP87CK29NG/UG				3	24		1		5				1		4	•	•	43		−30 to 70		TMP87PM29NG/UG	SDIP64/ LQFP64 (10 x 10 mm)
TMP87CK40ANG/FG	24K	1K	(1)0.50/122 (2)0.95/122	8		2			8				2	2	•	•						TMP87PM40ANG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP87CK41NG/FG/UG				8		2				16			2	2	•	•		56		−40 to 85		TMP87PM41NG/FG/UG	SDIP64/ QFP64 (14 x 20 mm)/ LQFP64 (10 x 10 mm)
TMP87CK78FG			(1)0.50/122 (2)122		40	2			8				2	2	•	•		89				TMP87PM78FG	QFP100 (14 x 20 mm)
TMP87CM70BFG		512	(1)0.50/122 (2)0.95/122		16	1		1			6		2	2	•	•		73		(1)4.5 to 5.5 (2)2.7 to 5.5		TMP87PM70FG	QFP80 (14 x 20 mm)
TMP87CM14NG/FG			(1)0.50/122 (2)122		16	1			8				2	2	•	•		55				TMP87PM14NG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP87CM21CFG/DFG				1	32	2			8				2	2	•	•		52		−30 to 70		TMP87PP21FG/DFG	QFP80 (14 x 20 mm)/ LQFP80 (12 x 12 mm)
TMP87CM23AFG				1	40	2			8				2	2	•	•		70				TMP87PP23FG	QFP100 (14 x 20 mm)
TMP87CM29NG/UG				3	24		1		5				1		4	•	•	43				TMP87PM29NG/UG	SDIP64/ LQFP64 (10 x 10 mm)
TMP87CM40ANG/FG			(1)0.50/122 (2)0.95/122	8		2			8				2	2	•	•						TMP87PM40ANG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP87CM41NG/FG/UG	32K	1K	(2)0.95/122	8		2				16			2	2	•	•		56			−40 to 85	TMP87PM41NG/FG/UG	SDIP64/ QFP64 (14 x 20 mm)/ LQFP64 (10 x 10 mm)
TMP87CM48UG/DFG				8			1	1		16			2	2	•	•						TMP87PM48UG/DFG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm)
TMP87CM53FG				7		1	1		8				2	2	•	•	•	72	(1)4.5 to 5.5 (2)2.2 to 5.5	−30 to 60		TMP87PM53FG	QFP80 (14 x 20 mm)
TMP87CM74AFG				16	37	1	1	1	12				2	2	•	•		71				TMP87PM74FG	QFP80 (14 x 20 mm)
TMP87CM75FG			(1)0.50/122 (2)122	16	51	1	1	1	16				2	2	•	•			(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70		TMP87PM75FG	QFP100 (14 x 20 mm)
TMP87CM78FG					40	2			8				2	2	•	•		89				TMP87PM78FG	
TMP87CM24AFG				1	40	2			8				2	2	•	•		69	(1)4.5 to 5.5 (2)2.2 to 5.5	−10 to 70		TMP87PP24AFG	LQFP100 (14 x 14 mm)
TMP87CP21CFG/DFG			(1)0.50/122 (2)0.95/122	1	32	2			8				2	2	•	•		52	(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70		TMP87PP21FG/DFG	QFP80 (14 x 20 mm)/ LQFP80 (12 x 12 mm)
TMP87CP23FG	48K	2K	(2)0.95/122	1	40	2			8				2	2	•	•		70				TMP87PP23FG	QFP100 (14 x 20 mm)
TMP87CP24AFG				1	40	2			8				2	2	•	•		69	(1)4.5 to 5.5 (2)2.2 to 5.5	−10 to 70		TMP87PP24AFG	LQFP100 (14 x 14 mm)
TMP87CS68DFG				7		1	1		8				2	2	•	•	•	72				TMP87PS68DFG	LQFP80 (12 x 12 mm)
TMP87CS71BFG	60K		(1)0.50/122 (2)122		16	1		1			6		2	2	•	•		73	(1)4.5 to 5.5 (2)2.7 to 5.5	−30 to 70		TMP87PS71AFG	QFP80 (14 x 20 mm)

Note 1: Either I²C bus or SIO module can be selected via software.

Note 2: Minimum instruction execution times (1) to (2) correspond to power supply voltages (1) to (2).

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

TLCS-870 Family: TLCS-870/X Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 4)	Flash Version	VFT Driver (fluc. tube) (Ch)	SIO (Ch)	UART (Ch)	I ² C (Ch) (Note 1)	PWM (Ch)	10-Bit AD Converter (Ch)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Motor Controller (Ch)	Remote Control Preprocessor	Watchdog Timer	Dual Clocks	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP/Flash Version	Package
TMP88CH40NG/MG	16K	512	0.20		14	(Note 2) 1	(Note 2) 1			4	1	2	1	●		19			-40 to 85	TMP88PH40NG/MG	SDIP28/SOP28
TMP88CH41NG/UG					16	(Note 2) 1	(Note 2) 1			8	2	2	1	●				4.5 to 5.5		TMP88PH41NG/UG	SDIP42/ LQFP44 (10 x 10 mm)
TMP88CM38ANG	32K	1.5K	0.25		4			(Note 3) 1	10	6	2	2	●	●		33				TMP88PS38NG	SDIP42/ QFP44 (14 x 14 mm)
TMP88CM38AF (Note 5)								(Note 3) 1	10	6	2	2	●	●						TMP88PS38FG	
TMP88CM38BNG/FG					4			(Note 3) 1	10	6	2	2	●	●						TMP88PS38BNG/FG	
TMP88CP77FG		1K	(1)0.32/122 (2)122		53	2		1	12	3	1		●	●		88		(1)4.5 to 5.5 (2)2.7 to 5.5		TMP88PU77FG	QFP100 (14 x 20 mm)
TMP88CP34NG/FG	48K				1			(Note 3) 1	4	6	2	2	●	●						TMP88PS34NG/FG	
TMP88CP38ANG					4			(Note 3) 1	10	6	2	2	●	●					-30 to 70	TMP88PS38NG	
TMP88CP38AF (Note 5)		1.5K			4			(Note 3) 1	10	6	2	2	●	●						TMP88PS38FG	
TMP88CP38BNG/FG			0.25		4			(Note 3) 1	10	6	2	2	●	●		33				TMP88PS38BNG/FG	SDIP42/ QFP44 (14 x 14 mm)
TMP88CS34NG/FG					1			(Note 3) 1	4	6	2	2	●	●				4.5 to 5.5		TMP88PS34NG/FG	
TMP88CS38NG/FG					4			(Note 3) 1	10	6	2	2	●	●						TMP88PS38NG/FG	
TMP88CS38BNG/FG	64K				4			(Note 3) 1	10	6	2	2	●	●						TMP88PS38BNG/FG	
TMP88CS42NG/FG		2K	0.20		24	1	1	2	16	2	4	2	●			55			-40 to 85	TMP88PS42NG/FG	SDIP64/ QFP64 (14 x 20 mm)
TMP88CS43FG					24	1	1	2	16	2	4	2	●			71				TMP88PS43FG	QFP80 (14 x 20 mm)
TMP88CS77FG					53	2	1	12	3	1			●	●		88				TMP88PU77FG	QFP100 (14 x 20 mm)
TMP88CU74FG	96K		(1)0.32/122 (2)122		37	1	1	12	2	2			●	●		71		(1)4.5 to 5.5 (2)2.7 to 5.5	-30 to 70	TMP88PU74FG	QFP80 (14 x 20 mm)
TMP88CU77FG		3K			53	2	1	12	3	1			●	●		88				TMP88PU77FG	
TMP88CW44FG	**				24	1	2	2	16	2	4	2	●			91				TMP88FW44FG	** QFP100 (14 x 20 mm)
TMP88FW44FG	**	120K	4K	0.20	● 24	1	2	2	16	2	4	2	●			91		4.5 to 5.5	-40 to 85	—	
TMP88CW45FG	**				24	1	2	2	16	2	4	2	●			71				TMP88FW45FG	** QFP80 (14 x 20 mm)
TMP88FW45FG	**				● 24	1	2	2	16	2	4	2	●			71				—	

Note 1: Either I²C bus or SIO module can be selected via software.

Note 2: Cannot be used at the same time because their I/O pins are multiplexed.

Note 3: Has two selectable SDA/SCL pairs.

Note 4: Minimum instruction execution times (1) to (2) correspond to power supply voltages (1) to (2).

Note 5: Although the part number does not have a (G) suffix, this product is Lead(Pb)-Free.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

16-Bit Microcontrollers

TLCS-900 Family TLCS-900/L1 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)			Flash Version	SIO (Ch)	SIO/UART (Ch)	CAN (8 Mailboxes) (Ch)	I ² C Bus/SIO (Ch)	Memory Bank Controller DRAM Controller (Ch)	10-Bit AD Converter (Ch)	LCD Controller	LCD Driver (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	32-kHz Timer (to SW-RTC)	16-Bit PWM Timer (Ch)	8-Bit PWM Timer (Ch)	HW-RTC	CS/WAIT Controller (Ch)	PDC (Ch)	Watchdog Timer	Dual Clocks	Clock Gear	I/O Port (Pins)	Operating Temperature (°C)	OTP/Flash Version	Package
			5V±10%	3V±10%	2V±10%																								
TMP91C016FG				148	400		1			1	●	●	●	●	4		●		4		●	●	●	●	31	-40 to 85		LQFP100 (14 x 14 mm)	
TMP91C025FG		NA	—	(Note 5) 111			2				●	4	●		4		●		4		●	●	●	●	38				
TMP91C219FG		2K	(Note 1) 111	—	—		1					4			6	1			4		●		●		54	-20 to 70			
TMP91C630FG	NA	6K		111			2					8			6	1			4		●	●	●	●					
TMP91C815FG			—	148	400		2		1		●	8	●		4		●		4		●	●	●	●	61	-40 to 85	—	TQFP128 (14 x 14 mm)	
TMP91C824FG				122			2		1		●	8			4		●		4		●	●	●	●	35			LQFP100 (14 x 14 mm)	
TMP91C829FG		8K	(Note 1) 111	—			2					8			6	1			4		●		●	●	54	-20 to 70		LQFP100 (14 x 14 mm)	
TMP91C820AFG	8K			(Note 4) 111			3		1	1	●	8	●		4	1		●		4		●	●	●	77			LQFP144 (16 x 16 mm)	
TMP91CK27UG	24K	1K		148	400		2		1			4			6	1	●		3		●	●	●	●	53		TMP91FY27UG	LQFP64 (10 x 10 mm)	
TMP91CP27UG	48K	4K	—				2		1			4			6	1	●		3		●	●	●	●	53		TMP91FY27UG	LQFP64 (10 x 10 mm)	
TMP91CU10FG		3K		296	—		3					8			8	2			3		●	●	●	●	80	-40 to 85	TMP91PW10FG	LQFP100 (14 x 14 mm)	
TMP91CU27UG		10K		148	400		2		1			4			6	1	●		3		●	●	●	●	53		TMP91FY27UG	LQFP64 (10 x 10 mm)	
TMP91CW11FG			160	320	—		3	2	1			8			2	2	●	2	4		●	●	●	●	79		TMP91PW11FG	LQFP100 (14 x 14 mm)	
TMP91CW12FG				250			2		1			8			8	2	●		4		●	●	●	●	81		TMP91PW12FG		
TMP91CW12AFG			—	148	400		2		1			8			8	2	●		4		●	●	●	●			TMP91FY42FG	**	
TMP91CW18AFG		4K	160	—			(Note 3) 1	(Note 2) 3				12			8	1				●		●	●	●	62	-20 to 70	TMP91PW18AFG	QFP80 (14 x 20 mm)	
TMP91CW40FG **							4					4		40	4	3	●				●	●			61	-40 to 85	TMP91FW40FG **		
TMP91FW40FG **	128K			148		●	4					4		40	4	3	●				●	●					—	LQFP100 (14 x 14 mm)	
TMP91CW28FG					(Note 6) 400		1		2			8			4	2			4		●		●	●	80	-20 to 70	TMP91FY28FG **		
TMP91CW60FG/DFG ++							3		2			16			6	5	●		4		●	●	●	●	83	-40 to 85	TMP91FW60FG/DFG **	LQFP100 (14 x 14 mm)	
TMP91FW60FG/DFG **		8K	200	—	—	●	3		2			16			6	5	●		4		●	●	●	●	83	-40 to 85	—	QFP100 (14 x 20 mm)	
TMP91CY28FG					(Note 6) 400		1		2			8			4	2			4		●	●	●	●	80	-20 to 70	TMP91FY28FG **	LQFP100 (14 x 14 mm)	
TMP91FY28FG **					400	●	1		2			8			4	2			4		●	●	●	●	80		—		
TMP91CY22FG					400		2		1			8			8	2	●		4		●	●	●	●	81		TMP91FY42FG **		
TMP91FY42FG **	256K	16K	—	148		●	2		1			8			8	2	●		4		●	●	●	●	81	-40 to 85		LQFP100 (14 x 14 mm)	
TMP91FY27UG				(Note 7) 148		●	2		1			4			6	1	●		3		●	●	●	●	53	-20 to 70	—	LQFP64 (10 x 10 mm)	

Note 1: 3.0 V to 3.6 V internally; 4.75 V to 5.25 V for input/output interface

Note 2: I²C/SIO selectable: 1 channel, I²C: 2 channels

Note 3: UART only

Note 4: Operating voltage is 3.0 V to 3.6 V.

Note 5: The relationships between voltage ranges and minimum instruction execution times are as follows:

2.4 V to 3.6 V: 250 ns at 16 MHz

2.7 V to 3.6 V: 148 ns at 27 MHz

3.0 V to 3.6 V: 111 ns at 36 MHz

Note 6: 1.8 V to 2.6 V

Note 7: Operating voltage is 2.85 V to 3.3 V.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

++ : Being planned

TLCS-900 Family: TLCS-900/L Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)		SIO (Ch)	I ² C Bus/SIO (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	LCD Driver (Ch)	VFT Driver (fluor. tube) (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	32-kHz Timer (for S/W RTC)	Timebase Counter	Motor Pattern Generator (Ch)	8-Bit PWM Timer (Ch)	14-Bit PWM Timer (Ch)	CS/WAIT Controller (Ch)	VCR Servo Controller	Watchdog Timer	Dual Clocks	Clock Gear	I/O Port (Pins)	Operating Temperature (°C)	OTP Version	Package
TMP93CS41DFG	NA	2K			2			8			2	2			2	2		3		•	•	•	61			LQFP100 (14 x 14 mm)
TMP93CS45FG				320	2	1	8				4	2								•	•	•	44		—	LQFP80 (12 x 12 mm)
TMP93CW41DFG		4K			2		8				2	2			2	2		3		•	•	•	61			LQFP100 (14 x 14 mm)
TMP93CM40DFG	32K			400	2		8				2	2			2	2		3		•	•	•	79		TMP93PS40DFG	LQFP100 (14 x 14 mm)
TMP93CS20FG					2	1	8	•			4	4	•							•	•	•	88	-40 to 85	TMP93PW20AFG	LQFP144 (16 x 16 mm)
TMP93CS32FG			200		2		6				4	2								•	•	•	49		TMP93PW32FG	QFP64 (14 x 14 mm)
TMP93CS36UG	64K	2K		320	2		4				4	2								•	•	•	33		—	LQFP44 (10 x 10 mm)
TMP93CS40DFG					2		8				2	2			2	2		3		•	•	•	79		TMP93PS40DFG	LQFP100 (14 x 14 mm)
TMP93CS42ADFG				—	2		5				2	2				2		3		•	•	•	80		TMP93PS42ADFG	LQFP100 (14 x 14 mm)
TMP93CS44FG				320	2	1	8				4	2								•	•	•	62		TMP93PS44FG	LQFP80 (12 x 12 mm)
TMP93CT76FG	72K		250	—		1	1	10		•	1	5	•	•		1	3		•	•	•	•	85	-20 to 70	TMP93PW76FG	QFP100 (14 x 20 mm)
TMP93CU76FG		2.5K				1	1	10		•	1	5	•	•		1	3		•	•	•	•				
TMP93CU44DFG (Note 1)	96K	3K	200	320	2	1	8				4	2								•	•	•	62	-40 to 85	TMP93PW44ADFG (Note 1)	QFP80 (14 x 20 mm)
TMP93CW76FG		2.5K	250	—		1	1	10		•	1	5	•	•		1	3		•	•	•	•	85	-20 to 70	TMP93PW76FG	QFP100 (14 x 20 mm)
TMP93CW40DFG	128K				2		8				2	2			2	2		3		•	•	•	79		TMP93PW40DFG	LQFP100 (14 x 14 mm)
TMP93CW44DFG (Note 1)		4K	200	320	2	1	8				4	2								•	•	•	62	-40 to 85	TMP93PW44ADFG (Note 1)	QFP80 (14 x 20 mm)
TMP93CW46AFG					5		8				2	2			2		3		•	•	•	•	79		TMP93PW46AFG	LQFP100 (14 x 14 mm)
TMP93CF77FG	160K		250	—		1	1	10		•	1	5	•	•		1	3		•	•	•	•	85	-20 to 70	TMP93PF76FG	QFP100 (14 x 20 mm)
TMP93CF76FG	192K					1	1	10		•	1	5	•	•		1	3		•	•	•	•				

Note 1: Operating voltage of OTP-version TMP93PW44ADFG is 4.5 V to 5.5 V.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

TLCS-900 Family: TLCS-900/H Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)		CAN (16 Mailboxes) (Ch)	SEI (Ch)	SI/UART (Ch)	DRAM Controller (Ch)	6-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	8-Bit DA Converter (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	Motor Pattern Generator (Ch)	8-Bit PWM Timer (Ch)	CS/MAT Controller (Ch)	Watchdog Timer	I/O Port (Pins)	Operating Temperature (°C)	OTP Version	Package
			5V±10%	3V±10%																	
TMP95C001FG	NA	NA		320												4	0				QFP64 (14 x 14 mm)
TMP95C061BDFG				—			2	1			4		4	2	2	4	●	56			LQFP100 (14 x 14 mm)
TMP95C063DFG			160			2	2		8	2	8	2	2	2	4	●	91	–20 to 70	—		LQFP144 (20 x 20 mm)
TMP95C265FG				400			3		8	2	8	2				4	●	55			
TMP95CW65FG		4K					3		8	2	8	2			4	●					
TMP95CS54FG (Note 1)	64K	2K	167	—	1	1	2		8	8	2				●			–40 to 85	TMP95PS54FG (Note 1)		
TMP95CS64FG			400		3		8	2	8	2		4	●			–20 to 70	TMP95PW64FG	LQFP100 (14 x 14 mm)			
TMP95CS66FG					1			8	2		4	●	81								
TMP95CU54AFG			96K	3K	167	—	1	1	2		8	8	2			●		–40 to 85	—		
TMP95CW54AFG	128K	4K			1	1	2		8	8	2				●						
TMP95CW64FG			160	400			3		8	2	8	2		4	●		–20 to 70	TMP95PW64FG	LQFP100 (14 x 14 mm)		

Note 1: Operating voltage is 4.7 V to 5.3 V.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

TLCS-900 Family: TLCS-900 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)		CAN (16 Mailboxes) (Ch)	SEI (Ch)	SI/UART (Ch)	DRAM Controller (Ch)	6-Bit AD Converter (Ch)	8-Bit AD Converter (Ch)	10-Bit DA Converter (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	Motor Pattern Generator (Ch)	8-Bit PWM Timer (Ch)	CS/WAIT Controller (Ch)	Watchdog Timer	I/O Port (Pins)	Operating Temperature (°C)	OTP Version	Package
TMP96C031ZFG		NA	(Note 1)	—			2	1	4			4	1	2		4	●	37	-40 to 85		QFP64 (14 x 20 mm)
TMP96C041BFG	NA						2			4		2	2	2	2	3	●	47		—	
TMP96C141BFG		1K	200				2			4		2	2	2	2	3	●			QFP80 (14 x 20 mm)	
TMP96CM40FG	32K						2			4		2	2	2	2	3	●	65		TMP96PM40FG	

Note 1: Guaranteed minimum instruction execution time is 200 ns for –20°C to 70°C, and 250 ns for –40°C to 85°C.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

32-Bit Microcontrollers

TLCS-900 Family: TLCS-900/H1 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)		Flash Version	I/O Port (Pins)	Clock Gear	Dual Clocks	Watchdog Timer	CS/WAIT Controller (Ch)	Multiply-Accumulate (MAC)	Motor Pattern Generator (Ch)	H/W RTC	32-kHz Timer (for S/W RTC)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	LCD Controller	8-Bit DA Converter (Ch)	10-Bit AD Converter (Ch)	Memory Bank Controller	NAND Flash Controller (Ch)	DRAM Controller (Ch)	DMA Controller	I ² C Bus/SIO (Ch)	SIO/UART (Ch)	High-Speed SIO (Ch)	SPI (SD Card)	USB Device (Full Speed)	Operating Temperature (°C)	Flash Version	Package		
			5V±10%	3.3V±0.3V																													
TMP94C241CFG ◇		2K	50	—						6	●						4	4		8	2		2		2						QFP160 (28 x 28 mm)		
TMP94C251ADFG ◇										6	●							4	4		8	2		2								LQFP144 (20 x 20 mm)	
TMP92C820FG		8K		50										●			●	4	1	●	5		1	●	3	1							
TMP92CA25FG		10K		(Note 2) 50						4	●	●	●				●	4	1	●	4		1	2	●	1	1	●					LQFP144 (16 x 16 mm)
TMP92CH21FG	NA	16K								4	●	●	●	●			●	4	1	●	4		1	2	●	2	1	●					—
TMP92CM22FG		32K		50						4	●		●					4	2		8				2	1							LQFP100 (14 x 14 mm)
TMP92CM27FG			—															8	6	12	2		1	2	4	2						LQFP144 (16 x 16 mm)	
TMP92CZ26XBG **		288K		(Note 1) 16.7						4	●	●	●	●			●	8	2		6		1	2	●	1	1	●					FBGA228 (15 x 15 mm)
TMP92CY23FG/DFG **										4	●	●	●					6	2	12					3	2							TMP92FY23FG/DFG **
TMP92FY23FG/DFG **	256K	16K								4	●	●	●					6	2	12					3	2							—
TMP92CD23AFG/DFG **			50							4	●	●	●					6	2	12					1	3	2						QFP100
TMP92FD23AFG/DFG **	512K	32K								4	●	●	●					6	2	12					1	3	2						—

◇: Contain is a 900/H2 core that is functionally fully compatible with 900/H1 core.

** : Under development

Note 1: 1.4 V to 1.6 V internally; 3.0 V to 3.6 V for input/output interface.

Note 2: Minimum instruction execution times depend on operating voltage, as follows:

2.7 to 3.6 V: 74 ns at 13.5 MHz (fsys)

3.0 to 3.6 V: 50 ns at 20 MHz (fsys)

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

Automotive Microcomputer Selection Guide

8-Bit Microcontrollers for Automotive

TLCS-870 Family: TLCS-870/C Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs) (Note 4)	LED Driver (Ch)	LCD Driver (Ch)	CAN (Ch) (Note 5)	SEI (Ch)	SIO (Ch)	UART (Ch)	SI/UART (Ch)	I ² C (Ch)	8-Bit AD Converter (Ch)	10-Bit AD Converter (Ch)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Watchdog Timer	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP/Flash Version	Package		
TMP86C407IMG/ING	4K			8			1		(Note2) 1		6			1	2	●	●	22		−40 to 85	TMP86P807MG/NG	SOP28/SDIP28	
TMP86C407SMG/SNG				8			1		(Note2) 1		6			1	2	●	●			−40 to 125			
TMP86C408IDMG				8			1		(Note2) 1		6			1	2	●	●	24		−40 to 85	TMP86P808DMG	SSOP30	
TMP86C408SDMG				8			1		(Note2) 1		6			1	2	●	●			−40 to 125			
TMP86C807IMG/ING	8K	256	(1)0.25/122 (2)0.50/122	8			1		(Note2) 1		6			1	2	●	●	22	(1)4.5 to 5.5 (2)2.7 to 5.5	−40 to 85	TMP86P807MG/NG	SOP28/SDIP28	
TMP86C807SMG/SNG				8			1		(Note2) 1		6			1	2	●	●			−40 to 125			
TMP86C808IDMG				8			1		(Note2) 1		6			1	2	●	●	24				TMP86P808DMG	SSOP30
TMP86C808SDMG				8			1		(Note2) 1		6			1	2	●	●			−40 to 85			
TMP86C847IUG				19				1	(Note2) 1			8		1	2	●	●	35			TMP86PM47AUG		
TMP86C847SUG				1										1	2	●	●		−40 to 125		TMP86PH47UG	LQFP44	
TMP86CH47IUG				19			1	(Note2) 1		8		1	2	●	●				−40 to 85		TMP86FH47AUG	(10 x 10 mm)	
TMP86CH47SUG		512																	−40 to 125				
TMP86CH49IUG/IFG	++	16K	(1)0.25/122 (2)0.50/122 (3)0.95/122	13				2	(Note2) 2	1		16		2	4	●	●	56	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM49UG/FG TMP86FS49AIUG	LQFP64 (10 x 10 mm)/ QFP64 (14 x 14 mm) ◇ ++	
TMP86CH87RUG		1K	0.25/122	8	(Note6) 1	1			(Note2) 1			14		1	2	●	●	35	4.5 to 5.5		TMP86PM87RUG	LQFP44 (10 x 10 mm)	
TMP86CM47AIUG	++	32K	(1)0.25/122 (2)0.50/122 (3)0.95/122	19				1	1			8		1	2	●	●	35	(1)4.5 to 5.5 (2)2.7 to 5.5 (3)1.8 to 5.5		TMP86PM47AUG	LQFP44 (10 x 10 mm)	
TMP86CM87RUG				8	(Note6) 1	1			(Note2) 1			14		1	2	●	●				TMP86PM87RUG		
TMP86CM89IFG	++		0.25/122	8					(Note3) 2			8		2	4	●	●	62	4.5 to 5.5		TMP86FS89FG	QFP80 (14 x 20 mm)	
TMP86CS89IFG	++	60K		8	40	1	1														++		

◇: The minimum instruction execution time is 500 ns for the supply voltage range of 3.0 to 5.5 V.

++: Being planned

Note 1: Either I²C bus or SIO module can be selected via software.

Note 2: UART only

Note 3: One channel can be configured as either SIO or UART via software, and the other channel can only be used as UART.

Note 4: Minimum instruction execution times (1) to (3) correspond to power supply voltages (1) to (3).

Note 5: There are four channels of mailboxes.

Note 6: Either the SEI or UART module should be selected via software.

◆ For further information about the I/R/S/T grade levels, please contact your nearest Toshiba sales representative.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

TLCS-870 Family: TLCS-870/X Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (μs)	LED Driver (Ch)	SIO (Ch)	UART (Ch)	10-Bit AD Converter (Ch)	16-Bit Timer/Counter (Ch)	8-Bit Timer/Counter (Ch)	Motor Controller (Ch)	Watchdog Timer	I/O Port (Pins)	Power Supply Voltage (V)	Operating Temperature (°C)	OTP Version	Package
TMP88CH40IMG				14	Note 1 1	Note 1 1	4	1	2	1	●	19			TMP88PH40MG	SOP28
TMP88CH41IUG ++	16K	512	0.20	16	Note 1 1	Note 1 1	8	2	2	1	●	33	4.5 to 5.5	-40 to 85	TMP88PH41UG	LQFP44(10 x 10 mm)
TMP88CH41SUG ++				16	Note 1 1	Note 1 1	8	2	2	1	●			-40 to 125		

Note 1: Cannot be used at the same time because their I/O pins are multiplexed.

++: Being planned

◆ For further information about the I/R/S/T grade levels, please contact your nearest Toshiba sales representative.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

16-Bit Microcontrollers for Automotive

TLCS-900 Family: TLCS-900/L1 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)			CAN (16 Mailboxes) (Ch)	SEI (Ch)	I ² C Bus/SIO (Ch)	10-Bit AD Converter (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	32-kHz Timer (for S/W RTC)	16-Bit PWM Timer (Ch)	CS/MAT Controller (Ch)	PDC (Ch)	Watchdog Timer	Dual Clocks	Clock Gear	I/O Port (Pins)	Operating Temperature (°C)	OTP/Flash Version	Package
TMP91CP82TFG	48K	2K	200	—	—	1	1	2	12	4	2		4		1			●	80	−40 to 125	TMP91PP82TFG	LQFP100 (14 x 14 mm)
TMP91CP27RUG **		4K						2	1	4	6	1	●	3		●	●	●	53	−40 to 85	TMP91FY27UG	LQFP64 (10 x 10 mm)
TMP91CU27RUG **	96K	10K	—	148	400			2	1	4	6	1	●	3		●	●	●				
TMP91CY22IFG	256K	16K						2	1	8	8	2	●	4		●	●	●	81		TMP91FY42FG	LQFP100 (14 x 14 mm)

◆ For further information about the I/R/S/T grade levels, please contact your nearest Toshiba sales representative.

** : Under development

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

32-Bit Microcontrollers for Automotive

TLCS-900 Family: TLCS-900/H1 Series (CMOS)

Part Number	ROM (Bytes)	RAM (Bytes)	Minimum Instruction Execution Times (ns)			Flash Version	CAN (16 Mailboxes) (Ch)	CAN (32 Mailboxes) (Ch)	SEI (Ch)	SIO/UART (Ch)	I ² C Bus/SIO (Ch)	10-Bit AD Converter (Ch)	LCD Driver (Ch)	8-Bit Timer/Counter (Ch)	16-Bit Timer/Counter (Ch)	16-Bit PPG (Ch)	H/W RTC	CS/MAT Controller (Ch)	Watchdog Timer	Dual Clocks	I/O Port (Pins)	Operating Temperature (°C)	Flash Version	Package
TMP92CD54IFG (Note 1)	512K	32K	(Note 2)	—	—			1	1	2	3	12		8	2		●	1	●		68	−40 to 85	TMP92FD54AIFG	LQFP100
TMP92FD54AIFG (Note 1)			50			●		1	1	2	3	12		8	2		●	1	●				—	(14 x 14 mm)

Note 1: Contains voltage regulator.

Note 2: Operating voltage is 4.5 V to 5.25 V.

◆ For further information about the I/R/S/T grade levels, please contact your nearest Toshiba sales representative.

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

TX System RISC Selection Guide

32-Bit Microcontrollers

TX19 Family

Part Number	Maximum Operating Frequency (MHz)	Internal Bus Width (Bits)	External Bus Width (Bits)	Internal ROM (kbytes)	Internal RAM (kbytes)	DMA Channels (Ch)	I/O Ports (Pins)	Serial Interface (Ch)	Timer Channels (Ch)	External Interrupt Pins (Pins)	Dual Clocks	Debug Support Unit	Features	Package
TMP1940CYAFG	32	32	16	Mask 256	10	4	77	5	8	11	●	●	AD converter	
TMP1940FDBFG	32	32	16	Flash 512	16	4	77	5	8	11	●	●	Flash version of TMP1940CYAFG, AD converter	LQFP100
TMP1941AFG	40	32	16	None	10	4	46	5	8	11	●	●	ROM-less version of TMP1940CYAFG, AD converter	
TMP1942CYUG	32	32	16	Mask 256	16	4	108	6	26	29	●	●	AD converter, DA converter	
TMP1942CZUG	32	32	16	Mask 384	16	4	108	6	26	29	●	●	AD converter, DA converter	LQFP144
TMP1942FDUG	32	32	16	Flash 512	20	4	108	6	26	29	●	●	Flash version of TMP1942CYUG/CZUG, AD converter, DA converter	
TMP1942CZXBG	32	32	16	Mask 384	16	4	108	6	26	29	●	●	AD converter, DA converter	
TMP1942FDXBG	32	32	16	Flash 512	20	4	108	6	26	29	●	●	Flash version of TMP1942CZXBG, AD converter, DA converter Only engineering samples are available now.	FBGA177
TMP19A43FDXBG **	40	32	16	Flash 512	24	8	143	7	17	48	●	●	AD converter, DA converter 32-bit timer: 1 channel (4 input capture channels, 8 output compare channels) For availability, please contact Toshiba.	FBGA193
TMP1962C10BXXBG	40.5	32	16	Mask 1024	40	8	202	8	17	25		●	Multiplexed/separate external bus interface, 32-bit timer: 1 channel (8 input capture channels, 8 output compare channels)	FBGA281
TMP1962F10AXBG	40.5	32	16	Flash 1024	40	8	202	8	17	25		●	2, 8-ch ADCs; 2 CANs For availability, please contact Toshiba.	LQFP100
TMP19A51FYFG (Note 1) **	56	32	16	Flash 256	16	8	62	5	13	16		●	Multiplexed/separate external bus interface, 32-bit timer: 1 channel (4 input capture channels, 10 output compare channels)	FBGA281
TMP19A64F20AXBG **	54	32	16	Flash 2048	64	8	209	8	26	20	●	●	AD converter, third-generation PMD	LQFP100
TMP19A70CYUG	56	32	—	Mask 256	10	8	75	3	4	10		●	AD converter, third-generation PMD	QFP100
TMP19A70CYFG	56	32	—	Mask 256	10	8	75	3	4	10		●	Flash version of TMP19A70CYUG AD converter, third-generation PMD	LQFP100
TMP19A70FYUG	56	32	—	Flash 256	10	8	75	3	4	10		●	Flash version of TMP19A70CYFG AD converter, third-generation PMD	QFP100
TMP19A71CYUG **	56	32	—	Mask 256	10	8	75	4	4	10		●	AD converter, third-generation PMD	LQFP100
TMP19A71CYFG **	56	32	—	Mask 256	10	8	75	4	4	10		●	Flash version of TMP19A71CYUG AD converter, third-generation PMD	LQFP100
TMP19A71FYUG **	56	32	—	Flash 256	10	8	75	4	4	10		●	Flash version of TMP19A71CYFG AD converter, third-generation PMD	QFP100
TMP19A71FYFG **	56	32	—	Flash 256	10	8	75	4	4	10		●	AD converter, third-generation PMD	QFP100

Note 1: This product is for automotive applications.

** : Under development

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

32-Bit Microprocessors

TX39 Family

Part Number	Maximum Operating Frequency (MHz)	Internal Bus Width (Bits)	External Bus Width (Bits)	Instruction Cache (Kbytes)	Data Cache (Kbytes)	DMAC Channels (Ch)	I/O Ports (Pins)	Serial Interface (Ch)	Timer Channels (Ch)	External Interrupt Pins (Pins)	PCMCIA Interface	Debug Support Unit	Memory Controller	Others	Package
TMPR3911BU	58	32	32	4	1		39	3	2	39	●				LQFP176
TMPR3911BXB	58	32	32	4	1		39	3	2	39	●		SDRAM, ROM, SRAM, Flash	LCD interface	FBGA177
TMPR3912AUG-92	92	32	32	4	1		39	3	2	39	●				LQFP208
TMPR3912XBG-92	92	32	32	4	1		39	3	2	39	●				FBGA217
TMPR3916FG	60	32	32	4	1	2	30	4	2	3		●	SDRAM, ROM, SRAM, Flash	DA converter, CAN controller, graphics controller	QFP208
TMPR3927CF	133	32	32	8	4	4	16	2	3	6		●	SDRAM, SRAM, ROM, Flash	PCI controller (33 MHz)	QFP240

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

64-Bit Microprocessors

TX49 Family

Part Number	Maximum Operating Frequency (MHz)	Internal Bus Width (Bits)	External Bus Width (Bits)	Instruction Cache (Kbytes)	Data Cache (Kbytes)	DMAC Channels (Ch)	I/O Ports (Pins)	Serial Interface (Ch)	Timer Channels (Ch)	External Interrupt Pins (Pins)	PCMCIA Interface	Debug Support Unit	Memory Controller	Others	Package
TMPR4951BFG-200	200	64	32	16	8				1	7		●			QFP100
TMPR4955AFG-200B	200	64	32	32	32				1	7		●			
TMPR4955BFG-300	300	64	32	32	32				1	7		●		FPU	QFP160
TMPR4955CFG-400	400	64	32	32	32				1	7		●			
TMPR4956CXBG-400	400	64	64	32	32				1	7		●			PFBGA217
TMPR4925XBG-200	200	64	32	16	16	4	32	2	3	8	●	●	NAND Flash, SDRAM, SRAM, ROM, NOR Flash	PCI controller (33 MHz), FPU	PBGA256
TMPR4926XBG-200	200	64	32	16	16	4	32	2	3	8	●	●		PCI controller (33 MHz), FPU, DES/3DES	
TMPR4927ATBG-200	200	64	32	32	32	4	16	2	3	6		●	SDRAM, SRAM, ROM, Flash	PCI controller (66 MHz), FPU	TBGA420
TMPR4937XBG-300/333	300 /333	64	32	32	32	8	16	2	3	6		●	SDRAM, SRAM, ROM, Flash		PBGA484
TMPR4938XBG-300/333	300 /333	64	32	32	32	8	16	2	3	6		●		PCI controller (66 MHz), FPU, Ether MAC	
TX4939XBG-400	**	400	64	32	32	32	8	14	4	3	6	●	NAND Flash, SDRAM, SRAM, ROM, NOR Flash	PCI controller (66 MHz), RTC, FPU, Ether MAC, ATA/ATAPI, I ² S/I ² C, Crypt engine (DES/3DES, etc.)	PBGA456

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

64-Bit Microprocessors (Superscalar)

TX99 Family

Part Number	Maximum Operating Frequency (MHz)	Internal Bus Width (Bits)	External Bus Width (Bits)	Instruction Cache (Kbytes)	Data Cache (Kbytes)	DMA Channels (Ch)	I/O Ports (Pins)	Serial Interface (Ch)	Timer Channels (Ch)	External Interrupt Pins (Pins)	PCMCIA Interface	Debug Support Unit	Memory Controller	Others	Package
TX9956XBG-533 **	533	64	64	32	32				1	7		●		256-KB Level-2 cache, FPU	PBGA272

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

** : Under development

64-Bit Microprocessor Peripherals (PCI companion chip)

Part Number	Function	Package
TC86C001FG (GOKU-S)	PCI interface (32 bit, 33 MHz) ATA/ATAPI host controller, Ultra DMA transfer (mode 4), maximum transfer rate = 66 MB/s USB1.1 host controller: 2 ports (OpenHCI 1.0a compatible) USB device controller: 1 port I ² C bus/SIO Power supply voltage (I/O = 3.3 V, internal = 1.5 V)	LQFP144

◆ The suffix (G) appended to the part number represents a Lead(Pb)-Free product. For details, please contact your nearest Toshiba sales representative.

Microcomputer Development System Selection Guide

- TLCS-47 Family Development System● 24
- TLCS-870/C series Development System model15 System● 26
- TLCS-870/C series Development System Light System● 30
- TLCS-870 series Development System● 32
- TLCS-870/X series Development System● 36
- TLCS-900 Family Development System● 38
- TX19 series Development System● 42
- TX19A series Development System● 42
- Accessory Tools● 43

TLCS-47 Family Development System

□ Software Products

Language Tool		Test Tool
Assembler	C-Like Compiler	Debugger
SW471E0-ZZJ: Japanese edition SW471E0-ZZE: English edition	SW476E0-ZZJ: Japanese edition SW476E0-ZZE: English edition	SW477E0-ZZJ: Controller: BM1020A (for the RTE emulation system), Japanese edition SW477E0-ZZE: Controller: BM1020A (for the RTE emulation system), English edition SW477E1-ZZJ: Controller: BM1022R0B (for the model10 emulation system), Japanese edition SW477E1-ZZE: Controller: BM1022R0B (for the model10 emulation system), English edition

□ Hardware Products

Target MCU			Test Tools										
Part Number	OTP/Flash MCU	Package	Controller	Emulator/Emulation Pod	MCU Probe (#1, #2)	Package Converter (#1, #2)							
TMP47C101MG	—	SOP16	BM1020A ##	BM4721A ##	(PN100002 + PN200001)	BM1160 + AS-DIP.3-016-SO03-1							
TMP47C201MG	TMP47P201VPG	DIP16				BM47C203N0A ##	BM47C203N0A ##	BM1160					
TMP47C101PG													
TMP47C201PG													
TMP47C102MG	TMP47P202VMG	SOP20	BM1020A ##	BM47C203N0A ##	(PN100004)	AS-DIP.3-020-SO03-1							
TMP47C202MG	TMP47P202VPG	DIP20				BM47C203N0A ##	BM47C203N0A ##	—					
TMP47C102PG													
TMP47C202PG													
TMP47C103MG	TMP47P403VMG	SOP28	BM1020A ##	BM47C203N0A ##	(PN100003)	AS-DIP.6-028-SO08-1							
TMP47C203MG	TMP47P403VNG	SDIP28				BM47C203N0A ##	BM47C203N0A ##	(PN200004)					
TMP47C103NG													
TMP47C203NG													
TMP47C206MG	TMP47P206VMG	SOP20	BM1022R0B	BM47C206M0A	(PN100004)	(AS-DIP.3-020-SO03-1)							
TMP47C206PG	TMP47P206VPG	DIP20				BM1022R0B	BM47C206M0A	(PN100004)	—				
TMP47C222FG	TMP47P422VFG	QFP44 (14 x 14)								BM1022R0B	BM47C422N0B	(PN100002)	(PN200001)
TMP47C422FG													
TMP47C222NG													
TMP47C422NG	TMP47P422VNG	SDIP42	BM1020A ##	BM47214A ##	(PN110003)	BM1152 + AS-SDP.4-028-SO05-2							
TMP47C222UG	TMP47P422VUG	LQFP44 (10 x 10)				BM1022R0B	BM47C422N0B	(PN100002)	(PN200001)				
TMP47C422UG													
TMP47C241MG													
TMP47C241NG	TMP47P241VNG	SDIP28	BM1022R0B	BM47C443N0B	(PN100003)	BM1152							
TMP47C243DMG	TMP47P443VDMG	SSOP30				BM1022R0B	BM47C443N0B	(PN100003)	AS-DIP.6-028-SO08-1				
TMP47C443DMG													
TMP47C243MG													
TMP47C443MG	TMP47P443VMG	SOP28	BM1022R0B	BM47C443N0B	(PN100003)	AS-DIP.6-028-SO08-1							
TMP47C243NG	TMP47P443VNG	SDIP28					BM1022R0B	BM47C443N0B	(PN100003)	AS-DIP.6-028-SO08-1			
TMP47C443NG													
TMP47C443NG													

- The TLCS-47 family software runs in the following environments:
Japanese edition: DOS-compatible box under the Japanese Windows 95 or NT 4.0 environment, or Japanese MS-DOS.
English edition: DOS-compatible box under the English Windows 95 or NT 4.0 environment, or English MS-DOS.
 - #1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.
 - #2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."
 - ※: Emulation Technology products are available from Micron, Inc.
 - ** : Under development
 - ##: Contact your local Toshiba sales representative before ordering products.
- Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
As a guideline, the adapter should be replaced after 2,000 writes.

Accessories				Notes
QFP Adapter (#1)	MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	
			—	The package converter (AS-DIP.3-016-SO03-1) is made by Emulation Technology, Inc. (ET). ※
			BM1187	—
			BM11613 **	The package converter (AS-DIP.3-020-SO03-1) is made by Emulation Technology, Inc. (ET). ※
	—		BM1187	—
			BM11541	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
			BM1140	—
			BM11626 **	The package converter (AS-DIP.3-020-SO03-1) is made by Emulation Technology, Inc. (ET). ※
—			BM11125	—
	IC149-044-039-B5		BM11603	One IC socket (IC149-044-039-B5) is supplied with the PN120019. The IC socket (IC149-044-039-B5) is available from Yamaichi Electronics, Co. Ltd.
	—		BM11102	—
	IC149-044-052-B5		BM11670	One IC socket (IC149-044-052-B5) is supplied with the PN120030. The IC socket (IC149-044-052-B5) is available from Yamaichi Electronics, Co. Ltd.
	—		BM11557	The package converter (AS-SDP.4-028-SO05-2) is made by Emulation Technology, Inc. (ET). ※
			BM1156	—
	IC253-030-0002-B		BM11115	One IC socket (IC253-030-0002-B) is supplied with the PN200007. The IC socket (IC253-030-0002-B) is available from Yamaichi Electronics, Co. Ltd. (Note 1)
	—		BM11601	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
			BM11100	—

TLCS-870/C series Development System model15 System (1/2)

Software Products

Language Tool	Test Tool
C Compiler & Assembler Set (%1)	Debugger (%1)
SW86YN0-ZCK: 1 license (Japanese edition)	SW86DN9-ZCJ: 1 license (Japanese edition)
SW86YN0-ZCF: 1 license (English edition)	SW86DN9-ZCE: 1 license (English edition)
SW86YN3-ZCK: 10 licenses (Japanese edition)	SW86DN3-ZCJ: 10 licenses (Japanese edition)
SW86YN3-ZCF: 10 licenses (English edition)	SW86DN3-ZCE: 10 licenses (English edition)

Hardware Products

Target MCU			Test Tools				
Part Number	OTP/Flash MCU	Package	Controller	Interface Module	Emulation Module	Emulation Chip (#2)	Target Connection Board
TMP86CH06UG	TMP86PH06UG	LQFP44 (10 x 10)				TMP86C906XB **	BMP86D044DE0A
TMP86CH06AUG							
TMP86CH06NG	TMP86PH06NG	SDIP42					BMP86D042NB0A
TMP86P202MG		SOP20					BMP86D020MC0A
TMP86P203MG							
TMP86P202PG		DIP20					BMP86D020NA0A
TMP86P203PG							
TMP86C407NG	TMP86P807NG						
TMP86C807NG	TMP86F807NG						
TMP86C407ING	TMP86P807NG	SDIP28					BMP86D028NB0A
TMP86C407SNG							
TMP86C807ING							
TMP86C807SNG							
TMP86C407MG	TMP86P807MG				BMP86A200010B		
TMP86C807MG	TMP86F807MG						
TMP86C407IMG	TMP86P807MG	SOP28				TMP86C908XB **	BMP86D028MC0A
TMP86C407SMG							
TMP86C807IMG							
TMP86C807SMG							
TMP86C408NG	TMP86P808NG						
TMP86C808NG	TMP86F808NG	SDIP30					BMP86D030NB0A
TMP86C408DMG	TMP86P808DMG						
TMP86C808DMG	TMP86F808DMG						
TMP86C408IDMG							BMP86D030MF1A
TMP86C408SDMG	TMP86P808DMG	SSOP30					
TMP86C808IDMG							
TMP86C808SDMG							
TMP86CH12MG **	TMP86FH12MG **		BM1040R0A	BMP86A100010B			
TMP86FH12MG **	—						
TMP86C822UG	TMP86PH22UG	LQFP44 (10 x 10)					BMP86D044DE1A
TMP86CH22UG							
TMP86CM23AUG	TMP86PM23UG				BMP86A200010B	TMP86C923XB **	
TMP86CP23AUG	TMP86FS23UG TMP86PS23UG	LQFP64 (10 x 10)					BMP86D064DG0A
TMP86CM25AFG	TMP86FM25FG						
TMP86CM25FG		QFP100 (14 x 20)					BMP86D100FF0A
TMP86CS25AFG	TMP86PS25FG				BMP86A200020A	TMP86C925XB **	
TMP86CS25ADFG	—	LQFP100 (14 x 14)					BMP86D100DG0A
TMP86CM27FG	TMP86PS27FG	QFP80 (14 x 20)					
TMP86CP27AFG	TMP86FS27FG					TMP86C927XB **	BMP86D080FE0A
TMP86C420UG							
TMP86C820UG	TMP86P820UG						
TMP86CH21UG							
TMP86CH21AUG							
TMP86C829BUG	TMP86PM29BUG	LQFP64 (10 x 10)					BMP86D064DG0A
TMP86CH29BUG							
TMP86CM29BUG					BMP86A200010B		
TMP86FM29UG	—					TMP86C929AXB **	
TMP86FM29FG							
TMP86C420FG	TMP86P820FG						
TMP86C820FG							
TMP86CH21FG		QFP64 (14 x 14)					BMP86D064DE0A
TMP86C829BFG	TMP86PM29BFG						
TMP86CH29BFG							
TMP86CM29BFG							

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.
 #1: Those enclosed within parentheses are spare parts. One each is supplied with a target connection board.
 #2: The emulation chip is specifically designed for each target MCU.
 **: Under development
 ++: Being planned
 Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
 As a guideline, the adapter should be replaced after 2,000 writes.

Accessories				Notes
QFP Adapter (#1)	MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	
(PN210019)	PN210020A	(PN210021)	BM11656	—
	—		BM11155	
	(IC253-020-0004-B)		BM11704 **	
			BM11203	
			TMP86P807NG: BM11197 TMP86F807NG: PN410119	—
	—			
			BM11197	
			TMP86P807MG: BM11684 TMP86F807MG: PN410117	
—	(IC253-028-0003-B)	—	BM11684	One IC socket (IC253-028-0003-B) is supplied with the target connection board. The IC socket (IC253-028-0003-B) is available from Yamaichi Electronics, Co., Ltd.
	—		TMP86P808NG: BM11210 TMP86F808NG: PN410119	
			TMP86P808DMG: BM11183 TMP86F808DMG: PN410118	
	(IC253-030-0002-B)		BM11183	One IC socket (IC253-030-0002-B) is supplied with the target connection board. The IC socket (IC253-030-0002-B) is available from Yamaichi Electronics, Co., Ltd. (Note 1)
			PN410118 **	
(PN210019)	PN210020A	(PN210021)	BM11713	
			BM11698	
(PN210031)	PN210033	(PN210032)	TMP86PS23UG: BM11698 TMP86FS23UG: PN410105	
			PN410111	
(PN210004)	PN210005A	(PN210006)	BM11672	
(PN210022)	PN210023	(PN210024)	—	
(PN210001)	PN210002	(PN210003)	TMP86PS27FG: BM11701 TMP86FS27FG: PN410104	
			BM11662	
				—
(PN210031)	PN210033	(PN210032)	BM11662 **	
			PN410105 **	
			PN410108 **	
			BM11663	
(PN210025)	PN210026	(PN210027)		
			BM11663 **	

TLCS-870/C series Development System model15 System (2/2)

□ Software Products

Language Tool	Test Tool
C Compiler & Assembler Set (%1)	Debugger (%1)
SW86YN0-ZCK: 1 license (Japanese edition)	SW86DN9-ZCJ: 1 license (Japanese edition)
SW86YN0-ZCF: 1 license (English edition)	SW86DN9-ZCE: 1 license (English edition)
SW86YN3-ZCK: 10 licenses (Japanese edition)	SW86DN3-ZCJ: 10 licenses (Japanese edition)
SW86YN3-ZCF: 10 licenses (English edition)	SW86DN3-ZCE: 10 licenses (English edition)

□ Hardware Products

Target MCU			Test Tool				
Part Number	OTP/Flash MCU	Package	Controller	Interface Module	Emulation Module	Emulation Chip (#2)	Target Connection Board
TMP86CS44UG	TMP86PS44UG					TMP86C944XB **	
TMP86C845UG							
TMP86C847UG							
TMP86CH47AUG	TMP86PM47AUG						
TMP86CH47IUG	TMP86PH47UG						
TMP86C847IUG	TMP86FH47AUG	LQFP44 (10 x 10)					BMP86D044DE0A
TMP86C847SUG	TMP86FH47ADUG						
TMP86CH47IUG							
TMP86CH47SUG					BMP86A200010B		
TMP86CM47AUG	TMP86PM47AUG					TMP86C947XB **	
TMP86CM47AIUG ++							
TMP86FH46ANG	—						
TMP86C846NG	TMP86PH46NG						
TMP86CH46ANG	TMP86PM46NG	SDIP42					BMP86D042NB1A
TMP86CM46ANG	TMP86FH46ANG						
TMP86CM46ANG	TMP86PM46NG						
TMP86FH47ADUG		LQFP48 (7 x 7)					BMP86D048DG0A **
TMP86FM26UG							
TMP86FM48UG	—	LQFP64 (10 x 10)				TMP86C926XB **	BMP86D064DG0A
TMP86FP24FG		LQFP80 (12 x 12)			BMP86A200030A	TMP86C948XB **	BMP86D080DG1A
TMP86FM48FG							
TMP86CH49FG	TMP86PM49FG						
TMP86CM49FG	TMP86FS49AFG	QFP64 (14 x 14)	BM1040R0A	BMP86A100010B			BMP86D064DE0A
TMP86CS49FG	TMP86FS49AFG						
TMP86CH49NG							
TMP86CM49NG	TMP86PM49NG	SDIP64			BMP86A200010B	TMP86C949XB **	BMP86D064NB0A
TMP86CH49UG							
TMP86CH49IUG ++	TMP86PM49UG						
TMP86CM49UG	TMP86FS49AUG	LQFP64 (10 x 10)					BMP86D064DG0A
TMP86CS49UG	TMP86FS49AUG						
TMP86CS64AFG	TMP86PS64FG	QFP100 (14 x 20)			BMP86A200020A	TMP86C964XB **	BMP86D100FF0A
TMP86CH72FG	TMP86PM72FG **	QFP64 (14 x 14)					
TMP86CM72FG					BMP86A200010B	TMP86C972XB **	BMP86D064DE0A
TMP86CK74AFG	TMP86PM74AFG	QFP80 (14 x 20)				TMP86C974XB **	BMP86D080FE0A
TMP86CM74AFG							
TMP86CH87RUG	TMP86PM87RUG	LQFP44 (10 x 10)					BMP86D044DE0A
TMP86CM87RUG					BMP86A200020A	TMP86C987XB **	
TMP86C809NG **	TMP86FH09NG **	SDIP32					BMP86D032NB0A
TMP86CH09NG **							
TMP86CS28FG **	TMP86FS28FG **	QFP80 (14 x 20)					BMP86D080FE0A
TMP86CS28DFG **	TMP86FS28DFG **	LQFP80 (12 x 12)			BMP86A200010B	TMP86C989XB **	BMP86D080DG0A
TMP86CM89IFG ++	TMP86FS89FG ++	QFP80 (14 x 20)					BMP86D080FE0A
TMP86CS89IFG ++							

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.
 #1: Those enclosed within parentheses are spare parts. One each is supplied with a target connect board.
 #2: The emulation chip is specifically designed for each target MCU.
 **: Under development
 ++: Being planned

Accessories				Notes
QFP Adapter (#1)	MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	
			BM11687	
			TMP86PM47AUG: BM11687	
			TMP86PH47UG: BM11687 **	
(PN210019)	PN210020A	(PN210021)	TMP86FH47AUG: PN410109 **	
			TMP86FH47ADUG: PN410115 **	
			BM11687	
			PN410110 **	
—	—	—	TMP86PH46NG/TMP86PM46NG: BM11188	
			TMP86FH46ANG: PN410110 **	
			BM11188	
**	**	**	PN410115 **	
(PN210031)	PN210033	(PN210032)	PN410105	
(PN210007)	PN210008	(PN210009)	TBD	
			PN410108	
(PN210025)	PN210026	(PN210027)	TMP86PM49FG: BM11709	—
			TMP86FS49AFG: TBD	
			TBD	
—	—	—	BM11211	
(PN210031)	PN210033	(PN210032)	TMP86PM49UG: BM11708	
			TMP86FS49AUG: PN410105 **	
			PN410105 **	
(PN210004)	PN210005A	(PN210006)	TMP86PS64FG: BM11690	
			TMP86FS64FG: PN410111	
(PN210025)	PN210026	(PN210027)	BM11707	
(PN210001)	PN210002	(PN210003)	BM11689	
(PN210019)	PN210020A	(PN210021)	BM11687	
—	—	—	PN410119 **	
(PN210001)	PN210002	(PN210003)	PN410104 **	
(PN210007)	PN210008	(PN210009)	PN410007 **	
(PN210001)	PN210002	(PN210003)	PN410104 **	

TLCS-870/C series Development System Light System (1/2)

□ Software Products

Language Tool	Test Tool
C Compiler & Assembler Set (%1)	Debugger (%2)
SW86YN0-ZCK: 1 license (Japanese edition) SW86YN0-ZCF: 1 license (English edition) SW86YN3-ZCK: 10 licenses (Japanese edition) SW86YN3-ZCF: 10 licenses (English edition)	The emulator comes with a download license.

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.
%2: A dedicated debugger can be downloaded from the TOSHIBA Microcomputer Development System Web site.

#2: The emulation chip is specifically designed for each target MCU.
#3: Adlinks probe sets are available from Daimaru Kogyo, Ltd.

** : Under development
++ : Being planned

Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
As a guideline, the adapter should be replaced after 2,000 writes.

□ Hardware Products

Target MCU			Test Tools		Accessories		Notes
Part Number	OTP/Flash MCU	Package	Emulator	Emulation Chip (#2)	Adlinks Probe Set (#3)	OTP/Flash Programming Adapter	
TMP86CH06UG	TMP86PH06UG	LQFP44 (10 x 10)		TMP86C906XB **	AP44QP	BM11656	
TMP86CH06AUG							
TMP86CH06NG	TMP86PH06NG	SDIP42			AP42D0U-2	BM11155	
TMP86P202MG	—	SOP20			AP20S3U-2	BM11704 **	
TMP86P203MG		DIP20			AP20D3W-2	BM11203	
TMP86P202PG							
TMP86P203PG	TMP86P807NG					TMP86P807NG: BM11197	
TMP86C407NG						TMP86F807NG	TMP86F807NG: PN410119
TMP86C807NG	TMP86P807NG	SDIP28			AP28D4U	BM11197	
TMP86C407ING							
TMP86C407SNG							
TMP86C807ING							
TMP86C807SNG	TMP86P807MG		BMP86A300010A			TMP86P807MG: BM11684	
TMP86C407MG						TMP86F807MG	TMP86F807MG: PN410117
TMP86C807MG	TMP86P807MG	SOP28		TMP86C908XB **	AP28S9T	BM11684	
TMP86C407IMG							
TMP86C407SMG							
TMP86C807IMG							
TMP86C807SMG	TMP86P808NG	SDIP30				TMP86P808NG: BM11210	
TMP86C408NG						TMP86F808NG	TMP86F808NG: PN410119
TMP86C808NG	TMP86P808DMG					TMP86P808DMG: BM11183	
TMP86C408DMG						TMP86F808DMG	TMP86F808DMG: PN410118
TMP86C808DMG	TMP86P808DMG	SSOP30			AP30S3N-2	BM11183	(Note1)
TMP86C408IDMG							
TMP86C408SDMG							
TMP86C808IDMG							
TMP86C808SDMG	TMP86FH12MG **		BMP86A300020A	TMP86C912XB **	AP30S3N **	PN410118	
TMP86CH12MG **							
TMP86FH12MG **	TMP86PH22UG	LQFP44 (10 x 10)			AP44QP-2	BM11713 **	
TMP86C822UG							
TMP86CH22UG	TMP86PM23UG	LQFP64 (10 x 10)	BMP86A300010A	TMP86C923XB **	AP64QM	BM11698	
TMP86CM23AUG						TMP86FS23UG	TMP86FS23UG: PN410105 **
TMP86CP23AUG	TMP86PS23UG					TMP86PS23UG: BM11698	
TMP86CM25AFG	TMP86FM25FG					PN410111	
TMP86CM25FG	TMP86PS25FG	QFP100 (14 x 20)	BMP86A300020A	TMP86C925XB **	AP100QN	BM11672	
TMP86CS25AFG							
TMP86CS25ADFG	—	LQFP100 (14 x 14)			AP100QM-2	—	
TMP86CM27FG	TMP86PS27FG	QFP80 (14 x 20)		TMP86C927XB **	AP80QP	TMP86PS27FG: BM11701	
TMP86CP27AFG	TMP86FS27FG					TMP86FS27FG: PN410104	
TMP86C420UG	TMP86P820UG					BM11662	
TMP86C820UG							
TMP86CH21UG	TMP86PM29BUG	LQFP64 (10 x 10)			AP64QM	BM11662 **	
TMP86CH21AUG							
TMP86C829BUG							
TMP86CH29BUG							
TMP86CM29BUG			BMP86A300010A				
TMP86FM29UG							
TMP86FM29FG	—			TMP86C929AXB **		PN410105 **	
TMP86C420FG	TMP86P820FG					PN410108 **	
TMP86C820FG						BM11663	
TMP86CH21FG	TMP86PM29BFG	QFP64 (14 x 14)			AP64QP	BM11663 **	
TMP86C829BFG							
TMP86CH29BFG							
TMP86CM29BFG							

TLCS-870/C series Development System Light System (2/2)

Software Products

Language Tool	Test Tool
C Compiler & Assembler Set (%1)	Debugger (%2)
SW86YN0-ZCK: 1 license (Japanese edition) SW86YN0-ZCF: 1 license (English edition) SW86YN3-ZCK: 10 licenses (Japanese edition) SW86YN3-ZCF: 10 licenses (English edition)	The emulator comes with a download license.

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.
%2: A dedicated debugger can be downloaded from the TOSHIBA Microcomputer Development System Web site.
#2: The emulation chip is specifically designed for each target MCU.
#3: Adlinks probe sets are available from Daimaru Kogyo, Ltd.
**: Under development
++: Being planned

Hardware Products

Target MCU			Test Tools		Accessories		Notes
Part Number	OTP/Flash MCU	Package	Emulator	Emulation Chip (#2)	Adlinks Probe Set (#3)	OTP/Flash Programming Adapter	
TMP86CS44UG	TMP86PS44UG			TMP86C944XB **		BM11687	
TMP86C845UG							
TMP86C847UG							
TMP86CH47AUG	TMP86PM47AUG					TMP86PM47AUG: BM11687	
TMP86C847IUG	TMP86PH47UG					TMP86PH47UG: BM11687 **	
TMP86C847SUG	TMP86FH47AUG	LQFP44 (10 x 10)			AP44QP	TMP86FH47AUG: PN410109 **	
TMP86CH47IUG	TMP86FH47ADUG					TMP86FH47ADUG: PN410115 **	
TMP86CH47SUG							
TMP86CM47AUG			BMP86A300010A				
TMP86CM47AIUG ++	TMP86PM47AUG			TMP86C947XB **		BM11687	
TMP86FH46ANG	—					PN410110 **	
TMP86C846NG	TMP86PH46NG						
TMP86CH46ANG	TMP86PM46NG	SDIP42			AP42D0U-3	TMP86PH46NG/TMP86PM46NG : BM11188	
TMP86CM46ANG	TMP86FH46ANG					TMP86FH46ANG: PN410110 **	
TMP86CM46ANG	TMP86PM46NG					BM11188	
TMP86FH47ADUG		LQFP48 (7 x 7)			**	PN410115 **	
TMP86FM26UG							
TMP86FM48UG		LQFP64 (10 x 10)	BMP86A300030A	TMP86C926XB ** TMP86C948XB **	AP64QM	PN410105	
TMP86FP24FG		LQFP80 (12 x 12)	—	—	—	TBD	Currently supported by model15 system
TMP86FM48FG			BMP86A300030A	TMP86C948XB **		PN410108	
TMP86CH49FG	TMP86PM49FG						
TMP86CM49FG	TMP86FS49AFG	QFP64 (14 x 14)			AP64QP	TMP86PM49FG: BM11709 TMP86FS49AFG: TBD	
TMP86CS49FG	TMP86FS49AFG					TBD	
TMP86CH49NG	TMP86PM49NG						
TMP86CM49NG		SDIP64	BMP86A300010A	TMP86C949XB **	AP64D0U-2	BM11211	
TMP86CH49UG	TMP86PM49UG						
TMP86CH49IUG ++	TMP86FS49AUG	LQFP64 (10 x 10)			AP64QM	TMP86PM49UG: BM11708 TMP86FS49AUG: PN410105 **	
TMP86CM49UG							
TMP86CS49UG	TMP86FS49AUG					PN410105 **	
TMP86CS64AFG	TMP86PS64FG TMP86FS64FG	QFP100 (14 x 20)	BMP86A300020A	TMP86C964XB **	AP100QN	TMP86PS64FG: BM11690 TMP86FS64FG: PN410111	
TMP86CH72FG	TMP86PM72FG **	QFP64 (14 x 14)		TMP86C972XB **	AP64QP	BM11707	
TMP86CM72FG			BMP86A300010A				
TMP86CK74AFG	TMP86PM74AFG	QFP80 (14 x 20)		TMP86C974XB **	AP80QP	BM11689	
TMP86CM74AFG							
TMP86CH87RUG	TMP86PM87RUG	LQFP44 (10 x 10)			AP44QP	BM11687	
TMP86CM87RUG			BMP86A300020A	TMP86C987XB **			
TMP86C809NG **	TMP86FH09NG **	SDIP32			AP32D4U	PN410119 **	
TMP86CH09NG **							
TMP86CS28FG **	TMP86FS28FG **	QFP80 (14 x 20)			AP80QP	PN410104 **	
TMP86CS28DFG **	TMP86FS28DFG **	LQFP80 (12 x 12)	BMP86A300010A	TMP86C989XB **	AP80QM	PN410007 **	
TMP86CM89IFG ++	TMP86FS89FG ++	QFP80 (14 x 20)			AP80QP	PN410104 **	
TMP86CS89IFG ++							

TLCS-870 series Development System (1/2)

□ Software Products

Language Tool	Test Tool
C/C-Like Compiler & Assembler Set (%1)	Debugger (%1)
SW87YN0-ZCJ: 1 license (Japanese edition)	SW87DN9-ZCK: 1 license (Japanese edition)
SW87YN0-ZCE: 1 license (English edition)	SW87DN9-ZCF: 1 license (English edition)
SW87YN3-ZCJ: 10 licenses (Japanese edition)	SW87DN3-ZCK: 10 licenses (Japanese edition)
SW87YN3-ZCE: 10 licenses (English edition)	SW87DN3-ZCF: 10 licenses (English edition)

□ Hardware Products

Target MCU			Test Tools		Accessories			
Part Number	OTP/Flash MCU	Package	Controller	Emulation Pod	MCU Probe (#1, #2)	Package Converter (#1, #2)	QFP Adapter (#1)	
TMP87C405AMG	TMP87P808MG	SOP28		BM87C408M0A	(PN100003)	(AS-DIP.6-028-SO08-1)	—	
TMP87C807UG	TMP87PH47UG	QFP44 (10 x 10)		BM87CH47U0B	(PN120011)	—	(PN210019)	
TMP87C408DMG	TMP87P808MG TMP87P808NG	SSOP30				PN200007		
TMP87C408LMG	TMP87P808LMG	SOP28				(AS-DIP.6-028-SO08-1)		
TMP87C808LMG								
TMP87C408LNG	TMP87P808LNG	SDIP28		BM87C408M0A		PN200004		
TMP87C808LNG								
TMP87C408MG	TMP87P808MG	SOP28			(PN100003)	(AS-DIP.6-028-SO08-1)	—	
TMP87C808MG								
TMP87C408NG	TMP87P808NG	SDIP28				PN200004		
TMP87C808NG								
TMP87C409BMG	TMP87P809MG	SOP28				AS-DIP.6-028-SO08-1		
TMP87C809BMG								
TMP87C409BNG	TMP87P809NG	SDIP28		BM87C809N0A		(PN200004)		
TMP87C809BNG								
TMP87C814FG	TMP87PM14FG	QFP64 (14 x 20)				PN120007	PN210010	
TMP87CH14FG								
TMP87CK14FG								
TMP87CM14FG								
TMP87C814NG	TMP87PM14NG	SDIP64		BM87CM14N0A	(PN110008)			
TMP87CH14NG			BM1022R0B				—	
TMP87CK14NG								
TMP87CM14NG								
TMP87CH21CDFG	TMP87PP21DFG	LQFP80 (12 x 12)			PN120006A		PN210007	
TMP87CP21CDFG								
TMP87CH21CFG	TMP87PP21FG	QFP80 (14 x 20)			PN120004		PN210001	
TMP87CP21CFG				BM87CP23F0B				
TMP87CM21CDFG	TMP87PP21DFG	LQFP80 (12 x 12)			PN120006A		PN210007	
TMP87CM21CFG	TMP87PP21FG	QFP80 (14 x 20)			PN120004		PN210001	
TMP87CM23AFG	TMP87PP23FG	QFP100 (14 x 20)			(PN120005)		(PN210004)	
TMP87CP23FG								
TMP87CM24AFG	TMP87PP24AFG	LQFP100 (14 x 14)		BM87CP24F0A	(PN120013)	—	(PN210022)	
TMP87CP24AFG								
TMP87CH29NG	TMP87PM29NG	SDIP64			PN110005		—	
TMP87CK29NG				BM87CM29U0B				
TMP87CH29UG	TMP87PM29UG	LQFP64 (10 x 10)			(PN120022)		(PN210031)	
TMP87CK29UG								
TMP87CM29UG	TMP87PM40AFG	QFP64 (14 x 20)			PN120014		PN210010	
TMP87CK40AFG								
TMP87CM40AFG	TMP87PM40ANG	SDIP64		BM87CK40N0B				
TMP87CK40ANG					(PN110005)		—	
TMP87CM40ANG								

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.
 #1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.
 #2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."
 ※: Emulation Technology products are available from Micron, Inc.
 Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
 As a guideline, the adapter should be replaced after 2,000 writes.

			Notes
MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	
—	—	BM11616	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
PN210020A	(PN210021)	BM11594	—
IC253-030-0002-B		TMP87P808MG: BM11616 TMP87P808NG: BM11122	One IC socket (IC253-030-0002-B) is supplied with the PN200007. The IC socket (IC253-030-0002-B) is available from Yamaichi Electronics, Co. Ltd. The TMP87C408DMG is packaged in a 30-pin SSOP. However, the OTP version is not available in the same package. If necessary, use the 28-pin TMP87P808MG (SOP) or TMP87P808NG (SDIP) with on-chip OTP.
		BM11616	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
		BM11122	—
	—	BM11616	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
—		BM11122	—
		BM11616	The package converter (AS-DIP.6-028-SO08-1) is made by Emulation Technology, Inc. (ET). ※
		BM11122	—
PN210011A	PN210012	BM11199	(Note 1)
—	—	BM11198	
PN210008	PN210009	BM11605	
PN210002	PN210003	BM11604	
PN210008	PN210009	BM11605	
PN210002	PN210003	BM11604	—
PN210005A	(PN210006)	BM11585	
PN210023	(PN210024)	BM11627	
—	—	BM11143	
PN210033	(PN210032)	BM11617	
PN210011A	PN210012	BM11137	(Note 1)
—	—	BM11714	—

TLCS-870 series Development System (2/2)

□ Software Products

Language Tool	Test Tool
C/C-Like Compiler & Assembler Set (%1)	Debugger (%1)
SW87YN0-ZCJ: 1 license (Japanese edition)	SW87DN9-ZCK: 1 license (Japanese edition)
SW87YN0-ZCE: 1 license (English edition)	SW87DN9-ZCF: 1 license (English edition)
SW87YN3-ZCJ: 10 licenses (Japanese edition)	SW87DN3-ZCK: 10 licenses (Japanese edition)
SW87YN3-ZCE: 10 licenses (English edition)	SW87DN3-ZCF: 10 licenses (English edition)

□ Hardware Products

Target MCU			Test Tools		Accessories			
Part Number	OTP/Flash MCU	Package	Controller	Emulation Pod	MCU Probe (#1, #2)	Package Converter (#1, #2)	QFP Adapter (#1)	
TMP87C840FG	TMP87PH40AFG	QFP64 (14 x 20)		BM87CK40N0B	PN120014		PN210010	
TMP87CC40FG								
TMP87CH40FG								
TMP87C840NG	TMP87PH40ANG	SDIP64			(PN110005)		—	
TMP87CC40NG								
TMP87CH40NG								
TMP87C841FG	TMP87PM41FG	QFP64 (14 x 20)			PN120014	—	PN210010	
TMP87CC41FG								
TMP87CH41FG								
TMP87CK41FG	TMP87PM41NG	SDIP64		BM87CM41N0A			—	
TMP87CM41FG								
TMP87C841NG								
TMP87CC41NG	TMP87PM41UG	LQFP64 (10 x 10)			(PN110005)			
TMP87CH41NG								
TMP87CK41NG								
TMP87C841UG	TMP87PM41UG	LQFP64 (10 x 10)				PN120035	PN210031	
TMP87CC41UG								
TMP87CH41UG								
TMP87CK41UG	TMP87PH46NG	SDIP42	BM1022R0B		(PN100002 + PN200001)		—	
TMP87CM41UG								
TMP87C446NG								
TMP87C847LUG	TMP87PH47LUG	QFP44 (10 x 10)		BM87CH47U0B	(PN120011)		(PN210019)	
TMP87CH47LUG								
TMP87C447UG								
TMP87C847UG	TMP87PM48UG	LQFP64 (10 x 10)		BM87CH48U0A	(PN120022)		(PN210031)	
TMP87CH47UG								
TMP87C448DFG								
TMP87C848DFG	TMP87PM53FG	QFP80 (14 x 20)		BM87CM53F0A	(PN120004)	—	(PN210001)	
TMP87CH48DFG								
TMP87CM48DFG								
TMP87C848UG	TMP87PS68DFG	LQFP80 (12 x 12)		BM87CS68DF0A	(PN120006A)		(PN210007)	
TMP87CH48UG								
TMP87CM48UG								
TMP87CM53FG	TMP87PM70FG	QFP80 (14 x 20)		BM87CK70F0B	PN120004		PN210001	
TMP87CS68DFG								
TMP87CM70BFG								
TMP87CS71BFG	TMP87PM74FG			BM87CM75F0A				
TMP87CH74AFG								
TMP87CM74AFG								
TMP87CH75FG	TMP87PM75FG							
TMP87CM75FG								
TMP87CC78FG								
TMP87CH78FG	TMP87PM78FG	QFP100 (14 x 20)		BM87CM78F0A	(PN120005)		(PN210004)	
TMP87CK78FG								
TMP87CM78FG								

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.

#1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.

#2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."

Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
As a guideline, the adapter should be replaced after 2,000 writes.

MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	Notes
PN210011A	PN210012	BM1137	(Note 1)
—	—	BM1136	—
PN210011A	PN210012	BM1137	(Note 1)
—	—	BM1136	—
PN210033	PN210032	BM11621	—
—	—	BM1193	—
PN210020A	(PN210021)	BM11594	—
PN210026	PN210027	BM11647	—
PN210033	(PN210032)	BM11617	—
PN210002	(PN210003)	BM11604	—
PN210008	(PN210009)	BM11605	—
PN210002	PN210003	BM11550	To connect the supplied probe (which has two 40-pin flat cables with the HIF3BA-40D-2.54R sockets) to the target system, the target system must have the pin header HIF3BA-40PA-2.54DSA or its equivalent. The socket (HIF3BA-40D-2.54R) and the pin header (HIF3BA-40PA-2.54DSA) are available from Hirose Electric, Co., Ltd.
		BM11607	
		BM11620	
PN210005A	(PN210006)	BM11624	—
		BM11588	—

TLCS-870/X series Development System

□ Software Products

Language Tool	Test Tool
C Compiler & Assembler Set (%1)	Debugger (%1)
SW88YN0-ZCK: 1 license (Japanese edition)	SW88DN9-ZFJ: 1 license (Japanese edition)
SW88YN0-ZCF: 1 license (English edition)	SW88DN9-ZFE: 1 license (English edition)
SW88YN3-ZCK: 10 licenses (Japanese edition)	SW88DN3-ZFK: 10 licenses (Japanese edition)
SW88YN3-ZCF: 10 licenses (English edition)	SW88DN3-ZFF: 10 licenses (English edition)

□ Hardware Products

Target MCU			Test Tools					
Part Number	OTP/Flash MCU	Package	Controller	Emulation Pod	MCU Probe (#1, #2)	Package Converter (#1, #2)		
TMP88CP34FG	TMP88PS34FG	QFP44 (14 x 14)		BM88CS34N0A-M15	PN120066			
TMP88CS34FG								
TMP88CP34NG								
TMP88CS34NG	TMP88PS34NG	SDIP42			(PN110016)			
TMP88CM38AF	TMP88PS38FG	QFP44 (14 x 14)			PN120058			
TMP88CM38BFG	TMP88PS38BFG				PN120064			
TMP88CP38AF	TMP88PS38FG				PN120058			
TMP88CP38BFG	TMP88PS38BFG				PN120064			
TMP88CS38FG	TMP88PS38FG				PN120058			
TMP88CS38BFG	TMP88PS38BFG				PN120064			
TMP88CM38ANG	TMP88PS38NG				SDIP42	BM1040R0A/ BM1055R0B		(PN110013)
TMP88CM38BNG	TMP88PS38BNG	PN110015						
TMP88CP38ANG	TMP88PS38NG	(PN110013)						
TMP88CP38BNG	TMP88PS38BNG	PN110015						
TMP88CS38NG	TMP88PS38NG	(PN110013)						
TMP88CS38BNG	TMP88PS38BNG	PN110015						
TMP88CH40MG	TMP88PH40MG	SOP28						PN100003 + PN200008
TMP88CH40IMG								
TMP88CH40NG	TMP88PH40NG	SDIP28			PN100003 + PN200004			
TMP88CH41NG	TMP88PH41NG	SDIP42			PN100002 + PN200001			
TMP88CH41UG	TMP88PH41UG	LQFP44 (10 x 10)		BM88CS43F0A-M15				
TMP88CH41IUG ++					PN120011			
TMP88CH41SUG ++								
TMP88CS42FG	TMP88PS42FG	QFP64 (14 x 20)			PN120014			
TMP88CS42NG	TMP88PS42NG	SDIP64			PN110005			
TMP88CS43FG	TMP88PS43FG	QFP80 (14 x 20)			(PN120004)			
TMP88CW44FG **	TMP88FW44FG	QFP100 (14 x 20)	T.B.D.	T.B.D.	T.B.D.			
TMP88CW45FG **	TMP88FW45FG	QFP80 (14 x 20)						
TMP88CU74FG	TMP88PU74FG				(PN120004)			
TMP88CP77FG	TMP88PU77FG	QFP100 (14 x 20)	BM1055R0B	BM88CP77F0A				
TMP88CS77FG					(PN120005)			
TMP88CU77FG								

%1: The Japanese edition runs on Japanese Windows, and the English edition runs on English Windows.

#1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.

#2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."

** : Under development

++ : Being planned

Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.
As a guideline, the adapter should be replaced after 2,000 writes.

Accessories				Notes
QFP Adapter (#1)	MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	
	IC149-044-039-B5		BM11675	One IC socket (IC149-044-039-B5) is supplied with the PN120066. The IC socket is (IC149-044-039-B5) is available from Yamaichi Electronics, Co., Ltd.
	—		BM11174A	—
	IC149-044-039-B5		BM11675	One IC socket (IC149-044-039-B5) is supplied with the PN120058 or PN120064. The IC socket is (IC149-044-039-B5) is available from Yamaichi Electronics, Co., Ltd.
—		—		
			BM11174A	—
	IC253-028-0003-B		BM11695	One IC socket (IC253-028-0003-B) is supplied with the PN200008. The IC socket is (IC253-028-0003-B) is available from Yamaichi Electronics, Co., Ltd.
	—		BM11196	
			BM11205	—
PN210019	PN210020A	PN210021	BM11706	
PN210010	PN210011A	PN210012	BM11200	(Note 1)
—	—	—	BM11199	
(PN210001)	PN210002	(PN210003)	BM11680	
T.B.D.	T.B.D.	T.B.D.	T.B.D.	
(PN210001)	PN210002	(PN210003)	BM11631	—
(PN210004)	PN210005A	(PN210006)	BM11650	

TLCS-900 Family Development System (1/2)

□ Software Products

Toshiba Integrated Development Environment (TIDE)		Real-Time OS
C Compiler	Build Manager, Debugger & Simulator	μITRON 3.0
SW96CN0-ZCC: 1 license SW96CN3-ZCC: 10 licenses	SW96MN0-ZCC: 1 license SW96MN3-ZCC: 10 licenses	SW96RN2-ZCC: Object code can be freely copied. SW96RNC-ZCC: Object code can be freely copied and comes with source code.

□ Hardware Products

Target MCU			Test Tools		Accessories			
Part Number	OTP/Flash MCU	Package	Controller	Emulation Pod (#3)	MCU Probe (#1, #2)	Package Converter (#1, #2)	QFP Adapter (#1)	
TMP96C031ZFG	—	QFP64 (14 x 20)	BM1055R0B	BM96C031F0A	(PN110007)	(PN120007)	(PN210010)	
TMP96CM40FG	TMP96PM40FG							
TMP96C041BFG		QFP80 (14 x 20)		BM96C141F0D-M15	(PN120009)		(PN210001)	
TMP96C141BFG	—							
TMP95C001FG		QFP64 (14 x 14)		BM95C001F0B-M15	(PN120039A)		(PN210025)	
TMP95CS54FG	TMP95PS54FG	LQFP100 (14 x 14)		BM95CS54F0A-M15	(PN120013)		(PN210022)	
TMP95C061BDFG		LQFP100 (14 x 14)		BM95C061F0C-M15				
TMP95C063DFG	—	LQFP144 (20 x 20)	BM1040R0A/ BM1055R0B	BM95C063F0B-M15	(PN120027)		(PN210034)	
TMP95CS64FG	TMP95PW64FG							
TMP95CW64FG								
TMP95C265FG	—			BM95CS64F0B-M15		—		
TMP95CW65FG		LQFP100 (14 x 14)			(PN120013)		(PN210022)	
TMP95CS66FG	TMP95PW64FG							
TMP95CU54AFG				BM95FW54F0A-M15				
TMP95CW54AFG	—							
TMP94C241CFG		QFP160 (28 x 28)	BM1056R0B	BM94C241F0A	(PN120040A)		(PN210028)	
TMP94C251ADFG		LQFP144 (20 x 20)		BM94C251F0A	(PN120050)		(PN210034)	
TMP93CS20FG	TMP93PW20AFG	LQFP144 (16 x 16)		BM93CS20F0B-M15	(PN120044)		(PN210043)	
TMP93CS32FG	TMP93PW32FG	QFP64 (14 x 14)		BM93CS32F0B-M15	(PN120039A)		(PN210025)	
TMP93CS36UG	—	LQFP44 (10 x 10)				PN120063	PN210019	
TMP93CS40DFG	TMP93PS40DFG							
TMP93CW40DFG	TMP93PW40DFG							
TMP93CM40DFG	TMP93PS40DFG	LQFP100 (14 x 14)		BM93CM40F0C-M15	(PN120013)		(PN210022)	
TMP93CS41DFG	—							
TMP93CW41DFG								
TMP93CS42ADFG	TMP93PS42ADFG			BM93CS42F0B-M15				
TMP93CU44DFG	TMP93PW44ADFG	QFP80 (14 x 20)	BM1040R0A/ BM1055R0B		PN120009		PN210001	
TMP93CW44DFG				BM93CS44F0B-M15		—		
TMP93CS44FG	TMP93PS44FG	LQFP80 (12 x 12)			(PN120042)		(PN210007)	
TMP93CS45FG	—							
TMP93CW46AFG	TMP93PW46AFG	LQFP100 (14 x 14)		BM93CW46F0B-M15	(PN120013)		(PN210022)	
TMP93CF76FG	TMP93PF76FG							
TMP93CF77FG								
TMP93CW76FG		QFP100 (14 x 20)		BM93CW76F0A-M15	(PN120023B)		(PN210004)	
TMP93CU76FG	TMP93PW76FG							
TMP93CT76FG								

● The real-time OS requires a license agreement. For details, please contact your local Toshiba sales representative.

#1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.

#2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."

#3: The model25 and model15 pods can use the same accessories.

Note 1: The OTP programming adapter durability is lowered when used with lead (Pb)-free packaged products.

As a guideline, the adapter should be replaced after 2,000 writes.

MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	Notes
PN210011A	(PN210012)	—	The BM96C031F0A requires a dedicated adapter for connection to the controller (BM1055R0B).
		BM11539	
PN210002	(PN210003)	—	
PN210026	(PN210027)	—	
PN210023	(PN210024)	BM11629	
PN210036	(PN210035)	—	
		BM11629	
PN210023	(PN210024)	—	—
		BM11629	
		—	
PN210030	(PN210029)	—	
PN210036	(PN210035)	—	
(PN210044)	(PN210045)	BM11641	
PN210026	(PN210027)	BM11632	
PN210020A	PN210021	—	
		BM11629	
PN210023	(PN210024)	BM11109	
		—	—
		BM11109	
PN210002	PN210003	BM11652	
PN210008	(PN210009)	BM11628	—
		—	
PN210023	(PN210024)	BM11629	
		—	
PN210005A	(PN210006)	BM11646	—
		—	

TLCS-900 Family Development System (2/2)

Software Products

Toshiba Integrated Development Environment (TIDE)		Real-Time OS
C Compiler	Build Manager, Debugger & Simulator	μITRON 3.0
SW96CN0-ZCC: 1 license SW96CN3-ZCC: 10 licenses	SW96MN0-ZCC: 1 license SW96MN3-ZCC: 10 licenses	SW96RN2-ZCC: Object code can be freely copied. SW96RNC-ZCC: Object code can be freely copied and comes with source code.

Hardware Products

Target MCU			Test Tools		Accessories			
Part Number	OTP/Flash MCU	Package	Controller	Emulation Pod (#3)	MCU Probe (#1, #2)	Package Converter (#1, #2)	QFP Adapter (#1)	
TMP92CM22FG		LQFP100 (14 x 14)		BM92CM22F0A-M15	(PN120013)		(PN210022)	
TMP92C820FG				BM92C820F0A-M15				
TMP92CA25FG		LQFP144 (16 x 16)		BM92CA25F0A-M15	(PN120044)		(PN210043)	
TMP92CH21FG				BM92CH21F0A-M15				
TMP92CD23AFG **	TMP92FD23AFG **	LQFP100 (14 x 14)		T.B.D	T.B.D	T.B.D	T.B.D	
TMP92CD23ADFG **	TMP92FD23ADFG **	QFP100 (14 x 20)						
TMP92CY23FG **	TMP92FY23FG **	LQFP100 (14 x 14)	BM1040R0A BM1055R0B	BM92CY23F0A-M15 **	(PN120013)		(PN210022)	
TMP92CY23DFG **	TMP92FY23DFG **	QFP100 (14 x 20)				PN120068	(PN210004)	
TMP92CZ26XBG **		FBGA228 (15 x15)		T.B.D	T.B.D	T.B.D	T.B.D	
TMP92CM27FG		LQFP144 (16 x 16)		BM92CM27F0A-M15	(PN120044)		(PN210043)	
TMP92CD54IFG	TMP92FD54AIFG			BM92CY54F0A-M15				
TMP92FD54AIFG								
TMP91CU10FG	TMP91PW10FG	LQFP100 (14 x 14)		BM91CU10F0B-M15	(PN120013)		(PN210022)	
TMP91CW11FG	TMP91PW11FG			BM91CW11F0B-M15				
TMP91CW12FG	TMP91PW12FG			BM91CW12F0A-M15				
TMP91CW12AFG	TMP91FY42FG **			BM91CW12AF0A-M15				
TMP91C815FG		TQFP128 (14 x 14)	BM1040R0A	BM91C815F0A-M15	(PN120057)		(PN210053)	
TMP91C016FG		LQFP100 (14 x 14)		BM91C016F0A-M15	(PN120013)		(PN210022)	
TMP91CW18AFG	TMP91PW18AFG	QFP80 (14 x 20)	BM1040R0A BM1055R0B	BM91CW18F0A-M15	(PN120009)		(PN210001)	
TMP91C219FG		LQFP100 (14 x 14)		BM91C219F0A-M15	(PN120013)		(PN210022)	
TMP91C820AFG		LQFP144 (16 x 16)		BM91CM20F0A-M15	(PN120044)		(PN210043)	
TMP91CY22FG	TMP91FY42FG **		BM1040R0A	BM91CW12AF0A-M15				
TMP91CY22IFG		LQFP100 (14 x 14)					(PN210022)	
TMP91C824FG			BM1040R0A	BM91C824F0A-M15				
TMP91C025FG			BM1055R0B	BM91C025F0A-M15				
TMP91CK27UG								
TMP91CP27RUG								
TMP91CP27UG	TMP91FY27UG	LQFP64 (10 x 10)	BM1040R0A	BM91CW12AF0A-M15	(PN120013)	PN120065	PN210031	
TMP91CU27RUG								
TMP91CU27UG								
TMP91CW28FG	TMP91FY28FG **			BM91CW28F0A-M15 **				
TMP91CY28FG								
TMP91C829FG		LQFP100 (14 x 14)	BM1040R0A	BM91C829F0A-M15			(PN210022)	
TMP91C630FG			BM1055R0B	BM91C630F0A-M15				
TMP91CW40FG **	TMP91FW40FG **			BM91CW40F0A-M15 **				
TMP91CW60FG ++	TMP91FW60FG **		T.B.D.	T.B.D.	T.B.D.	T.B.D.	T.B.D.	
TMP91CW60DFG ++	TMP91FW60DFG **	QFP100 (14 x 20)						
TMP91CP82TFG	TMP91PP82TFG	LQFP100 (14 x 14)	BM1040R0A BM1055R0B	BM91CP82F0B-M15 **	(PN120013)		(PN210022)	

- The real-time OS requires a license agreement. For details, please contact your local Toshiba sales representative.
 - #1: Those enclosed within parentheses are spare parts. One each is supplied with an emulation pod.
 - #2: One QFP adapter and one pin protector are supplied with an MCU probe or a package converter whose name begins with "PN12."
 - #3: The model25 and model15 pods can use the same accessories.
 - ** : Under development
 - ++ : Being planned
- Note1: For details of the dedicated cable, please contact your local Toshiba sales representative.

OTP/MCU Mount Adapter (#1)	Pin Protector (#1)	OTP/Flash Programming Adapter	Notes
PN210023	(PN210024)		A dedicated cable is required in combination to perform performance analysis by using BM92CM22F0A-M15 and BM1055R0B. (Note1)
			A dedicated cable is required in combination to perform performance analysis by using BM92C820F0A-M15 and BM1055R0B. (Note1)
(PN210044)	(PN210045)	—	A dedicated cable is required in combination to perform performance analysis by using BM92CA25F0A-M15 and BM1055R0B. (Note1)
			A dedicated cable is required in combination to perform performance analysis by using BM92CH21F0A-M15 and BM1055R0B. (Note1)
T.B.D	T.B.D	T.B.D	—
PN210023	(PN210024)	PN410106	A dedicated cable is required in combination to perform performance analysis by using BM92CY23F0A-M15 and BM1055R0B. (Note1)
PN210005A	(PN210006)	PN410111	
T.B.D	T.B.D	T.B.D	—
(PN210044)	(PN210045)		A dedicated cable is required in combination to perform performance analysis by using BM92CM27F0A-M15 and BM1055R0B. (Note1)
		—	A dedicated cable is required in combination to perform performance analysis by using BM92CY54F0A-M15 and BM1055R0B. (Note1)
PN210023	(PN210024)	BM11629	The 2-V conversion adapter (PN410001) is required to operate the TMP91CU10FG off a 2-V power supply on the target board.
		BM11649	—
		PN410106 **	The BM91CW12AF0A-M15 does not support 2-V operation.
PN210054	(PN210055)		The BM91C815F0A-M15 does not support 2-V operation.
PN210023	(PN210024)	—	The BM91C016F0A-M15 does not support 2-V operation.
PN210002	(PN210003)	BM11679 **	—
PN210023	(PN210024)	—	
(PN210044)	(PN210045)		
		PN410106 **	The BM91CW12AF0A-M15 does not support 2-V operation.
PN210023	(PN210024)		The BM91C824F0A-M15 does not support 2-V operation.
		—	—
PN210033	PN210032	PN410105	The BM91CW12AF0A-M15 does not support 2-V operation.
		PN410106	—
PN210023	(PN210024)	—	
		—	
T.B.D	T.B.D	T.B.D	
PN210023	(PN210024)	BM11671	

TX19 series Development System

● The real-time OS requires a license agreement. For details, please contact your local Toshiba sales representative.

#1: DSU PROBE model110 is a simplified version of DSU PROBE model120.

** : Under development

□ Software Products

Toshiba Integrated Development Environment (TIDE)		Real-Time OS
C Compiler	Build Manager, Debugger & Simulator	μITRON 3.0
SW19CN0-ZCC: 1 license SW19CN3-ZCC: 10 licenses	SW19MN0-ZCC: 1 license SW19MN3-ZCC: 10 licenses	SW19RN2-ZCC: Object code can be freely copied. SW19RN3-ZCC: The Green Hills Software (GHS) compiler is supported. Object can be freely copied. SW19RNC-ZCC: Object code can be freely copied and comes with source code. SW19RND-ZCC: The Green Hills Software (GHS) compiler is supported. Object can be freely copied and comes with source code.

□ Hardware Products

Target MCU	Test Tool	Notes
Part Number	DSU PROBE for N-Wire	
TMP1940FDBFG	BM1200R0A	The BM1200R0A is shipped with the TX19 Family DSU PROBE debugger, a dedicated debugger for the TMP1940/42.
TMP1942FDUG		
TMP1942FDXBG **		Does not support the debugger shipped with the BM1200R0A. Please separately order the TX19 Series integrated development environment.
TMP1962C10BxBG **		
TMP1962F10AxBG		You can download firmware from the TOSHIBA Microcomputer Development Systems Web site.

TX19A series Development System

□ Software Products

Toshiba Integrated Development Environment (TIDE)		Real-Time OS
C Compiler	Build Manager, Debugger & Simulator	μITRON 4.0
SW1ACN0-ZCC: 1 license SW1ACN3-ZCC: 10 licenses	SW1AMN0-ZCC: 1 license SW1AMN3-ZCC: 10 licenses	SW1ARN5-ZCC: Object code can be freely copied. SW1ARNF-ZCC: Object code can be freely copied and comes with source code.

□ Hardware Products

Target MCU	Test Tool	Notes
Part Number	DSU PROBE model110/120 (#1)	
TMP19A43FDXBG **	BM1210R0A BM1211R0A	Incorporates a license to download the TX19A Series integrated development environment dedicated to the DSU PROBE model110/120 (SW1AMN5-Z0C). (Simulators are not supported.) Firmware for the TX19A43/51/64/71 is under development.
TMP19A64F20AxBG **		
TMP19A70CYUG		
TMP19A70CYFG		
TMP19A70FYUG		
TMP19A70FYFG		
TMP19A71CYUG **		
TMP19A71CYFG **		
TMP19A71FYUG **		
TMP19A71FYFG **		
TMP19A51FYFG **		

Accessory Tools

QFP Adapter Footprint

The QFP adapter provides a convenient way to plug the MCU probe of an emulation pod to your target system. Since the adapter is designed to be compatible with many QFP packages, its footprint slightly differs from those of the MCUs and OTPs. When both a QFP adapter and an MCU or OTP are to be mounted on the same board, it must be designed to accommodate both their dimensions. (Toshiba's QFP adapters/Pin Protectors are compatible with the Tokyo Eletec products. For the recommended footprint dimensions, please check out the Web/Pin Protectors page of Tokyo Eletec: http://www.tetc.co.jp/e_tet.htm)

Tokyo Eletec QFP Adaptors and Pin Protectors

QFP adaptors and pin protectors compatible with Toshiba's are available from Tokyo Eletec Corporation.

IC Package (Unit: mm)			QFP Adapter		Pin Protector	
Package	Body Size	Lead Pitch	Toshiba Part Number	Tokyo Eletec Part Number	Toshiba Part Number	Tokyo Eletec Part Number
QFP44	10x10	0.8	PN210019	TQPACK044SA	PN210021	TQSOCKET044SAG
QFP64	14x20	1	PN210010	TQPACK064RZ	PN210012	TQSOCKET064RZG
QFP64	14x14	0.8	PN210025	TQPACK064SA	PN210027	TQSOCKET064SAG
QFP64	10x10	0.5	PN210031	TQPACK064SD	PN210032	TQSOCKET064SDG
QFP80	14x20	0.8	PN210001	TQPACK080RA	PN210003	TQSOCKET080RAG
QFP80	12x12	0.5	PN210007	TQPACK080SD	PN210009	TQSOCKET080SDG
QFP80	14x14	0.65	PN210017	TQPACK080SB	PN210016	TQSOCKET080SBG
QFP100	14x20	0.65	PN210004	TQPACK100RB	PN210006	TQSOCKET100RBG
QFP100	22x22	0.8	PN210015	TQPACK100SA	PN210014	TQSOCKET100SAG
QFP100	14x14	0.5	PN210022	TQPACK100SD	PN210024	TQSOCKET100SDG
QFP120	14x14	0.4	PN210050	NQPACK120SE	PN210052	YQPACK120SE
QFP128	14x14	0.4	PN210053	NQPACK128SE	PN210055	YQPACK128SE
QFP144	16x16	0.4	PN210043	NQPACK144SE	PN210045	YQPACK144SE
QFP144	20x20	0.5	PN210034	TQPACK144SD	PN210035	TQSOCKET144SDG
QFP160	28x28	0.65	PN210028	TQPACK160SB	PN210029	TQSOCKET160SBG

Yamaichi Electronics

IC Sockets

The indicated part numbers are Yamaichi's.

Part Number	IC Package (Unit: mm)		
	Package	Body Size	Lead Pitch
IC149-044-039-B5	QFP44	14X14	0.8
IC149-044-052-B5	QFP44	10X10	0.8
IC149-120K13207-0B	QFP120	28X28	0.8
IC253-028-0003-B	SOP28	—	—
IC253-030-0002-B	SSOP30	—	—
IC253-020-0004-B	SOP	—	—

Emulation Technology (ET)

Package Converters

The indicated part numbers are ET's.

Part Number	Conversion
AS-DIP.3-016-SO03-1	DIP16 → SOP16
AS-DIP.3-020-SO03-1	DIP20 → SOP20
AS-DIP.6-028-SO08-1	DIP28 → SOP28
AS-DIP.6-040-SO11-1	DIP40 → SSOP40
AS-SDIP-QF52S-47C800F	SDIP42 → QFP44
AS-SDP.4-028-SO05-2	SDIP28 → SOP28

Accessory Manufacturers and Distributors

Please check out the latest product information before designing pc boards or purchasing accessories.

TOKYO ELETECH CORPORATION
YAMAICHI ELECTRONICS Co., Ltd.

http://www.tetc.co.jp/e_tet.htm
http://www.yamaichi.co.jp/index_e.shtml

**Toshiba America
Electronic Components, Inc.**

Headquarters-Irvine, CA
19900 MacArthur Boulevard,
Suite 400, Irvine, CA 92612, U.S.A.
Tel: (949)623-2900 Fax: (949)474-1330

Boulder, CO (Denver)
3100 Arapahoe #500,
Boulder, CO 80303, U.S.A.
Tel: (303)442-3801 Fax: (303)442-7216

Buffalo Grove (Chicago)
2150 E. Lake Cook Road, Suite 310,
Buffalo Grove, IL 60089, U.S.A.
Tel: (847)484-2400 Fax: (847)541-7287

Duluth, GA (Atlanta)
3700 Crestwood Pkwy, #160,
Duluth, GA 30096, U.S.A.
Tel: (770)931-3363 Fax: (770)931-7602

Beaverton/Portland, OR
8323 SW Cirrus Drive, Beaverton,
OR 97008, U.S.A.
Tel: (503)466-3721 Fax: (503)629-0827

Raleigh, NC
3120 Highwoods Blvd., #108, Raleigh,
NC 27604, U.S.A.
Tel: (919)859-2800 Fax: (919)859-2898

Richardson, TX (Dallas)
777 East Campbell Rd., #650, Richardson,
TX 75081, U.S.A.
Tel: (972)480-0470 Fax: (972)235-4114

San Jose Engineering Center, CA
1060 Rincon Circle, San Jose, CA 95131, U.S.A.
Tel: (408)526-2400 Fax: (408)526-8910

Wakefield, MA (Boston)
401 Edgewater Place, #360, Wakefield,
MA 01880-6229, U.S.A.
Tel: (781)224-0074 Fax: (781)224-1095

Wixom (Detroit)
48679 Alpha Drive, Suite 100, Wixom,
MI 48393 U.S.A.
Tel: (248)449-6165 Fax: (248)449-8430

Toshiba Electronics do Brasil Ltda.
Rua Afonso Celso, 552-8 andar, C.J. 81
Vila Mariana Cep 04119-002 São Paulo SP, Brasil
Tel: (011)5576-6619 Fax: (011)5576-6607

Toshiba India Private Ltd.
6F DR. Gopal Das Bhawan 28,
Barakhamba Road, New Delhi, 110001, India
Tel: (011)2331-8422 Fax: (011)2371-4603

Toshiba Electronics Europe GmbH

Düsseldorf Head Office
Hansaallee 181, D-40549 D sseldorf,
Germany
Tel: (0211)5296-0 Fax: (0211)5296-400

München Office
B ro M nchen Hofmannstrasse 52,
D-81379, M nchen, Germany
Tel: (089)748595-0 Fax: (089)748595-42

France Branch
Les Jardins du Golf 6 rue de Rome F-93561,
Rosny-Sous-Bois, Cedex, France
Tel: (1)48-12-48-12 Fax: (1)48-94-51-15

Italy Branch
Centro Direzionale Colleoni,
Palazzo Perseo 3,
I-20041 Agrate Brianza, (Milan), Italy
Tel: (039)68701 Fax: (039)6870205

Spain Branch
Parque Empresarial, San Fernando, Edificio Europa,
1ª Planta, E-28831 Madrid, Spain
Tel: (91)660-6798 Fax: (91)660-6799

U.K. Branch
Riverside Way, Camberley Surrey,
GU15 3YA, U.K.
Tel: (01276)69-4600 Fax: (01276)69-4800

Sweden Branch
Gustavslundsv gen 18, 5th Floor,
S-167 15 Bromma, Sweden
Tel: (08)704-0900 Fax: (08)80-8459

**Toshiba Electronics Asia
(Singapore) Pte. Ltd.**
438B Alexandra Road, #06-08/12 Alexandra
Technopark, Singapore 119968
Tel: (6278)5252 Fax: (6271)5155

**Toshiba Electronics Service
(Thailand) Co., Ltd.**
135 Moo 5, Bangkok Industrial Park, Tivanon Road,
Pathumthani, 12000, Thailand
Tel: (02)501-1635 Fax: (02)501-1638

**Toshiba Electronics Trading
(Malaysia) Sdn. Bhd.**

Kuala Lumpur Head Office
Suite W1203, Wisma Consplant, No.2,
Jalan SS 16/4, Subang Jaya, 47500 Petaling Jaya,
Selangor Darul Ehsan, Malaysia
Tel: (03)5631-6311 Fax: (03)5631-6307

Penang Office
Suite 13-1, 13th Floor, Menara Penang Garden,
42-A, Jalan Sultan Ahmad Shah,
10050 Penang, Malaysia
Tel: (04)226-8523 Fax: (04)226-8515

Toshiba Electronics Philippines, Inc.
26th Floor, Citibank Tower, Valero Street, Makati,
Manila, Philippines
Tel: (02)750-5510 Fax: (02)750-5511

Toshiba Electronics Asia, Ltd.

Hong Kong Head Office
Level 11, Tower 2, Grand Century Place, No.193,
Prince Edward Road West, Mongkok, Kowloon, Hong Kong
Tel: 2375-6111 Fax: 2375-0969

Beijing Office
Room 714, Beijing Fortune Building, No.5 Dong San Huan Bei-Lu,
Chao Yang District, Beijing, 100004, China
Tel: (010)6590-8796 Fax: (010)6590-8791

Chengdu Office
Suite 403A, Holiday Inn Crown Plaza 31, Zongfu Street,
Chengdu, 610016, Sichuan, China
Tel: (028)8675-1773 Fax: (028)8675-1065

Qingdao Office
Room 4(D-E), 24F, International Financial Center,
59 Xiang Gang Zhong Road, Qingdao, Shandong, China
Tel: (0532)579-3328 Fax: (0532)579-3329

Toshiba Electronics Shenzhen Co., Ltd.
Room 2601-2609, 2616, Office Tower Shun Hing Square,
Di Wang Commercial Center, 5002 Shennan East Road,
Shenzhen, 518008, China
Tel: (0755)2583-0810 Fax: (0755)8246-1581

Toshiba Electronics (Shanghai) Co., Ltd.

Shanghai Head Office
11F, HSBC Tower, 101 Yin Cheng East Road,
Pudong New Area, Shanghai, 200120, China
Tel: (021)6841-0666 Fax: (021)6841-5002

Hangzhou Office
502 JiaHua International Business Center,
No.28 HangDa Road, Hangzhou, 310007, China
Tel: (0571)8717-5004 Fax: (0571)8717-5013

Nanjing Office
23F Shangmao Century Plaza,
No.49 Zhong Shan South Road, Nanjing, 210005, China
Tel: (025)8689-0070 Fax: (025)8689-0125

Toshiba Electronics (Dalian) Co., Ltd.
14/F, Senmao Building, 147, Zhongshan Road,
Xigang Dist., Dalian, 116011, China
Tel: (0411)8368-6882 Fax: (0411)8369-0822

Tsurong Xiamen Xiangyu Trading Co., Ltd.
14G, International Bank BLDG., No.8 Lujiang Road,
Xiamen, 361001, China
Tel: (0592)226-1398 Fax: (0592)226-1399

Toshiba Electronics Korea Corporation

Seoul Head Office
891, Samsung Life Insurance Daechi Tower 20F, Daechi-dong,
Gangnam-gu, Seoul, 135-738, Korea
Tel: (02)3484-4334 Fax: (02)3484-4302

Gumi Office
6F, Goodmorning Securities Building, 56 Songjung-dong,
Gumi-shi, Gyeongbuk, 730-090, Korea
Tel: (054)456-7613 Fax: (054)456-7617

Toshiba Electronics Taiwan Corporation

Taipei Head Office
17F, Union Enterprise Plaza Building, 109
Min Sheng East Road, Section 3, Taipei, 10544, Taiwan
Tel: (02)2514-9988 Fax: (02)2514-7892

Kaohsiung Office
16F-A, Chung-Cheng Building, 2, Chung-Cheng 3Road,
Kaohsiung, 80027, Taiwan
Tel: (07)237-0826 Fax: (07)236-0046

The information contained herein is subject to change without notice. 021023_D

The information contained herein is presented only as a guide for the applications of our products. No responsibility is assumed by TOSHIBA for any infringements of patents or other rights of the third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of TOSHIBA or others. 021023_C

TOSHIBA is continually working to improve the quality and reliability of its products. Nevertheless, semiconductor devices in general can malfunction or fail due to their inherent electrical sensitivity and vulnerability to physical stress. It is the responsibility of the buyer, when utilizing TOSHIBA products, to comply with the standards of safety in making a safe design for the entire system, and to avoid situations in which a malfunction or failure of such TOSHIBA products could cause loss of human life, bodily injury or damage to property. In developing your designs, please ensure that TOSHIBA products are used within specified operating ranges as set forth in the most recent TOSHIBA products specifications. Also, please keep in mind the precautions and conditions set forth in the Handling Guide for Semiconductor Devices, or TOSHIBA Semiconductor Reliability Handbook etc. 021023_A

The Toshiba products listed in this document are intended for usage in general electronics applications (computer, personal equipment, office equipment, measuring equipment, industrial robotics, domestic appliances, etc.). These Toshiba products are neither intended nor warranted for usage in equipment that requires extraordinarily high quality and/or reliability or a malfunction or failure of which may cause loss of human life or bodily injury (Unintended Usage). Unintended Usage include atomic energy control instruments, airplane or spaceship instruments, transportation instruments, traffic signal instruments, combustion control instruments, medical instruments, all types of safety devices, etc. Unintended Usage of Toshiba products listed in this document shall be made at the customer's own risk. 021023_B

TOSHIBA has made this document deliberately in order to make its contents as accurate as possible. Nevertheless, if any trouble should occur due to any error contained in this document, TOSHIBA shall not have any liability therefore. Also, please keep in mind the precautions and conditions set forth in the "Instruction Manual or Operation Manual of TOSHIBA Products," or "The Precautions or Procedure Files described in the Installation Disk such as Floppy Disk or CD-ROM etc." Please constantly pay attention to the latest information on the TOSHIBA products which is to be released through the web page of TOSHIBA microcomputer development system. (http://www.semicon.toshiba.co.jp/mctool/index_e.htm) 021023_N

The products described in this document may include products subject to the foreign exchange and foreign trade laws. 021023_F

The products described in this document contain components made in the United States and subject to export control of the U.S. authorities. Diversion contrary to the U.S. law is prohibited. 021023_G

TOSHIBA products should not be embedded to the downstream products which are prohibited to be produced and sold, under any law and regulations. 030519_Q

TOSHIBA

TOSHIBA CORPORATION
Semiconductor Company

Website: <http://www.semicon.toshiba.co.jp/eng>

©2005 TOSHIBA CORPORATION

Previous edition: BCE0023C
2005-10(5)PK-PCO

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Toshiba:

[TMP86FS49AFG\(Z\)](#) [TMP86FS49AUG\(JZ\)](#)