

[Amphenol Worldwide](#) [Amphenol RF Employment](#) [Engineering Focus](#) [Quality Focus](#) [Weather and Directions](#)
[Locate A Distributor](#) [Check Distributor Inventory](#)
[Frequency Range Chart](#) [Glossary](#) [Technical Questions](#) [VSWR Calculator](#) [VSWR Chart](#)
[Customer Drawings](#) [Assembly Instructions](#) [Catalog](#)
[Product Overview](#) [Product Search](#) [Cross Reference](#) [QPL Products](#) [Markets Served](#) [Product Literature](#)
[Newsletter](#)
[Customer Extranet](#) [Salesperson Extranet](#) [Vendor Extranet](#) [Employee Extranet](#) [Internal Employee Extranet](#)
[Amphenol RF Manufacturers Rep.](#)

Product Searches

[7/16](#)
[1.0/2.3](#)
[1.6/5.6](#)
[AEI](#)
[AMC](#)
[BNC / RPBNC](#)
[C](#)
[FAKRA SMB](#)
[FME](#)
[HN](#)
[MCX](#)
[Mini BNC](#)
[Mini UHF](#)
[Mini 75 ? SMB](#)
[MMCX](#)
[Precision \(APC\)](#)
[QMA](#)
[SC](#)
[SMA / RPSMA](#)
[SMB](#)
[SMC](#)
[SMP](#)
[SSMB](#)
[TNC / RPTNC](#)
[Triax](#)
[True 75 ? BNC](#)
[Twin BNC](#)
[Twinax](#)
[Type F](#)
[Type G](#)
[Type N](#)
[UHF](#)
[Reverse Polarity](#)
.....
[Adapters](#)
[Tools](#)
[Accessories](#)
.....
[Product Search](#)
.....
[Inventory Search](#)

product details

image
not yet
available

Please note: Images are for reference only

Amphenol Part Number: 082-61
Product Series: [Type N](#)
Product Type: [Connectors](#) » [Cable](#)
Body Plating: [Nickel](#)
Cable Group: [G4](#)
Cable Type: [213,9](#)
Connector Body Style: [Straight](#)
Contact Plating: [Nickel](#)
Gender: [Plug](#)
Impedance: [50 Ohm](#)
RoHS Certificate: [Yes](#)
IGS File: [Yes](#)
More Information: [Distributor Inventory](#)