



D



1

0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN-LEAD IN LOCALIZED TIN-LEAD PLATE AREA OVER 0.00130 [.000050] MIN NICKEL.

2

WIRE RANGE: 0.12 – 0.4mm² (26–22 AWG).

3

INSULATION RANGE: 1.20–1.75[.047–.069] DIA.



4

DIMENSIONS IN BRACKETS ARE IN INCHES.

5


0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA AND 0.00254 [.000100] MIN BRIGHT TIN IN LOCALIZED TIN PLATE AREA OVER 0.00130 [.000050] MIN NICKEL.

C



SECTION A–A
SCALE 20:1

B



SECTION B–B
SCALE 20:1

5	0.20 [.008] PH BRZ	1–770902–1
5	0.20 [.008] BRASS	1–770902–0
1	0.20 [.008] PH BRZ	770902–6
PRE–TIN	0.20 [.008] PH BRZ	770902–4
1	0.20 [.008] BRASS	770902–3
PRE–TIN	0.20 [.008] BRASS	770902–1
FINISH	MATERIAL	PART NUMBER

A

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. HOOVER 16OCT02		 TE Connectivity							
		CHK C. JONES 16OCT02									
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME SOCKET, MINI UNIVERSAL MATE-N-LOK(TM)							
		APVD C. JONES 16OCT02									
		PRODUCT SPEC —									
		APPLICATION SPEC —									
		SIZE A2		CAGE CODE 00779		DRAWING NO C=770902		RESTRICTED TO —			
MATERIAL —		FINISH —		WEIGHT —							
CUSTOMER DRAWING				SCALE 10:1		SHEET 1 of 1		REV P1			