

Date: 10/27/2008

VARISTOR SPECIFICATION SHEET

MAIDA STYLE NUMBER D6121ZOV300RA05

MAIDA ITEM NUMBER 01-0121

Electrical Specifications

Continuous AC Voltage	30	VAC
Continuous DC Voltage	38	VDC
Maximum DC Leakage @ 38 VDC	200	uA
Low Varistor Voltage Limit	42	VDC
High Varistor Voltage Limit	52	VDC
Nominal Varistor Voltage	47	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	93	V
Maximum Clamp Voltage Test Current	5	A
Peak Current Rating (1 Pulse)	1000	A
Peak Current Rating (2 Pulse)	500	A
Energy Rating (8X20us)	6.8	J
Energy Rating (10X1000us)	6.8	J
Typical Capacitance	5140	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ


Thermal Specifications

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C

Notes

Physical Specifications

Lead Style	110B1
X Nominal	0.3 in.
X Tolerance	0.04 in.
Lead Length Nominal	1.00 in.
Lead Length Tolerance	min. in.
Y Nominal	0.075 in.
Y Tolerance	0.03 in.
d Nominal	0.032 in.
Wire Gauge	20 AWG
Minimum Marking	Z300-05UL
Nominal Disk Size	10 mm
D Maximum	0.472 in.
T Maximum	0.19 in.
H Maximum	0.597 in.



* Contact Maida for a more detailed configuration drawing.

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	
CSA File Number	
VDE File Number	
SEV File Number	



DEVELOPMENT COMPANY

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194