

Features

- Small Size
- Low Ripple
- Low Loss


Description

Surface mount, silver (Ag) coated ceramic filter. Developed for use in Digital Audio Broadcast Applications.

Weight: 0.4 grams typical

Material: Filter is composed of a ceramic block plated with Ag.

Filter complies with RoHS standards.



Electrical Specifications

Parameter	Frequency MHz	Typical @ 25°C	Specification @ 25°C	Spec over -40°C to +85°C
TX to Antenna Response				
Passband Iloss	1452 - 1492	0.5	-0.8	-1.0
Passband Ripple	1452 - 1492	0.2	0.4	0.4
Passband Return Loss @ TX	1452 - 1492	-15.0	-10.0	-10.0
Passband Return Loss @ Ant	1452 - 1492	-15.0	-10.0	-10.0
Attenuation	880 - 960	-32.5	-30.0	-30.0
	1800 - 2180	-26.0	-22.0	-22.0
Power into any port		1 Watt max		

Note: Supplier shall test each filter to the critical electrical specifications of the above table. Any subsequent audits may deviate from in value due to measurement repeatability among different test systems. Such deviations shall not exceed the following limits:

Specification Allowance


Insertion Loss	0.1 dB
Return Loss	1.0 dB
Stopbands	1.0 dB

*This product is covered by one or more of the following U.S. and foreign patents including: US 4,692,726;US 4,742,562; US 4,800,348;US 4,829,274;US 5,146,193;EP 0573597;DE 0573597;FR 0573597;JP 508149/92;KR 142171;US 5,162,760;US 5,218,329;US 5,250,916;US 5,327,109;US 5,488,335;CA 2114029;FR 9306297;GB 2273393;JP 3205337;KR 115113;CN 93106228.4;US 5,512,866;EP 0706719;DE 0706719;FR 0706719;GB 0706719;CN 95190359.4;US 5,602,518;US 5,721,520;US 5,745,018;EP 0910875;DE 0910875;DK 0910875;FR 0910875;GB 0910875;JP 50518298;KR 10-323013;US 5,994,978;US 6,462,629;CN 00610420.4;US 6,559,735;US 6,650,202;US 6,834,429. Other US and foreign patents pending.

CTS Corporation 2006 reserves all copyrights in the layout, design and configuration of the patterns on this product.


Mechanical Drawing

Rev 0 – Origin Date: March 7, 2006 – Revision Date: March 7, 2006




Dim	Nominal (mm)	Tolerance (mm) +/- or max/min
A		
B	5.58	Max
C		
D	1.03	0.25
E	3.28	0.25
F		
G	1.4	0.13
H	0.51	0.13
I	0.6	0.13
J	1.24	0.13
K	0.38	0.25
L	4.99	Max
M	3.2	Max

Electrical response





PCB Layout



Packaging and Marking

DIMENSION	UNITS	SPECIFICATION
REEL DIAMETER	mm	12
REEL WEIGHT	kg	1.2
REEL QUANTITY	ea.	1000

Customer Feed Direction
 → → →



MODEL NO.	Wo	Ao	Bo	Ko	Po
CER0074	12.0/(0.472)	5.36/(0.211)	5.77/(0.227)	3.73/(0.147)	8.0/(0.315)