

MOS FET Relays


G3VM-81GR1

New MOS FET Relay Designed for Switching Minute and Analog Signals, SOP Package.

- New model for 80-V loads.
- Low $C \times R$ of 32.5 pF•Ω.
- Dielectric strength of 1,500 Vrms between I/O.
- RoHS compliant

Application Examples

- Broadband systems
- Measurement devices and Data loggers
- Amusement machines



Note: The actual product is marked differently from the image shown here.

List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
SPST-NO	Surface-mounting terminals	80 VAC	G3VM-81GR1	100	---
			G3VM-81GR1(TR)	---	2,500


Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-81GR1




Note: The actual product is marked differently from the image shown here.




Terminal Arrangement/Internal Connections (Top View)

G3VM-81GR1



Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-81GR1



■ Absolute Maximum Ratings (Ta = 25°C)


Item	Symbol	Rating	Unit	Measurement Conditions
Input	LED forward current	I_F	50	mA
	Repetitive peak LED forward current	I_{FP}	1	A
	LED forward current reduction rate	$\Delta I_F/^\circ\text{C}$	-0.5	mA/°C $T_a \geq 25^\circ\text{C}$
	LED reverse voltage	V_R	5	V
	Connection temperature	T_j	125	°C
Output	Load voltage (AC peak/DC)	V_{OFF}	80	V
	Continuous load current	I_O	200	mA
	ON current reduction rate	$\Delta I_O/^\circ\text{C}$	-2.0	mA/°C $T_a \geq 25^\circ\text{C}$
	Connection temperature	T_j	125	°C
Dielectric strength between input and output (See note 1.)		V_{I-O}	1,500	V_{rms} AC for 1 min
Ambient operating temperature		T_a	-20 to +85	°C With no icing or condensation
Storage temperature		T_{slg}	-40 to +125	°C With no icing or condensation
Soldering temperature		---	260	°C 10 s

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

■ Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.0	1.15	1.3	V $I_F = 10 \text{ mA}$
	Reverse current	I_R	---	---	10	μA $V_R = 5 \text{ V}$
	Capacity between terminals	C_T	---	15	---	pF $V = 0, f = 1 \text{ MHz}$
	Trigger LED forward current	I_{FT}	---	---	3	mA $I_O = 200 \text{ mA}$
Output	Maximum resistance with output ON	R_{ON}	---	5	8	Ω $I_F = 5 \text{ mA}, I_O = 200 \text{ mA}$
	Current leakage when the relay is open	I_{LEAK}	---	0.5	1	nA $V_{OFF} = 80 \text{ V}, T_a = 50^\circ\text{C}$
	Capacity between terminals	C_{OFF}	---	6.5	11	pF $V = 0, f = 100 \text{ MHz}, t < 10 \text{ s}$
Capacity between I/O terminals		C_{I-O}	---	0.7	---	pF $f = 1 \text{ MHz}, V_s = 0 \text{ V}$
Insulation resistance between I/O terminals		R_{I-O}	1,000	---	---	M Ω $V_{I-O} = 500 \text{ VDC}, R_{RH} \leq 60\%$
Turn-ON time		t_{ON}	---	0.13	0.5	ms $I_F = 5 \text{ mA}, R_L = 200 \Omega, V_{DD} = 10 \text{ V}$ (See note 2.)
Turn-OFF time		t_{OFF}	---	0.17	0.5	ms

Note: 2. Turn-ON and Turn-OFF Times




■ Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	64	V
Operating LED forward current	I_F	5	---	30	mA
Continuous load current (AC peak/DC)	I_O	---	---	200	mA
Operating temperature	T_a	25	---	60	°C

■ Engineering Data


**LED forward current vs.
Ambient temperature**
 $I_F - T_a$




**Continuous load current vs.
Ambient temperature**
 $I_O - T_a$




**LED forward current vs.
LED forward voltage**
 $I_F - V_F$




**Continuous load current vs.
On-state voltage**
 $I_O - V_{ON}$




**On-state resistance vs.
Ambient temperature**
 $R_{ON} - T_a$




**Trigger LED forward current vs.
Ambient temperature**
 $I_{FT} - T_a$




**Turn ON, Turn OFF time vs.
LED forward current**
 $t_{ON}, t_{OFF} - I_F$




**Turn ON, Turn OFF time vs.
Ambient temperature**
 $t_{ON}, t_{OFF} - T_a$



**Current leakage vs.
Load voltage**
 $I_{LEAK} - V_{OFF}$



**Output terminal capacitance
COFF/COFF(ov) vs. Load voltage**
 $COFF - V_{OFF}$



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA