

## Double-Balanced Mixer

Rev. V3


### Features

- LO 7 TO 17 GHz
- RF 9 TO 15 GHz
- IF DC TO 2.5 GHz
- LO DRIVE: +10 dBm (NOMINAL)
- LOW NOISE FIGURE: 6.5 dB (TYP.)

### Description

The M67 is a double balanced mixer, designed for use in military, commercial and test equipment applications. The design utilizes Schottky ring quad diodes and broadband soft dielectric and ferrite baluns to attain excellent performance. This mixer can also be used as a phase detector and/or bi-phase modulator since the IF port is DC coupled to the diodes. The use of high temperature solder and welded assembly processes used internally makes it ideal for use in manual, semi-automated assembly. Environmental screening available to MIL-STD-883, MIL-STD-202, or MIL-DTL-28837, consult factory.

### Product Image



### Ordering Information


Part Number	Package
M67	Minpac
M67C	SMA Connectorized

### Electrical Specifications: $Z_0 = 50\Omega$ $Lo = +10$ dBm (Downconverter application only)


Parameter	Test Conditions	Units	Typical	Guaranteed	
				+25°C	-54° to +85°C
SSB Conversion Loss (max) & SSB Noise Figure (max)	$f_R = 9.5$ to 13 GHz, $f_L = 9$ to 13.5 GHz, $f_I = 30$ to 500 GHz $f_R = 9$ to 15 GHz, $f_L = 8$ to 16 GHz, $f_I = 30$ to 1000 GHz $f_R = 9$ to 15 GHz, $f_L = 7$ to 17 GHz, $f_I = 30$ to 2000 GHz $f_R = 9.5$ to 13.5 GHz, $f_L = 7$ to 16 GHz, $f_I = 30$ to 2500 GHz	dB	5.5 6.5 6.5 6.5	7.0 8.5 9.0 9.0	7.5 9.0 9.5 9.5
Isolation, L to R (min)	$f_L = 7$ to 15 GHz $f_L = 15$ to 17 GHz	dB	40 30	22 10	20 8
Isolation, L to I (min)	$f_L = 7$ to 17 GHz	dB	25	15	13
1 dB Conversion Comp.	$f_L = +10$ dBm	dBm	+4		
Input IP3	$f_R=11.5$ GHz at $-6$ dBm, $f_R=11.5$ GHz at $-6$ dBm, $f_L = 12$ GHz at $= +10$ dBm	dBm	+11		

### Typical Performance Curves


Conversion Loss vs. LO Drive





Conversion Loss vs. RF Input Power




Conversion Loss vs. Frequency




Isolation vs. Frequency



L-Port VSWR vs. Frequency



Conversion Loss vs. Output Frequency




## Double-Balanced Mixer

Rev. V3



## Absolute Maximum Ratings

Parameter	Absolute Maximum
Operating Temperature	-54°C to +100°C
Storage Temperature	-65°C to +100°C
Peak Input Power	+23 dBm max @ +25°C +20 dBm max @ +100°C
Peak Input Current	50 mA DC


## R-Port VSWR vs. Frequency



## I-Port VSWR vs. f\_L




## Outline Drawing: Minpac \*



Weight: 6 grams (0.21 oz.) max

## Outline Drawing: SMA Connectorized \*



Weight: 25 grams (0.88 oz.) max

\* Dimensions are inches (millimeters)  $\pm 0.015$  (0.38) unless otherwise specified.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[MACOM:](#)

[M67](#) [M67C](#)