

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- . - .

© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

U2

REVISED PER ECO-10-006709


3/29/10

SS

SS


CLAMPING INSERT 

(2) SELF-TAPPING SCREWS
SOLID OR SLOTTED SHANK
TYPE: SEE TABLE
MATERIAL: ZINC PLATED STEEL
LENGTH: SEE TABLE



.825±.025 DIA

1.250±.030



 CLAMPING AREA SHADED

1 PARTS PACKAGED UNASSEMBLED.

CABLE CLAMPING AREA ADJUSTABLE FROM .004 TO .055 SQ IN
BY REVERSING CLAMPING INSERTS.

3

.329 MAXIMUM CABLE OUTSIDE DIAMETER.



BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 400 ONLY.



OBSOLETE PART NUMBER.



STAINLESS STEEL (NON MAGNATIC).



CABLE CLAMP WITH NON-MAGNETIC STAINLESS STEEL SCREWS.



ZINC PLATED STEEL, NON-HEXAVALENT CHROMATE.



OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



BULK

.50±.00
 .05

#5-20

1-206062-7

INDIVIDUAL

.38±.00
 .05

#5-20

1-206062-6



BULK

.38±.00
 .05

#5-20

1-206062-5

INDIVIDUAL

.50±.00
 .05

#5-20

1-206062-4

INDIVIDUAL

.62±.00
 .05

#5-20

1-206062-3



INDIVIDUAL

.50±.00
 .05

#5-20

1-206062-2

INDIVIDUAL

.62±.00
 .05

#5-20

1-206062-1



OBSOLETE

SMALL PACK

.38±.00
 .05

#5-20

1-206062-0

AMP BRAZIL USE ONLY

INDIVIDUAL

12mm^{+.0}
 _{-.8}

3mm-20



206062-9

AMP BRAZIL USE ONLY

INDIVIDUAL

10mm^{+.0}
 _{-.8}

3mm-20



206062-8

 BULK.50±.00
 .05

#5-20

206062-4

INDIVIDUAL

.50±.00
 .05

#5-20

206062-3

 BULK.38±.00
 .05

#5-20

206062-2

INDIVIDUAL

.38±.00
 .05

#5-20

206062-1

PACKAGING

SCREW
FINISHSCREW
LENGTHSCREW
TYPEPART
NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN A GRAFF 4/29/91

CHK W.G.LENKER 7-22-92

APVD -

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-



Tyco Electronics Corporation

Harrisburg, PA 17105-3608

NAME

CABLE CLAMP KIT, STANDARD,
SHELL SIZE 11, CPC

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-206062

-

CUSTOMER DRAWING

SCALE NTS

SHEET

1 OF 1

REV U2