







LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
ES	00		R	REVISED PER ECO-12-012349	28MAR13	BL	AC



- 1 NUMBER "n" IS COUNTED FROM DATUM
(CIRCUIT NO.1 IS "AMP" MARK SIDE.)
- 2 MATERIAL: HOUSING, 66 NYLON (GF) UL 94V-0, BLACK.
: CONTACT, PHOSPHOR BRONZE.
: RETENTION LEG; BRASS.
- 3 FINISH: CONTACT; Au AT CONTACT AREA (SEE TABLE),
TIN AT TINE, OVER Ni.
RETENTION LEG; TIN UNDER Ni.
- 4 P.C. BOARD THK MUST BE 1.6 $\pm$ 0.15 FOR CARD EDGE CONNECTOR



RECOMMENDED P.C. BOARD DIMMENSIONS.



LEAD FREE

GENERAL TOLERANCE

10 $\geq$: $\pm$ 0.2

30 $\geq$ > 10: $\pm$ 0.25

100 $\geq$ > 30: $\pm$ 0.3

ANGLES: $\pm$ 3°

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.ISHIKAWA 13OCT88	TE Connectivity				
DIMENSIONS:	mm	CHK Steven Yao 19AUG2004					
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD Julyee Zhu 19AUG2004	NAME				
		PRODUCT SPEC	AMP CHAMP .050 CONNECTOR (B-T-B) RECEPTACLE CONECTOR (HORIZONTAL WITH RETENTION LEG)				
MATERIAL	FINISH	APPLICATION SPEC	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
2	3	108-60038	A2	00779	C=5175474		
CUSTOMER DRAWING			SCALE	NTS	SHEET	1 OF 1	REV R

OBSOLETE	6-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	6-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	6-	-0		100	49	62.23	67.77	69.63	73.43	64.13
	5-	-9		80	39	49.53	55.07	56.93	60.73	51.43
	5-	-8		68	33	41.91	47.45	49.31	53.11	43.81
	5-	-7		60	29	36.83	42.37	44.23	48.03	38.73
	5-	-6		50	24	30.48	36.02	37.88	41.68	32.38
	5-	-5		40	19	24.13	29.67	31.53	35.33	26.03
	5-	-3		30	14	17.78	23.32	25.18	28.98	19.68
	5-	-1	0.00076	20	9	11.43	16.97	18.83	22.63	13.33
	4-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	4-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	4-	-0		100	49	62.23	67.77	69.63	73.43	64.13
	3-	-9		80	39	49.53	55.07	56.93	60.73	51.43
	3-	-8		68	33	41.91	47.45	49.31	53.11	43.81
	3-	-7		60	29	36.83	42.37	44.23	48.03	38.73
	3-	-6		50	24	30.48	36.02	37.88	41.68	32.38
	3-	-5		40	19	24.13	29.67	31.53	35.33	26.03
	3-	-3		30	14	17.78	23.32	25.18	28.98	19.68
	3-	-1	0.0005	20	9	11.43	16.97	18.83	22.63	13.33
OBSOLETE	1-	-2		130	64	81.28	86.82	88.68	92.48	83.18
	1-	-1		120	59	74.93	80.47	82.33	86.13	76.83
	1-	-0		100	49	62.23	67.77	69.63	73.43	64.13
		-9		80	39	49.53	55.07	56.93	60.73	51.43
		-8		68	33	41.91	47.45	49.31	53.11	43.81
		-7		60	29	36.83	42.37	44.23	48.03	38.73
		-6		50	24	30.48	36.02	37.88	41.68	32.38
		-5		40	19	24.13	29.67	31.53	35.33	26.03
OBSOLETE		-4		36	17	21.59	27.13	28.99	32.79	23.49
		-3		30	14	17.78	23.32	25.18	28.98	19.68
			0.0002	20	9	11.43	16.97	18.83	22.63	13.33
PART NO.		Au PLATE	POS.	n	A	B	C	D	E	