



PART NO.

HV Series

REVISIONS

ECN #

REV

DESCRIPTION

DRAWN

DATE

CHECKD

DATE

APPRVD

DATE

-

A

RELEASED

S. R


8/5/06

K. S

8/5/06

N. K

22/5/06



Lead Wire Dimensions

ϕD	5 - 13	16 - 25
ϕd	0.6	0.8

Dimensions : Millimetres

Dimensions : Millimetres

Features:

- Low Impedance characteristics.
- Case sizes are smaller than conventional general-purpose capacitors, with very high performance.
- Can size larger than 8mm diameter has safety vent on rubber bun.
- General purpose 85°C.
- Axial leaded electrolytic.

This data sheet and its contents (the "Information") belong to the Premier Farnell Group (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. MULTICOMP is the registered trademark of the Group. © Premier Farnell plc 2004.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

S. Ram

DATE:

08/05/06

CHECKED BY:

K. Suresh

DATE:

08/05/06

APPROVED BY:

N. Kiwomya

DATE:

22/05/06

DRAWING TITLE:

HV Series - Axial Electrolytic Capacitors

SIZE
A

DWG NO.

M10000225

ELECTRONIC FILE
208517_1_DWGREV
A

SCALE: NTS

U.O.M.: mm

SHEET: 1 OF 5

SHEET: 4 OF 4