

Date: 06/12/2008

VARISTOR SPECIFICATION SHEET

MAIDA STYLE NUMBER D73ZOV321RA27

MAIDA ITEM NUMBER 01-0670

Electrical Specifications

Continuous AC Voltage	320	VAC
Continuous DC Voltage	420	VDC
Maximum DC Leakage @ 420 VDC	200	uA
Low Varistor Voltage Limit	453	VDC
High Varistor Voltage Limit	553	VDC
Nominal Varistor Voltage	503	VDC
Current for Varistor Voltage	1	mA
Maximum Clamp Voltage	850	V
Maximum Clamp Voltage Test Current	10	A
Peak Current Rating (1 Pulse)	1750	A
Peak Current Rating (2 Pulse)	1250	A
Energy Rating (8X20us)	46	J
Energy Rating (10X1000us)	46	J
Typical Capacitance	100	pF
Impulse Response Time	< 50	ns
Minimum Hipot of Coating	2500	VDC
Minimum I.R. of Coating	1000	MΩ


Thermal Specifications

Minimum Operating Temperature	-40	°C
Maximum Operating Temperature	85	°C
Varistor Voltage Temperature Coeff	-0.05	%/°C
Minimum Storage Temperature	-50	°C
Maximum Storage Temperature	125	°C
Current/Energy Derating Above 85°C	-2.5	%/°C

Notes

Physical Specifications

Lead Style	005N
X Nominal	0.2 in.
X Tolerance	0.04 in.
Lead Length Nominal	1.00 in.
Lead Length Tolerance	min. in.
Y Nominal	0.103 in.
Y Tolerance	0.03 in.
d Nominal	0.025 in.
Wire Gauge	22 AWG
Minimum Marking	Z321-27UL
Nominal Disk Size	7 mm
D Maximum	0.354 in.
T Maximum	0.272 in.
H Maximum	0.479 in.



* Contact Maida for a more detailed configuration drawing.

Safety Agency Recognitions

UL 1449 File Number	E86730
UL 1414 File Number	E38785
CSA File Number	LR33468
VDE File Number	
SEV File Number	



DEVELOPMENT COMPANY

P.O. Box 3529

Hampton, Virginia 23663

(757) 723-0785 Fax (757) 722-1194