


LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
AF	50				L	REV PER 061A-0418-98	11/25/98	JR/DD



- 1
- WIRE TYPES NOT DESCRIBED SHALL BE SUBMITTED TO AMP ENGINEERING FOR WIRE-TO-TERMINAL APPLICATION APPROVAL
- 2
- APPLICATION OF TERMINAL INTO P.C.BOARD AND WIRE INSERTION INTO TERMINAL SHALL BE IN ACCORDANCE WITH AMP SPEC.114-2051
- 3
- MAXIMUM WIDTH AFTER INSERTION IN P.C. BOARD
- 4
- CONTINUOUS STRIP ON REELS WITH TERMINALS LOCATED ON 3.18±0.076[0.125±.003] CENTERS
- 5
- SLOT ACCEPTS 0.20mm² [#24] AWG 7 STRANDED (TIN PLATED) COPPER WIRE, 0.50-0.40mm [#24-#26] AWG SOLID COPPER WIRE, 0.40mm [#26] AWG FUSED COPPER WIRE.
- 6
- 0.00381 [0.000150] MIN TIN PER MIL-T-10727 OVER 0.00254[0.000100] MIN COPPER UNDERPLATE PER MIL-T-14550.
OR
0.00381 [0.000150] MIN TIN PER MIL-T-10727 OVER 0.00127 [0.000050] MIN NICKEL UNDERPLATE PER QQ-N-290.

		1.52 [0.060] MAX	63007-1
		INSULATION DIA. (PVC)	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.25[0.010] 3 PLC DEC ± - ANGLES ± 1°		DR 13/SEPT/95 R.GRZYBOWSKI CHK 13/SEPT/95 M.S.FEHER APPD 13/SEPT/95 G.PORTA APPD 13/SEPT/95 T.L.SHUTTER PRODUCT SPEC 108-2032	NAME AMP Incorporated Harrisburg, PA 17105-3608
MATERIAL H04 BRASS	FINISH	APPLICATION SPEC 2	SIZE C CAGE CODE 00779 DRAWING NO G=63007
WEIGHT -		SCALE 10:1	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.