

LS-Titan Miniature DIN Switches



LS-Titan Safety Interlock Switches



46.3	LS-Titan Miniature DIN Switches	
	Product Description	2
	Features	2
	Standards and Certifications	2
	Product Identification	3
	Product Selection	4
	Accessories	14
	Technical Data and Specifications	15
	Contact Travel Diagrams	18
	Dimensions	21
45.1	LS-Titan Safety Interlock Switches	
	Product Description	24
	Features	24
	Standards and Certifications	24
	Product Identification	25
	Product Selection	26
	Technical Data and Specifications	29
	Mounting Instructions	30
	Dimensions	31

Note: Supplement to Volume 8—Sensing Solutions, CA08100010E, Tabs 46 and 45.

LS-Titan Miniature DIN Switches

46



Contents

Description	Page
LS-Titan Miniature DIN Switches	
Product Identification	3
Product Selection	4
LS-Titan Plastic Safety Switches	4
LS-Titan Plastic Electronic Safety Position Switches	7
LS-Titan Metal Safety Switches	11
Understanding LS-Titan Electronic Safety Position Switches	13
Operating Point Adjustment	13
Accessories	14
Technical Data and Specifications	15
Contact Travel Diagrams	18
Dimensions	21

LS-Titan Miniature DIN Switches

Product Description

Eaton's LS-Titan™ limit switch line is a complete offering of safety position switches designed for worldwide application. Economical insulated plastic or rugged metal enclosures and modular, plug-in operating heads and bodies make LS-Titan a flexible switching solution.

A highlight of the LS-Titan switch line is the world's first electronic position switch (LSE models). These switches feature freely programmable operating points that can be set individually at any time. Additional LSE models provide analog outputs proportional to the actuator position.

LS-Titan switches are suitable for use in safety applications designed to protect persons or processes.

Features

- Modular, plug-in system (head and body components)
- Positive opening NC contacts for safety applications
- Wide variety of economical plastic and rugged metal versions available
- Operating heads can be rotated 90 degrees to suit specific direction of operation
- Unique electronic safety position switches (LSE models) provide analog (0–10 Vdc or 4–20 mA) outputs proportional to the actuator position and allow for easy configuration of a custom trip point
- Can be ordered as separate components (head and body) or as completely assembled switches
- Screw and Cage Clamp® (standard on LSE models and optionally available on mechanical models) connections provide larger wiring areas for easier installation
- Approved for worldwide application

Standards and Certifications


- Safety function by positive opening contacts per IEC/EN 60947-5-1 up to Category 4 per EN 954-1
- TÜV-Rheinland Certified for Functional-Safety (LSE models)
- CSA® certified
- UL® listed
- CE
- CCC



Note: Cage Clamp is a registered trademark of Wago Kontakttechnik, 32423 Minden, Germany.

For the most current information on this product, visit our web site: www.eaton.com

Product Identification



Notes

① Basic device (see Pages 4–12)

According to EN 50047
 With screw-on cover
 Contacts: 1NO-1NC, 2NO, 2NC
 Cage Clamp, screw terminal
 As snap-action or standard-action switch
 As electronic snap-action switch
 (individually adjustable)
 As 4–20 mA analog signal encoder
 As 0–10 Vdc analog signal encoder

② Fixing adapter (see Page 14)

Allows mounting of M22 pushbuttons

③ Roller lever (see Pages 4 and 7)

For one-sided operation with higher operating speed

④ Angled roller lever

(see Pages 4, 7 and 11)
 For actuation along the unit axis

⑤ Rotary lever (see Pages 4, 8 and 11)

For actuation from the side, for pendulum movements

⑥ Roller plunger (see Pages 4, 7 and 11)

For actuation from the side with low actuating force

⑦ Adjustable roller lever

(see Pages 5, 8, 9 and 11)
 For length adjustment as required

⑧ Actuating rod (see Pages 6, 10 and 12)

On conveyor belts for lightweight goods

⑨ Spring-rod (see Pages 6, 10 and 12)

For flexible actuation from all sides

j Actuating rod (see Pages 6, 10 and 12)

Withdrawable mechanism from front

k Pushbuttons from the M22 family; see M22 catalog (CA04716001E) or www.eaton.com/m22

Operating heads can be rotated by 90 degrees.

Product Selection

LS-Titan Plastic Safety Switches

46

Plastic Safety Switch Body



Assembled Switch



Plastic Safety Switches

Switch Body Catalog Number

Output Function

Terminal Connection

Contact Sequence

Contact Travel

■ = contact closed
□ = contact open


Operating Head Type ②

Head Only Catalog Number

LS-S02

2NC with positive opening contacts


Screw terminal ①



LS-S20A

2NO with slow make/break

Screw terminal ①



LS-S11S

1NO and 1NC with positive opening contact

Screw terminal ①



Snap-action contact



Top Push Roller Plunger



Long Roller Lever



Short Roller Lever



Large Roller Lever



Angled Roller



Rotary Lever



LS-XP

LS-S02-P

LS-S20A-P

LS-S11S-P

LS-XL

LS-S02-L

LS-S20A-L

LS-S11S-L

LS-XLS

LS-S02-LS

LS-S20A-LS

LS-S11S-LS

LS-XLB

LS-S02-LB

LS-S20A-LB

LS-S11S-LB

LS-XLA

LS-S02-LA

LS-S20A-LA

LS-S11S-LA

LS-XRL

LS-S02-RL

LS-S20A-RL

LS-S11S-RL

Notes

① Cage Clamp versions available. Contact Application Engineering.

② For operating head dimensions, see **Page 21**.

Plastic Safety Switch Body



Assembled Switch




Plastic Safety Switches, continued

Switch Body Catalog Number
Output Function


Terminal Connection
Contact Sequence

Contact Travel
■ = contact closed
□ = contact open


LS-S02
2NC with positive opening contacts
Screw terminal ①



LS-S20A
2NO with slow make/break
Screw terminal ①



LS-S11S
1NO and 1NC with positive opening contact
Screw terminal ①



Operating Head Type ②

Head Only
Catalog Number

Assembled Switch
Catalog Number

Adjustable Roller Lever (with 18 mm Roller)



LS-XRLA

LS-S02-RLA

LS-S20A-RLA

LS-S11S-RLA

Adjustable Roller Lever (with 30 mm Roller)



LS-XRLA30

LS-S02-RLA30

LS-S20A-RLA30

LS-S11S-RLA30

Adjustable Roller Lever (with 40 mm Roller)



LS-XRLA40

LS-S02-RLA40

LS-S20A-RLA40

LS-S11S-RLA40

Adjustable Roller Lever (with 40 mm Rubber Roller)



LS-XRLA40R

LS-S02-RLA40R

LS-S20A-RLA40R

LS-S11S-RLA40R

Notes

- ① Cage Clamp versions available. Contact Application Engineering.
- ② For operating head dimensions, see Page 21.

Plastic Safety Switch Body



Assembled Switch



Plastic Safety Switches, continued

Switch Body Catalog Number

Output Function

Terminal Connection

Contact Sequence

Contact Travel

■ = contact closed

□ = contact open


Operating Head Type ②

Head Only
Catalog Number

LS-S02

2NC with positive
opening contacts

Screw terminal ①




Zw = 4.5 mm

LS-S20A

2NO with slow
make/break

Screw terminal ①



ZW = 4.5 mm


LS-S11S

1NO and 1NC with
positive opening contact

Screw terminal ①



Snap-action contact



Zw = 5.5 mm

Plastic Rod Lever



Metal Rod



Spring Rod (Wobble) ③



Actuating Rod



LS-XRR

LS-S02-RR

LS-S20A-RR

LS-S11S-RR

LS-XRRM

LS-S02-RRM

LS-S20A-RRM

LS-S11S-RRM

LS-XS

LS-S02-S

LS-S20A-S

LS-S11S-S

LS-XOR

LS-S02-OR

LS-S20A-OR

LS-S11S-OR

Notes

① Cage Clamp versions available. Contact Application Engineering.

② For operating head dimensions, see **Page 21**.

③ Not to be used as a safety position switch. Use only in conjunction with snap-action contact.

LS-Titan Plastic Electronic Safety Position Switches**Plastic Electronic Safety Position Switch Body****Assembled Switch****Plastic Electronic Safety Position Switches****Switch Body****Catalog Number****LSE-11****LSE-02****LSE-AI****LSE-AU****Output Function**

1NO and 1 NC

2NC

Analog 4–20 mA

Analog 0–10V

Terminal Connections

Cage Clamp ①

Cage Clamp ①



Cage Clamp ①

Cage Clamp ①

Safety Functions and Approvals

These models may be used in safety-oriented circuits. Visual status LED indication is comparable to positive opening contacts. Certified by TÜV as a "Functional-Safety" device. Suitable for protection of people or processes.

Additional diagnostic output that registers a 0V signal in the event of a fault. Self-test function continuously tests both outputs for overloads, short circuits to 0V and short circuits to +U_e. Certified by TÜV to EN 954-1, Category 3 or 4. Suitable for protection of people or processes.





**Contact Sequence**

Analog 4–20 mA

Analog 0–10V

Contact Travel

■ = contact closed
□ = contact open

**Operating Head Type ②****Head Only****Catalog Number****Assembled Switch Catalog Number****Top Push Roller Plunger****LS-XP****LSE-11-P****LSE-02-P****LSE-AI-P****LSE-AU-P****Long Roller Lever****LS-XL****LSE-11-L****LSE-02-L****LSE-AI-L****LSE-AU-L****Short Roller Lever****LS-XLS****LSE-11-LS****LSE-02-LS****LSE-AI-LS****LSE-AU-LS****Large Roller Lever****LS-XLB****LSE-11-LB****LSE-02-LB****LSE-AI-LB****LSE-AU-LB****Angled Roller****LS-XLA****LSE-11-LA****LSE-02-LA****LSE-AI-LA****LSE-AU-LA****Notes**① A compatible Cage Clamp tool is available as an accessory on **Page 14**.② For operating head dimensions, see **Page 21**.

Plastic Electronic Safety Position Switch Body



Assembled Switch



Plastic Electronic Safety Position Switches, continued

Switch Body
Catalog Number

Output Function

Terminal Connections

Safety Functions
and Approvals

LSE-11

1NO and 1NC

Cage Clamp ①

LSE-02

2NC

Cage Clamp ①

LSE-AI

Analog 4–20 mA

Cage Clamp ①

LSE-AU

Analog 0–10V



Cage Clamp ①

These models may be used in safety-oriented circuits. Visual status LED indication is comparable to positive opening contacts. Certified by TÜV as a "Functional-Safety" device. Suitable for protection of people or processes.

Additional diagnostic output that registers a 0V signal in the event of a fault. Self-test function continuously tests both outputs for overloads, short circuits to 0V and short circuits to +U_e. Certified by TÜV to EN 954-1, Category 3 or 4. Suitable for protection of people or processes.







Contact Sequence



Contact Travel

■ = contact closed

□ = contact open



Operating Head Type ②

Head Only
Catalog NumberAssembled Switch
Catalog Number

Rotary Lever



LS-XRL

LSE-11-RL

LSE-02-RL

LSE-AI-RL

LSE-AU-RL

Adjustable Roller Lever
(with 18 mm Roller)

LS-XRLA

LSE-11-RLA

LSE-02-RLA

LSE-AI-RLA

LSE-AU-RLA

Adjustable Roller Lever
(With 30 mm Roller)

LS-XRLA30

LSE-11-RLA30

LSE-02-RLA30

LSE-AI-RLA30

LSE-AU-RLA30

Notes

① A compatible Cage Clamp tool is available as an accessory on **Page 14**.② For operating head dimensions, see **Page 21**.

Plastic Electronic
Safety Position
Switch Body

Assembled Switch



Plastic Electronic Safety Position Switches, continued

Switch Body

Catalog Number

LSE-11

LSE-02

LSE-AI

LSE-AU

Output Function

1NO and 1NC

2NC

Analog 4–20 mA

Analog 0–10V

Terminal Connections



Cage Clamp ^①Cage Clamp ^①Cage Clamp ^①Cage Clamp ^①Safety Functions
and Approvals

These models may be used in safety-oriented circuits. Visual status LED indication is comparable to positive opening contacts. Certified by TÜV as a "Functional-Safety" device. Suitable for protection of people or processes.

Additional diagnostic output that registers a 0V signal in the event of a fault. Self-test function continuously tests both outputs for overloads, short circuits to 0V and short circuits to +U₀. Certified by TÜV to EN 954-1, Category 3 or 4. Suitable for protection of people or processes.



Contact Sequence







Analog 4–20 mA

Analog 0–10V

Contact Travel

■ = contact closed

□ = contact open

Operating Head Type ^②

Head Only

Catalog Number

Assembled Switch
Catalog Number

LS-XRLA40

LSE-11-RLA40

LSE-02-RLA40

LSE-AI-RLA40

LSE-AU-RLA40

Adjustable
Roller Lever
(With 40 mm Roller)Adjustable
Roller Lever
(With 40 mm Roller)

Plastic Rod Lever



LS-XRLA40R

LSE-11-RLA40R

LSE-02-RLA40R

LSE-AI-RLA40R

LSE-AU-RLA40R

LS-XRR

LSE-11-RR

LSE-02-RR

LSE-AI-RR

LSE-AU-RR

Notes

^① A compatible Cage Clamp tool is available as an accessory on **Page 14**.

^② For operating head dimensions, see **Page 21**.

Plastic Electronic Safety Position Switch Body



Assembled Switch



Plastic Electronic Safety Position Switches, continued

Switch Body
Catalog Number

Output Function

Terminal Connections

Safety Functions
and Approvals

LSE-11

1NO and 1NC

Cage Clamp ①

LSE-02

2NC

Cage Clamp ①

LSE-AI

Analog 4–20 mA

Cage Clamp ①

LSE-AU

Analog 0–10V



Cage Clamp ①

These models may be used in safety-oriented circuits. Visual status LED indication is comparable to positive opening contacts. Certified by TÜV as a “Functional-Safety” device. Suitable for protection of people or processes.

Additional diagnostic output that registers a 0V signal in the event of a fault. Self-test function continuously tests both outputs for overloads, short circuits to 0V and short circuits to +U_e. Certified by TÜV to EN 954-1, Category 3 or 4. Suitable for protection of people or processes.



Contact Sequence







Analog 4–20 mA

Analog 0–10V

Contact Travel

■ = contact closed
□ = contact open



Operating Head Type ②

Head Only
Catalog NumberAssembled Switch
Catalog Number

Metal Rod



LS-XRRM

LSE-11-RRM

LSE-02-RRM

LSE-AI-RRM

LSE-AU-RRM

Spring Rod (Wobble) ③



LS-XS

LSE-11-S

LSE-02-S

LSE-AI-S

LSE-AU-S

Actuating Rod



LS-XOR

LSE-11-OR

LSE-02-OR

LSE-AI-OR

LSE-AU-OR

Notes

- ① A compatible Cage Clamp tool is available as an accessory on **Page 14**.
 ② For operating head dimensions, see **Page 21**.
 ③ Not to be used as a safety position switch. Use only in conjunction with snap-action contact.

LS-Titan Metal Safety Switches**Metal Safety Switch Body****Assembled Switch****Metal Safety Switches**

Switch Body Catalog Number
Output Function

Terminal Connection

Contact Sequence

Contact Travel

■ = contact closed

□ = contact open


Operating Head Type ①

Head Only Catalog Number

LSM-02


2NC with positive opening contacts

Cage Clamp

**LSM-20A**

2NO with slow make/break

Cage Clamp


**LSM-11S**

1NO and 1NC with positive opening contact

Cage Clamp



Snap-action contact

**Top Push Roller Plunger**

LSM-XP

LSM-02-P

LSM-20A-P

LSM-11S-P

Long Roller Lever

LSM-XL

LSM-02-L

LSM-20A-L

LSM-11S-L

Angled Roller

LSM-XLA

LSM-02-LA

LSM-20A-LA

LSM-11S-LA

Rotary Lever

LSM-XRL

LSM-02-RL

LSM-20A-RL

LSM-11S-RL

Adjustable Roller Lever

LSM-XRLA

LSM-02-RLA

LSM-20A-RLA

LSM-11S-RLA

Note

① For operating head dimensions, see **Page 21**.

Metal Safety
Switch Body

Assembled Switch



Plastic Rod Lever



Metal Rod Lever



Spring Rod (Wobble)



Metal Safety Switches, continued

Switch Body Catalog Number

Output Function

Terminal Connection

Contact Sequence

Contact Travel

■ = contact closed

□ = contact open

Operating Head Type ①


Head Only

Catalog Number

LSM-02

2NC with positive
opening contacts


Cage Clamp



LSM-20A

2NO with slow
make/break

Cage Clamp




LSM-11S

1NO and 1NC with
positive opening contact

Cage Clamp



Snap-action contact

Assembled Switch
Catalog Number

LSM-XRR

LSM-02-RR

LSM-20A-RR

LSM-11S-RR

LSM-XRRM

LSM-02-RRM

LSM-20A-RRM

LSM-11S-RRM

LSM-XS

LSM-02-S

LSM-20A-S

LSM-11S-S

Note

① For operating head dimensions, see **Page 21**.

Understanding LS-Titan Electronic Safety Position Switches

All four LS-Titan LSE switch bodies are safety-rated products. The LSE-11 and LSE-02 switch bodies both have a freely programmable operating point and can be individually adjusted to suit the application, and can be changed as often as required. These devices feature an LED on the body, providing simple indication during programming and operation.


The LSE-AI (4–20 mA) and LSE-AU (0–10V) analog position switches take position data and convert to an analog current or voltage value that can then be continuously fed into an automation system. These two switches also feature a diagnostic output for additional data processing.

This ensures that a safe operating state can be monitored and evaluated at any time. A self-test function is also present on these models. Outputs Q1 and Q2 are continuously tested for overloads, short circuits to 0V and short circuits to +U_e.


Like the electromechanical position switches, LS-Titan electronic position switches meet Category 3 or 4 of the EN 954-1 standard for machine safety when configured as a redundant system. All devices are thus suitable for safety applications that are used for the protection of persons or processes.

Operating Point Adjustment


LSE-11



LSE-02



Example of LS-Titan LSE Models in a Safety-Oriented Circuit



Notes

LSE-11 and LSE-02—individual operating point adjustment.

LSE-11 and LSE-02 can be used in safety circuits.

S1 is connected to 24 Vdc








S2, S3 each switch with a delay of 0.7s

R1, R2, e.g., series element M22-XLED60 (2820 ohms/0.5W)

Accessories

46

LS-Titan Safety Switches

	For Use With	Description	Notes	Catalog Number
V1-2-M20 	Any	M20 screw terminal in 1/2 in. For use with American pipe thread, metal.	The screw connection must be earthed. Not total insulation.	V1-2-M20-NA
	Any	M20 screw terminal in 1/2 in. For use with American pipe thread, molded material.	—	V1-2-M20
EMS20 	Any	M20 diaphragm bolt. With internal push-through membrane. Will fit cable with an external diameter of up to 13 mm. Rated IP65 with cable inserted.	—	EMS20
LS-XTW 	Any	Cage Clamp tool.	—	LS-XTW
M12A 	LS-Titan plastic bodies (LS-_)	Plug connector, 12 mm, 4-pin male connector M12x1 (M12x1). Rated IP65. Molded material. Color coded to IEC/EN 60947-5-2.		MS12A
M12A5 	LS-Titan metal bodies (LSM-_)	Plug connector, 12 mm, 5-pin male connector (M12x1). Rated IP65. Molded material. Color coded to IEC/EN 60947-5-2.		MS12A5
M22-LS 	Any	Allows mounting of M22 pushbuttons. (See the M22 catalog, CA04716001E, for a full selection of pushbuttons.)	—	M22-LS

Technical Data and Specifications

LS-Titan Miniature DIN Switches—IP66, IP67 Complete Units

Units			LS, LSM	LSE-11/LSE-02	LSE-AI ①	LSE-AU ①
General						
Standards			IEC/EN 60947	IEC/EN 60947 EN 61000-4	IEC/EN 60947 EN 61000-4	IEC/EN 60947 EN 61000-4
Climatic proofing			Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30	Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30	Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30	Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30
Ambient temperature		°F (°C)	–13° to 158°F (–25° to 70°C)	–13° to 158°F (–25° to 70°C)	–13° to 158°F (–25° to 70°C)	–13° to 158°F (–25° to 70°C)
Mounting position			As required	As required	As required	As required
Protection type			IP66, IP67	IP66, IP67	IP66, IP67	IP66, IP67
Terminal capacity of screw terminal and Cage Clamp						
Solid		mm ²	1 x (0.5–2.5)	1 x (0.5–2.5)	1 x (0.5–2.5)	1 x (0.5–2.5)
Flexible with ferrules to DIN 46228		mm ²	1 x (0.5–1.5)	1 x (0.5–1.5)	1 x (0.5–1.5)	1 x (0.5–1.5)
Power Supply						
Rated voltage		U _e Vdc	N/A	12–30	24 (–15%/+20%)	24 (–15%/+20%)
Burden current						
12V		I _e mA	N/A	15	N/A	N/A
24V		I _e mA	N/A	18	28–45	24
30V		I mA	N/A	19	N/A	N/A
Contacts/Switching Capacity						
Rated impulse withstand voltage		U _{imp} Vac	4000	N/A	N/A	N/A
Rated insulation voltage		U _i V	400	N/A	N/A	N/A
Overvoltage category/ pollution degree			III/3	III/3	N/A	N/A
Rated Operational Current						
AC-15						
24V		I _e A	6	N/A	N/A	N/A
230V/240V		I _e A	6	N/A	N/A	N/A
400V/415V		I _e A	4	N/A	N/A	N/A
DC-13						
24V		I _e A	3	0.2	N/A	N/A
110V		I _e A	0.8	N/A	N/A	N/A
220V		I _e A	0.3	N/A	N/A	N/A

Note

① The following applies for LSE-11 and LSE-02: ensure that the power supply operates correctly when setting the operating point.

LS-Titan Miniature DIN Switches—IP66, IP67 Complete Units. continued

	Units	LS, LSM	LSE-11/LSE-02	LSE-AI ①	LSE-AU ①
Burden Current					
Analog output Q1					
Output voltage (max. 10 mA)	Vdc	N/A	N/A		0–10
Output current	mA	N/A	N/A	4–20	
Fault scenario	V	N/A	N/A	0	0
Resolution	Steps	N/A	N/A	100	100
Step tolerance	Steps	N/A	N/A	1	1
Shunt resistor, resistive load	ohms	N/A	N/A	<400	>1000
Digital diagnostics output Q2 (switching to + pole PNP)					
Response threshold	V	N/A	N/A	Approx. U_e	Approx. U_e
	mA	N/A	N/A	<200	<200
Control circuit reliability					
At 24 Vdc/5 mA	H_F	Fault probability	$<10^{-7}$, <1 fault in 10^7 operations	N/A	N/A
At 5 Vdc/1 mA	H_F	Fault probability	$<10^{-6}$, <1 failure at 5×10^6 operations	N/A	N/A
Supply frequency	Hz	Max. 400	N/A	N/A	N/A
Short-circuit rating to IEC/EN 60947-5-1					
Maximum fuse	A gG/gL	6	N/A	N/A	N/A
Repetition accuracy	mm	± 0.02	± 0.02	± 0.02	± 0.02

Note

① The following applies for LSE-11 and LSE-02: ensure that the power supply operates correctly when setting the operating point.

LS-Titan Miniature DIN Switches—IP66, IP67 Complete Units

Units		LS, LSM		LSE-11/LSE-02	LSE-AI/LSE-AU	LSE-AI/LSE-AU
Mechanical Variables						
Lifespan						
Standard-action contact	Operations	X 10 ⁶	8	N/A	N/A	N/A
Snap-action contact	Operations	X 10 ⁶	8	3 (electronic)	N/A	N/A
Contact temperature of roller head		°C	≤100	≤100	≤100	≤100
Mechanical shock resistance (half-sinusoidal shock, 20 ms)						
Standard-action contact		g	25	N/A	N/A	N/A
Snap-action contact		g	N/A	N/A	N/A	N/A
Basic unit		g	N/A	30	30	30
Operating frequency	Operations/h		≤6000	≤3000	≤3000	≤3000
Switching point			N/A	0.5–5.5 mm freely adjustable	N/A	N/A
Hysteresis		mm	N/A	0.4	0.4	0.4
Contact sequence (contact closed open Zw = positive opening clearance)		mm	N/A	0.04	0.06	0.06
Actuation						
Mechanical						
Actuating force at beginning/ end of stroke						
Basic units		N	1.0/8.0	3.5/8.0	3.5/8.0	3.5/8.0
LS(M)-XP		N	1.0/8.0	1.0/8.0	1.0/8.0	1.0/8.0
LS(M)-XL		N	1.0/8.0	1.0/8.0	1.0/8.0	1.0/8.0
LS(M)-XLA		N	1.0/8.0	1.0/8.0	1.0/8.0	1.0/8.0
Actuating torque of rotary drives		Nm	0.2	0.2	0.2	0.2
Maximum operating speed with DIN cam						
Basic units for angle of actuation		α = 0°/30°	m/s	1/0.5	1/0.5	1/0.5
LS(M)-XRL for angle of actuation		α = 0°	m/s	1.5	1.5	1.5
LS(M)-XRLA for angle of actuation		α = 30°, L = 125 mm	m/s	1.5	1.5	1.5
LS(M)-XRR for angle of actuation		L = 130 mm	m/s	1.5	1.5	1.5
LS(M)-XL for angle of actuation		α = 30°/45°	m/s	1	1	1
LS(M)-XLA for angle of actuation		α = 30°/45°	m/s	1	1	1
LS(M)-XP for angle of actuation		α = 0°/30°	m/s	1/1	1/1	1/1
Electromagnetic Compatibility (EMC)						
Electrostatic discharge (IEC/EN 61000-4-2, Level 3 ESD)						
Air discharge		kV		8	8	8
Contact discharge		kV		4	4	4
Electromagnetic fields (IEC/EN 61000-403, RFI)		V/m		10	10	10
Burst pulses (IEC/EN 61000-4-4, Level 3)						
Supply cables		kV		2	2	2
Signal lines		kV		2	2	2
High-energy pulses (surge) (IEC/EN 61000-4-5)		kV		0.5	0.5	0.5
Immunity to line-conducted interference to (IEC/EN 610000-4-6)		V		10	10	10

Contact Travel Diagrams

LSE










46

Description	Contact Travel	LSE-11		LSE-02	
	■ = contact closed □ = contact open	Q1	Q2	Q1	Q2
Basic Units					
		0 0.5 5.5 6.1 Q1 Q2 default=3.0		0 0.5 5.5 6.1 Q1 Q2 default=3.0	
Operating Heads					
Roller plunger					
LS-XP LSM-XP		0 0.5 5.5 6.1 Q1 Q2 default=3.0		0 0.5 5.5 6.1 Q1 Q2 default=3.0	
Roller lever					
LS-XL LSM-XL LS-XL LS-XLB		0 0.5 9.0 9.6 Q1 Q2 default=4.4		0 0.5 9.0 9.6 Q1 Q2 default=4.4	
Angled roller lever					
LS-XLA LSM-XLA		0 0.5 10 10.8 Q1 Q2 default=5.0		0 0.5 10 10.8 Q1 Q2 default=5.0	
Rotary lever					
LS-XRL LSM-XRL		0° 5° 60° 65° Q1 Q2 default=30°		0° 5° 60° 65° Q1 Q2 default=30°	
Adjustable roller lever					
LS-XRLA LSM-XRLA LS-XRLA30 LS-XRLA40 LS-XRLA40R		0° 5° 60° 65° Q1 Q2 default=30°		0° 5° 60° 65° Q1 Q2 default=30°	
Actuating rod					
LS-XRR LSM-XRR LS-XRRM LSM-XRRM		0° 5° 60° 65° Q1 Q2 default=30°		0° 5° 60° 65° Q1 Q2 default=30°	
Spring rod					
LS-XS LSM-XS		0° 3° 23° 26° Q1 Q2 default=13°		0° 3° 23° 26° Q1 Q2 default=13°	

LS and LSM





Description	Contact Travel		LS-02, LS-S02, LSM-02		LS-11S, LS-S11S, LSM-11S		LS-20A, LS-S20A, LSM-20A	
	■ = contact closed □ = contact open		NC 12 11 22 21		NO 14 13 22 21		NO 14 13 24 23	
Basic Units								
Operating Heads								
Roller plunger LS-XP, LSM-XP								
Roller lever LS-XL, LSM-XL								
Roller lever, short LS-XLS								
Roller lever, large LS-XLB								

LS and LSM, continued

Contact Travel		LS-02, LS-S02, LSM-02		LS-11S, LS-S11S, LSM-11S		LS-20A, LS-S20A, LSM-20A	
Description	 = contact closed						
	 = contact open						
Operating Heads, continued							
Angled roller lever							
LS-XLA, LSM-XLA							
							
Rotary lever							
LS-XRL, LSM-XRL							
Adjustable roller lever							
LS-XRLA, LSM-XRLA LS-XRLA30, LS-XRLA40 LS-XRLA40R							
							
Actuating rod							
LS-XRR, LSM-XRR LS-XRRM, LSM-XRRM							
Spring rod							
LS-XS, LSM-XS							
							

Dimensions

Approximate Dimensions in Inches (mm)

Position Switches**LS-_, LSM-_, LSE-_****LS-_, LSM-_, LSE-_****LS(M)-_/S****LS(M)-_/P****Notes**

- ① Tightening torque of cover screws: 0.8 Nm $\pm$ 0.2 Nm.
- ② Only with LS (insulated version).
- ③ Fixing screws 2 x M4 $\geq$ 30
M_A = 1.5 Nm

Limit Switches


LS-Titan Miniature DIN Switches

Approximate Dimensions in Inches (mm)

46


Rotary Lever

LS(M)- /RL




Roller Lever

LS(M)-_/L




Roller Lever, Large

LS(M)-_/LB ①




Roller Lever, Short

LS(M)- /LS




Adjustable Roller Lever

LS(M)-_/RLA



Angled Roller Lever

LS(M)-_/XLA




Notes

- ① Tightening torque of cover screws: $0.8 \text{ Nm} \pm 0.2 \text{ Nm}$.
- ② Setting range of 54.5 to 97.


Approximate Dimensions in Inches (mm)

Actuating Rod

LS(M)-_/RR



LS(M)-_/OR



Notes

- ① LS_/RR ≤ 150
LS_/RRM ≤ 210
- ② Approach direction, vertical.
- ③ Guide is done by customer, not included.
- ④ Maximum push-through.

LS-Titan Safety Interlock Switches



LS-Titan Safety Interlock Switches

Product Description

Eaton's LS-Titan™ safety interlock switches have been specifically designed for monitoring the position of protective guards, such as doors, flaps, hoods and grilles. All switches in this family are safety-rated, include positively opening NC contacts, and cannot be defeated using simple tools, such as pliers, screwdrivers and nails.

The LS-Titan safety interlock family is comprised of three types of safety switches: key interlock, door-flap and door-hinge switches.

Key interlock switches are a two-piece design, made up of the switch and key (actuator). The key portion of the switch is affixed to a movable door, cover or other such guard. The switch itself is mounted to a rigid portion of the machine. When the guard is opened, the key is removed from the switch, thereby positively breaking the NC contacts. This interrupts the control circuit, stopping machine operation.

The door-flap and door-hinge switches are one-piece designs, suitable for when a key cannot be mounted in the application. When an attempt is made to open a protected door hinge or flap during operation, these switches disconnect the power supply to the machine or installation. Both switches feature four-way adjustable heads.

All LS-Titan safety interlock switches are approved to protect personnel and processes.

Contents

Description

Description	Page
LS-Titan Safety Interlock Switches	
Product Identification	25
Product Selection	
LS-Titan Miniature DIN Safety Interlock Switches	26
LS-Titan Full-Size DIN Safety Interlock Switches	27
LS-Titan Solenoid Safety Interlock Switches	27
LS-Titan Solenoid Safety Interlock Keys	28
Technical Data and Specifications	29
Mounting Instructions	30
Dimensions	31

Features

- Broad family of safety interlock switches in industry-standard enclosure sizes: miniature DIN; full-size DIN; and larger, solenoid key interlocks providing the highest degree of personnel and process protection
- Large selection of actuators (keys), including those for sliding doors, swing doors and doors that do not close precisely
- Miniature DIN models have a five-way adjustable head, while full-size DIN models have four-way adjustable heads
- Fully safety-rated as interlocking devices per EN 1088, with safety function by positive opening contacts per IEC/EN 60947-5-1
- Door-flap and door-hinge safety switches provide a unique solution when actuators (keys) cannot be used
- IP65 degree of protection

Standards and Certifications

- UL® listed
- CSA® approved
- CCC



- Positive opening NC contacts per EN 60947-5-1



Safety Notes

Do not use as a mechanical stop/shipping brace.

Any change to an original Eaton safety position switch is not permitted and automatically leads to the loss of all approvals.




Switch must never be used as a mechanical stop.

For the most current information on this product, visit our web site: www.eaton.com

Product Identification


Solenoid Safety Interlock Switches (LS-...ZBZ)



Notes

- ① **Basic device** (see Page 27)
Spring or magnet-powered interlock
For increased personnel and process protection
Tamper-proof
Multiple coded actuators
Contacts: 1NO-1NC or 2NC
- ② **Flat flexible actuator** (see Page 28)
For doors that do not close precisely
- ③ **Angled flexible actuator** (see Page 28)
For doors that do not close precisely
- ④ **Flat actuator** (see Page 28)
For sliding doors
- ⑤ **Angled actuator** (see Page 28)
For swing doors
- ⑥ **Flat compensating actuator** (see Page 28)
For increased tolerance compensation in the direction of door closure
- ⑦ **Angled compensating actuator** (see Page 28)
For increased tolerance compensation in the direction of door closure


Miniature DIN Safety Interlock Switch (LS-...ZB)



Notes

- ① **Complete device** (see Page 26)
For personnel protection
Contacts: 1NC, 1NO-1NC or 2NC
Five directions of operation possible
- ② **Actuator** (see Page 26)
Included with switch
Multiple coding protection against tampering


Door Flap Safety Switch (LSR-...TKG)



Note

- ① **Complete device** (see Page 26)
For personnel protection
Contacts: 1NO-1NC or 2NC
For swing doors with fixed connection to the door/hinge pin


Door Hinge Safety Switch (LSR-...TS)



Note

- ① **Complete device** (see Page 26)
For personnel protection
Contacts: 1NO-1NC or 2NC
For swing doors with fixed connection to the door/hinge pin

Full-Size DIN Safety Interlock Switch (LS4-...ZB)



Notes

- ① **Complete device** (see Page 27)
Narrow enclosure version
For personnel protection
Contacts: 1NO, 1NO-1NC
- ② **Actuator**
Included with switch, not orderable as a separate item
Multiple coding
For horizontal or vertical operation

Product Selection

LS-Titan Miniature DIN Safety Interlock Switches

Key Interlock Switch

Key Interlock Switch—LS-...ZB^①

Contacts	Contact Sequence	Contact Travel	Connection	Catalog Number (Includes Key)
2NC with positive opening		—	Screw terminal	LS-S02-ZB
1NO and 1NC with positive opening		—	Screw terminal	LS-S11-ZB
		Snap action contacts	Screw terminal	LS-S11S-ZB

Door-Flap Switch

Door-Flap Switch—LSR-...TKG^①


Contacts	Contact Sequence	Contact Travel	Connection	Catalog Number (Includes Key)
2NC with positive opening			Screw terminal	LSR-S02-1-I-TKG
1NO and 1NC with positive opening			Screw terminal	LSR-S11-1-I-TKG

Door-Hinge Switch

Door-Hinge Switch—LSR-...TS^①

Contacts	Contact Sequence	Contact Travel	Connection	Catalog Number (Includes Key)
2NC with positive opening			Screw terminal	LSR-S02-1-I-TS
1NO and 1NC with positive opening			Screw terminal	LSR-S11-1-I-TS

Replacement Safety Interlock Key

Replacement Safety Interlock Key^①

Description	Catalog Number
Replacement key for miniature DIN key interlock switches (only models LS-...ZB).	LS-XB-ZB

Note

① For dimensions, see **Page 31**.

LS-Titan Full-Size DIN Safety Interlock Switches**Key Interlock Switch****Full-Size DIN—LS4-...ZB** ^{①②}




Contacts	Contact Sequence	Contact Travel	Connection	Catalog Number (Includes Key)
1NO and 1NC with positive opening		—	Screw terminal	LS4-S11-1-I-ZB

LS-Titan Solenoid Safety Interlock Switches**Switch Body without Key****Switch Body without Key—LS-...ZBZ** ^{①②③}

Operation	Operating Voltage	Contacts	Contact Sequence	Catalog Number (Key not Included)
Power to unlock (mechanical bypass present)	24 Vdc	1NO and 1NC with positive opening		LS-S11-24DFT-ZBZ-X
		2NC with positive opening		LS-S02-24DFT-ZBZ-X
	120 Vac (50/60 Hz)	1NO and 1NC with positive opening		LS-S11-120AFT-ZBZ-X
		2NC with positive opening		LS-S02-120AFT-ZBZ-X
Power to lock (mechanical bypass present)	24 Vdc	1NO and 1NC with positive opening		LS-S11-24DMT-ZBZ-X
		2NC with positive opening		LS-S02-24DMT-ZBZ-X
	120 Vac (50/60 Hz)	1NO and 1NC with positive opening		LS-S11-120AMT-ZBZ-X
		2NC with positive opening		LS-S02-120AMT-ZBZ-X

Notes① For dimensions, see **Page 31**.② For mounting instructions, see **Page 30**.③ Key ordered separately, see **Page 28**.

LS-Titan Solenoid Safety Interlock Keys**Keys Only—LS-...ZBZ** ^{①②}

	Description	Application	Catalog Number
LS-XG-ZBZ 	Flat actuator	For sliding doors	LS-XG-ZBZ
LS-X...-ZBZ 	Angled actuator, short	For swing doors starting at 250 mm in width	LS-XW-ZBZ
	Angled actuator, long	For swing doors starting at 250 mm in width	LS-XWA-ZBZ
LS-XF-ZBZ 	Angled, flexible actuator	For doors that do not close precisely	LS-XF-ZBZ
LS-XFG-ZBZ 	Even, flexible coasting actuator	For doors that do not close precisely	LS-XFG-ZBZ
LS-XNG-ZBZ 	Flat, compensating actuator	Increased tolerance in closing direction for inaccurately closing doors	LS-XNG-ZBZ
LS-XNW-ZBZ 	Angled, compensating actuator	Increased tolerance in closing direction for inaccurately closing doors	LS-XNW-ZBZ

Notes

① Switch body ordered separately, see **Page 27**.

② For mounting instructions, see **Page 30**.

Technical Data and Specifications

LS-Titan Safety Interlock Switches


Units			LS-...ZBZ	LS-...ZB	LS4...ZB
General					
Standards			IEC/EN 60947	IEC/EN 60947	IEC/EN 60947
Climatic proofing			①	①	①
Ambient temperature	°C		−25... +0	−25... +70	−25... +70
Mounting position			As required	As required	As required
Protection type			IP65	IP65	IP65
Terminal capacities					
Solid	mm ²		1 x (0.75–2.5)/2 x (0.75–1.5)	1 x (0.75–2.5)/2 x (0.75–1.5)	1 x (0.75–2.5)/2 x (0.75–1.5)
Flexible with ferrule	mm ²		1 x (0.75–2.5)/2 x (0.75–1.5)	1 x (0.75–2.5)/2 x (0.75–1.5)	1 x (0.75–2.5)/2 x (0.75–1.5)
Contacts/Switching Capacity					
Rated impulse withstand voltage	U _{imp}	Vac	4000	6000	6000
Rated insulation voltage	U _i	V	400	500	500
Overvoltage category/pollution degree			III/3	III/3	III/3
Burden Current					
AC-15					
24V	I _e	A	6	10	10
230V/240V	I _e	A	6	6	6
400V/415V	I _e	A	4	4	4
DC-13					
24V	I _e	A	3	3	3
110V	I _e	A	0.8	0.8	0.8
220V	I _e	A	0.3	0.3	0.3
Supply frequency		Hz	max. 400	max. 400	max. 400
Short-circuit rating to IEC/EN 60947-5-1 Max. fuse		A gG/gL	6	6	6
Repetition accuracy		mm	± 0.02	± 0.02	± 0.02
Mechanical Variables					
Lifespan					
Standard-action contact	Operations	x 10 ⁶	1	10	10
Snap-action contact	Operations	x 10 ⁶	—	—	—
Mechanical shock resistance (half-sinusoidal shock, 20 ms)					
Standard-action contact		g	10	25	5
Snap-action contact		g	—	—	—
Operating frequency	Operations/h		≤ 800	≤ 1800	≤ 1800
Actuation					
Mechanical					
Actuating force at beginning/end of stroke					
ZB/ZBZ (push in/pull out)		N	25/15	10/5	15/20
Mechanical holding force according to GS-ET-19 (04/2004)					
XG, XW		N	1500	N/A	N/A
XFF, XNG, XWA		N	1300	N/A	N/A
XF		N	750	N/A	N/A
XNW		N	500	N/A	N/A
Electromechanical					
For magnet					
Power consumption					
at 120 Vac		VA	8	N/A	N/A
at 230 Vac		VA	11	N/A	N/A
at 24 Vdc		W	8	N/A	N/A
Pickup and dropout values		x U _s	0.85–1.1	N/A	N/A
Magnet duty factor		% ED	100	N/A	N/A

Note

① Damp heat, constant, to IEC 60068-2-78; damp heat, cyclical, to IEC 60068-2-30.


Mounting Instructions

LS-...ZB, TKG, TS




Actuator can be repositioned for horizontal or vertical installation. The operating heads can be rotated manually in 90° steps to suit the specified direction of operation.

LS4-...ZB




Actuator can be repositioned for horizontal or vertical installation. The operating heads can be rotated manually in 90° steps to suit the specified direction of operation.

LS-...ZBZ



The operating head can be rotated manually in 90° steps to suit the specified level of actuation.




In the event of a loss of voltage, (e.g., during commissioning), the spring-powered LS-...-...FT-ZBZ can be released with a screwdriver. **The auxiliary release mechanism must be sealed.**

Dimensions

Approximate Dimensions in Inches (mm)

Safety Position Switches








LS...-ZB



Notes

- ① The auxiliary release mechanism must be sealed for proper operation.
- ② Can be used as stop with the corresponding material selection and design.

Approximate Dimensions in Inches (mm)


Actuators**LS-XG-ZBZ****LS-XW-ZBZ****LS-XF-ZBZ****LS-XNW-ZBZ** ②**LS-XNG-ZBZ** ②**LS-XFG-ZBZ****LS-XWA-ZBZ** ③**Notes**

- ① Distance to device head = 0.1–3.0 mm.
- ② Fixing only allowed with M5 fixing screw and washer according to DIN EN ISO 7093.
- ③ Pin with a 4 mm pin after mounting.

Approximate Dimensions in Inches (mm)


Safety Door Flap Switch

LSR-.../TKG




Safety Hinge Switch

LSR-.../TS





Safety Position Switches

LS-...-ZB



Approximate Dimensions in Inches (mm)

Safety Position Switches**LS4...ZB****Actuator—Included with Switch Above**

Eaton's Electrical Sector is a global leader in power distribution, power quality, control and automation, and monitoring products. When combined with Eaton's full-scale engineering services, these products provide customer-driven PowerChain™ solutions to serve the power system needs of the data center, industrial, institutional, public sector, utility, commercial, residential, IT, mission critical, alternative energy and OEM markets worldwide.

PowerChain solutions help enterprises achieve sustainable and competitive advantages through proactive management of the power system as a strategic, integrated asset throughout its life cycle, resulting in enhanced safety, greater reliability and energy efficiency. For more information, visit www.eaton.com/electrical.

Eaton Corporation
Electrical Sector
1111 Superior Ave.
Cleveland, OH 44114
United States
877-ETN-CARE (877-386-2273)
Eaton.com

©2011 Eaton Corporation
All Rights Reserved
Printed in USA
Publication No. CA05208003E / Z10714
January 2011



PowerChain Management is a registered trademark of Eaton Corporation.

All other trademarks are property of their respective owners.