

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0026324044

Status:

Inactive

Overview:

kk

Description:

3.96mm (.156") KK® IDT Trifurcon™ Contact, 4 Circuits, Gold (Au), Feed-To, 18 Solid or Fused Stranded, Yellow ID Strip

Documents:

Drawing (PDF)

Agency Certification

UL

E29179

General

Product Family

IDT and Solder Connectors

Series

7674

Comments

Trifurcon™ contact

Crimp Quality Equipment

Yes

Overview

kk

Product Name

KK®, Trifurcon™

Physical

Circuits (Loaded)

4

Flammability

94V-2

Gender

Female

Glow-Wire Compliant

No

Lock to Mating Part

Yes

Number of Rows

1

Packaging Type

Bag

Panel Mount

No

Pitch - Mating Interface

3.96mm (.156")

Temperature Range - Operating

0°C to +75°C

Wire Size AWG

18 Solid, 18 Stranded Topcoat

Electrical

Voltage - Maximum

250V

Material Info

Old Part Number

A-7674-D04A502A


Reference - Drawing Numbers

Product Specification

PS-7660

Sales Drawing

SDA-7674-*



Series
image - Reference only

EU RoHS

China RoHS

Compliance Status

Not Reviewed

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7674Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Insertion Tool for 3.96mm (.156") Pitch KK® IDT Crimp Terminals	0638133503
IDT - Semi-automatic - Bench-Top Terminator	0011200418
IDT - Manual - Handtool	0011215196
IDT Manual Handtool - Bench-Top Terminator	0621000400
IDT - Semi-automatic - Bench-Top Terminator	0623000156

This document was generated on 02/23/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION