

MICRO SWITCH
a Honeywell Division

FED.MFG.CODE 91929

SWITCH - BASIC

CATALOG LISTING

V3L-3053

CQ-X1864

CATALOG LISTING
V3L-3053
PAGE 1 OF 1

ISSUE
M
2

REVISIONS

A 0005105
KSR
APR 04

REPLACES X100985-V3L

RELEASE NO. PR-22260

CHECK

27 APR 04

AK



CHECK

CHECK

28 JUN 96

DCS

DDM/CAD
DRAWN




NOTES

- 1 - SWITCH MATERIALS WILL WITHSTAND TEMPERATURE OF 300°F
- 2 - CAUTION: OVERTRAVEL FORCE ON LEVER MUST NOT RESULT IN AN OVERTRAVEL FORCE ON PLUNGER EXCEEDING FIVE POUNDS
- 3 - TERMINALS ARE PLATED FOR SOLDERING

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE --- 159 GRAMS MAX
RELEASE FORCE --- 17 GRAMS MIN
DIFFERENTIAL TRAVEL --- .014 MAX
OVERTRAVEL --- .036 MIN
RELEASE TRAVEL --- .008 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L215 15.1A 1/2HP 125, 250 or 277 VAC
1/2A 125 VDC, 1/4A 250 VDC
5A 120 VAC "L"



SCALE FULL

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE

ONE PLACE (.0) ±.030
TWO PLACE (.00) ±.015
THREE PLACE (.000) ±.005
ANGLES ±

WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[V3L-3053](#)