


THESE DRAWINGS ARE THE PROPERTY OF QUALTEK ELECTRONICS AND NOT TO BE REPRODUCED FOR OR COMMUNICATED TO A THIRD PARTY WITHOUT THE EXPRESS WRITTEN PERMISSION OF AN OFFICER OF QUALTEK ELECTRONICS.

REVISION			
REV.	DESCRIPTION	DATE	APPROVED
B	RoHS Compliancy	06-01-06	DP
C	Updated Graphics and Dimensions	06-02-10	LY
D	Added RTI Information	03-11-11	LY
E	Updated Dimensions	03-23-11	LY
F	Added Terminal Material and Tolerances	03-29-11	LY



NOTES:

RATING:

UL, CSA: 15A 250V AC
VDE, NEMKO, CCC, KTL: 10A 250V AC
APPROVALS: UL, CSA, VDE, NEMKO, CCC
PANEL THICKNESS: 0.8~1.5mm
MATERIAL:
BODY INSULATOR: PC BLACK COLOR
TERMINAL: BRASS STRIP C2680 NICKEL PLATED
UL 746B RELATIVE TEMPERATURE INDEX:
TENSILE STRENGTH: 125°C
TENSILE IMPACT STRENGTH: 115°C
ELECTRIC STRENGTH: 125°C
RoHS COMPLIANT

CONTROLLED

Dim range (mm)		Tolerance +/- (mm)		Qualtek Electronics Corp. PPC DIVISION		
0-1		0.15		Part Number: 716W-X2/03 RoHS Compliant		
1-6		0.20		Description: AC RECEPTACLE		
6-18		0.30		UNIT: mm REV. F		
18-50		0.50		Drawn / Date Checked / Date Approved / Date		
50-120		0.70		B.ZHANG 03-10-04 03-10-04 JJH / 03-10-04		
120-250		0.90				
250-500		1.20				