

SPECIFICATION FOR APPROVAL

客 戶

CUSTOMER:

客 戶 料 號

CUSTOMER PARTS NO.:

品 名

AC AXIAL FAN

DESCRIPTION:

機種

MODEL NO.:

4E-115B-17W

檔案序號

FILE NO.:

A4E0011LB-B1

核示 ISSUE	研發 R&D	品保 QA	版數 REVISION

客 戶 承 認

CUSTOMER APPROVAL

BI-SONIC TECHNOLOGY CO., LTD

HEADQUARTER: 2F, NO. 137, LANE 235, PAO CHAIO RD.,

HSIN-TIEN CITY, TAIPEI HSIEN, 231, TAIWAN , R.O.C.

TEL:(02)89192168 FAX:(02)89192169

PERFORMANCE SPECIFICATION

PRODUCT TITLE : AC AXIAL FAN

MODEL NO : 4E-115B-17W

1、SCOPE：

THIS SPECIFICATION DEFINES THE ELECTRICAL AND MECHANICAL CHARACTERISTICS OF THE AC AXIAL FLOW FAN·THE FAN MOTOR IS SHADED POLE MOTOR WITH EXTERNAL ROTOR·

2、ELECTRICAL CHARACTERISTICS：

ALL MEASUREMENTS PERFORMED AT 20-30℃ ROOM TEMPERATURE &50-70% R.H.
UNLESS OTHERWISE SPECIFIED. SPEED MEASURED AFTER CONTINUOUS 10 MINUTE
OPERATION AT RATED VOLTAGE IN CLEAN AIR.

ITEM	DESCRIPTION	UNIT	SYMBOL	SPEC.		CONDITION
				50Hz	60Hz	
1	RATED VOLTAGE	VOLTS	V	115	AC	
2	OPERATION VOLTAGE	VOLTS	V	105~125	AC	
3	INPUT CURRENT	AMP	A	0.21MAX	0.20MAX	AT RATED VOLTAGE
4	INPUT POWER	WATTS	W	21MAX	19MAX	AT RATED VOLTAGE
5	ROTATION SPEED	RPM	RPM	1600 ^{+20%} _{-10%}	1700 ^{+20%} _{-10%}	AT RATED VOLTAGE FREE AIR
6	ACOUSTICAL NOISE (AVG)	dB(A)	dB(A)	25 ^{+20%} _{-10%}	30 ^{+20%} _{-10%}	DETAILS SEE ATTACHED PAGE.
7	MAX. AIR-FLOW	CFM	Q	52.3 ^{+20%} _{-10%}	58.4 ^{+20%} _{-10%}	TWO-CHAMBER METHODS DETAILS SEE ATTACHED PAGE.
8	MAX. AIR-PRESSURE	mmH ₂ O	P	2.4 ^{+20%} _{-10%}	2.7 ^{+20%} _{-10%}	TWO-CHAMBER METHODS DETAILS SEE ATTACHED PAGE.
9	INSULATION RESISTANCE	MEG. OHM	MΩ	100MΩ MIN. AT 500V DC		BETWEEN FRAME AND LEAD WIRE.
10	DIELECTRIC STRENGTH			WITHSTANDING AT 1400V AC 60Hz. FOR 1 MINUTE		BETWEEN FRAME AND LEAD WIRE.

**BI-SONIC TECHNOLOGY
CO., LTD.**

FILE NO：

A4E0011LB-B1

REVISIONS：

ITEM	DESCRIPTION	SPEC.	
11	ROTATION	CW VIEW FROM NAME PLATE SIDE	
12	AIR-FLOW DIRECTION	AIR INTAKE OVER THE STRUTS	
13	INSULATION CLASS	CLASS B	
14	LIFE EXPECTANCY	50000 HOURS CONTINUOUS	□
15	SAFETY APPROVAL	UL. CSA. TUV. CE. IP54.	

□ LIFE IS DEFINED AS THE TIME MOTOR SPEED DECREASED MORE THAN 30% COMPARED WITH INITIAL VALUE.

3、MECHANICAL

- 3-1. DIMENSIONS----- SEE SECTION 8
- 3-2. FRAME ----- METAL CONSTRUCTION WITH ALUMINUM DIE-CASTING.
- 3-3. IMPELLER----- MADE OF METAL MATERIAL SPOT WELDING ON ROTOR SHELL.
- 3-4. COATING ----- CED (CATHONIC ELECTRODEPOSITION COATING WITH EPOXY) COATING ON METAL SURFACE BE CAPABLE OF IMPACT RESISTANT AND ABRASION RESISTANT.
- 3-5. BEARING SYSTEM ----- BALL BEARING
- 3-6. WEIGHT ----- 600 GRAMS
- 3-7. LEAD WIRE ----- 1007 AWG # 22
- 3-8. TYPE OF OUTPUT : LEADWIRE
- 3-9. PLASTIC PARTS ----- UNFLAMABLE MATERIAL , MEET UL 94V-0 RATING.

4、ENVIRONMENTAL :

- 4-1. OPERATING TEMPERATURE ----- -10 TO +70℃
- 4-2. STORAGE TEMPERATURE ----- -30 TO +75℃

**BI-SONIC TECHNOLOGY
CO., LTD**

FILE NO :

A4E0011LB-B1

REVISIONS :

4-3. OPERATING HUMIDITY----- RH 20% ~ 85%


5、PROTECTION：

5-1. IMPEDANCE PROTECTION

IMPEDANCE OF MOTOR COIL WINDING PROTECTS MOTOR FROM
FLAMING IN THE CONDITION OF 72 Hrs LOCKED ROTOR AT RATED
VOLTAGE·

6、ACOUSTICAL NOISE：

6-1. MEASUREMENT SET-UP



6-2. MEASUREMENT PERFORMED IN ANECHOIC TEST CHAMBER
UNDER FREE AIR CONDITION ·

6-3. CHAMBER BACKGROUND NOISE 17dB MAX ·

6-4. READING TAKEN FROM SPECTRUM ANALYZER ·


6-5. NOISE DISTRIBUTION CURVE SEE ATTACHED PAGE ·

7、STATICS PRESSURE VS AIR FLOW CURVE：

MEASURED PER TWO CHAMBER METHOD ·
DATA-CURVE SEE ATTACHED PAGE ·

8、DIMENSIONS DRAWING：

UNIT:mm



BI-SONIC TECHNOLOGY
CO., LTD.

FILE NO：

A4E0011LB-B1

REVISIONS：

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bi-Sonic:](#)

[4E-115B-17 W-G/ROHS](#)