

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD 230-702.

2. SEE SHEET 2 FOR WIRING SCHEMATIC.

3. HI-POT AT 300 VDC FOR 10 MILLISEC, 100 MEGOHMS MIN INSULATION RESISTANCE.

4


ASSY IDENTIFICATION LABEL TO BE LOCATED AS SHOWN, LABEL TO READ:

TE TYCO ELECTRONICS P/N

YYWW

COUNTRY OF ORIGIN

IF OUTSIDE USA



500.0±25.4 [19.68±1.00]	—	—	—	—	—	1-636218-3
1092.2±25.4 [43.00±1.00]	—	—	—	—	—	1-636218-2
660.4±25.4 [26.00±1.00]	—	—	—	—	—	1-636218-1
381±25.4 [15.00±1.00]	—	—	—	—	—	1-636218-0
20000±127.0 [787.40±5.00]	—	—	—	—	—	636218-9
10000±101.6 [393.70±4.00]	—	—	—	—	—	636218-8
4000±76.2 [157.48±3.00]	—	—	—	—	—	636218-7
15240±101.6 [608.00±4.00]	—	—	—	—	—	636218-6
1200±25.4 [47.24±1.00]	—	—	—	—	—	636218-5
5000±76.2 [196.85±3.0]	—	—	—	—	—	636218-4
3000±63.5 [118.0±2.5]	—	—	—	—	—	636218-3
2000±38.1 [78.75±1.5]	—	—	—	—	—	636218-2
1000±25.4 [39.37±1.0]	—	—	—	—	—	636218-1
L	5 OVERMOLD QTY=1	4 PRE- OVERMOLD QTY=1	3 LABEL QTY=1	2 CABLE,34 TW PR, SCS1, 90 OHM (SEM) QTY=AR	1 CONNECTOR KIT .8mm CHAMP QTY= 2	PART NUMBER


A

D

C

D

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. MORNINGSTAR 11-15-96 CHK J.A.HACKMAN 11-18-96 APVD J.A.HACKMAN 11-18-96 PRODUCT SPEC APPLICATION SPEC WEIGHT CUSTOMER DRAWING		Tyco Electronics Corporation Harrisburg, PA 17105-3608 CABLE ASSY,CHAMP 0.8mm, OFFSET, 68 POSN TO CHAMP - A2 00779 C=636218 N.T.S. 2 OF 2 F1	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± + - 2 PLC ± + - 3 PLC ± + - 4 PLC ± + - ANGLES ± - FINISH		NAME SIZE CAGE CODE DRAWING NO RESTRICTED TO	
MATERIAL					



THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
COPYRIGHT		ALL RIGHTS RESERVED.	
BY TYCO ELECTRONICS CORPORATION.			

LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

A

D

C

D