

**Specifications**

Output voltage	12 V dc at 500 mA	
Primary rated input	120 V ac 60 Hz 10 W	
Primary exciting current	70 mA rms max.	
Secondary rated voltage & current	no load voltage (max.)	19 V max.
	full load volatge (200 mA)	12 V $\pm$ 5%
Temperature rise of primary winding (full load)	70°C max. using resistance method	
Insulation resistance	$\geq$ 100 M Ohm at 500 V dc	
HI-POT test	from input to output for 1 min.	1240 V ac at 2 mA
	from input to output for 1 sec.	1600 V ac at 2 mA
	from primary to seconardy winding for 1 sec.	1600 V ac at 2 mA
	from primary winding to core for 1 sec.	1600 V ac at 2 mA
	from secondary winding to core for 1 sec.	750 V ac at 2 mA
Safety standard	UL/cUL	
RoHS compliant	yes	
Test conditions	Ambient temp	40°C $\pm$ 2°C
	Humidity	90-95% 96 hours at Full Load
	Rated voltage	8 hours at full load
Color	Case	black
	Cord	black
	Plug top	black



CUI INC

Part No: DPD120050-P5P-SZ


Description: linear power supply

Date: 2/27/2006


Unit: mm

Page No: 2 of 7

Test Diagram



Label





CUI INC

Part No: DPD120050-P5P-SZ

Description: linear power supply

Date: 2/27/2006


Unit: mm

Page No: 3 of 7

Mechanical Drawing

Tolerance: ± 1

Weight 248 g





CUI INC

Part No: DPD120050-P5P-SZ


Description: linear power supply

Date: 2/27/2006

Unit: mm

Page No: 4 of 7

Cord



#24AWG X2C BLACK/WHITE WIRE BLACK WIRE IN OUTER, BLACK/WHITE WIRE IN INNER

WIRE OD: $\phi 1.8 \times 3.6$



Parameter request	
VIBRATION TEST	a. 160'
	b. WEIGHT 20g
	c. 40 ROUND/MINUTE
	d. OVER 1000 COUNT MIN



CUI INC

Part No: DPD120050-P5P-SZ


Description: linear power supply

Date: 2/27/2006

Unit: mm

Page No: 5 of 7

Circuit Diagrams





CUI INC

Part No: DPD120050-P5P-SZ

Description: linear power supply



Date: 2/27/2006

Unit: mm

Page No: 6 of 7

Packaging

Tolerance: ± 1





CUI INC

Part No: DPD120050-P5P-SZ

Description: linear power supply

Date: 2/27/2006

Unit: mm

Page No: 7 of 7

Packaging

Tolerance: +7/-0

EXTERNAL CARTON MATERIAL:A=B(6mm)

INTERNAL CARTON MATERIAL:A-B(3mm)

CARTON SIZE: 376X357X190mm

Q'TY: 60pcs(20X3X1)

