





LOC		DIST		REVISIONS			
AD	00	P	LYR	DESCRIPTION	DATE	OWN	APVD
		A		REVISED PER ECO-11-013132	13JUL2011	HMR	MH

- △ CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- △ 0.76µm MIN TIN OVER 1.27µm MIN NICKEL
- △ MATERIAL: CONTACT - COPPER ALLOY
SHIELD - PHOSPHOR BRONZE
HOUSING - LCP, UL94V-0
CHICKLET - GLASS FILLED POLYESTER
- △ REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- △ DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- △ SEATING HEIGHT TO BOARD SURFACE.
- △ CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- △ DATE CODE
- △ PART NUMBER



RECOMMENDED PRINTED
CIRCUIT BOARD LAYOUT
COMPONENT SIDE OF PRINTED CIRCUIT BOARD

THIS DRAWING IS A CONTROLLED DOCUMENT.		OWN B. CARBO	08DEC04	5120794-1			
DIMENSIONS:		CHK R. PATTERSON	08DEC04	PART NUMBER			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD R. PATTERSON	08DEC04	TE Connectivity			
mm		PRODUCT SPEC		NAME			
9 PLC ±.2		108-1957		RECEPTACLE ASSEMBLY, 50 POSITION			
3 PLC ±0.13		APPLICATION SPEC		UNIVERSAL GUIDE PIN, RIGHT HAND,			
5 PLC ±0.05		114-13020		10 ROW, DUAL BEAM, Z-PACK HS3			
4 PLC ±.1		WEIGHT		SIZE CAGE CODE DRAWING NO			
FINISH		A100779		C=5120794			
SOLDER TAIL		CUSTOMER DRAWING		RESTRICTED TO			
CONTACT		SCALE 4:1		SHEET 1 OF 1			