



# SPECIFICATION

(Reference sheet)

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor


- Samsung P/N : **CL21A226KPCLRNC**
- Description : **CAP, 22uF, 10V, ±10%, X5R, 0805**

## A. Samsung Part Number

**CL 21 A 226 K P C L R N C**  
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor		
② Size	0805 (inch code)	L : $2.00 \pm 0.20$ mm	W : $1.25 \pm 0.20$ mm
③ Dielectric	X5R	⑧ Thickness division	Low profile
④ Capacitance	22 uF	Inner electrode	Ni
⑤ Capacitance tolerance	±10 %	Termination	Cu
⑥ Rated Voltage	10 V	Plating	Sn 100% (Pb Free)
⑦ Thickness	$0.85 \pm 0.10$ mm	⑨ Product	Size control code
		⑩ Special	Reserved for future use
		⑪ Packaging	Cardboard Type, 7" reel

## B. Structure & Dimension



Samsung P/N	Dimension(mm)			
	L	W	T	BW
CL21A226KPCLRNC	$2.00 \pm 0.20$	$1.25 \pm 0.20$	$0.85 \pm 0.10$	$0.50 +0.20/-0.30$

### C. Samsung Reliability Test and Judgement Condition

	Judgement	Test condition
<b>Capacitance</b>	Within specified tolerance	120Hz $\pm 20\%$ / 0.5 $\pm 0.1$ VRms
<b>Tan δ (DF)</b>	0.1 max.	*A capacitor prior to measuring the capacitance is heat treated at 150 $+0/-10$ for 1hour and maintained in ambient air for 24 $\pm 2$ hours.
<b>Insulation Resistance</b>	10,000Mohm or 100Mohm $\times \mu$ F Whichever is smaller	Rated Voltage 60~120 sec
<b>Appearance</b>	No abnormal exterior appearance	Microscope (x10)
<b>Withstanding Voltage</b>	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
<b>Temperature Characteristics</b>	X5R (From -55 °C to 85 °C, Capacitance change should be within $\pm 15\%$ )	
<b>Adhesive Strength of Termination</b>	No peeling shall be occur on the terminal electrode	500g·f, for 10 $\pm 1$ sec.
<b>Bending Strength</b>	Capacitance change : within $\pm 12.5\%$	Bending to the limit (1mm) with 1.0mm/sec.
<b>Solderability</b>	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245 $\pm 5$ °C, 3 $\pm 0.3$ sec. (preheating : 80~120°C for 10~30sec.)
<b>Resistance to Soldering Heat</b>	Capacitance change : within $\pm 7.5\%$ Tan δ, IR : initial spec.	Solder pot : 270 $\pm 5$ °C, 10 $\pm 1$ sec.
<b>Vibration Test</b>	Capacitance change : within $\pm 5\%$ Tan δ, IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
<b>Moisture Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.2 max IR : 500Mohm or 12.5Mohm $\times \mu$ F Whichever is smaller	With rated voltage 40 $\pm 2$ °C, 90~95%RH, 500+12/-0hrs
<b>High Temperature Resistance</b>	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.2 max IR : 1,000Mohm or 25Mohm $\times \mu$ F Whichever is smaller	With 150% of the rated voltage Max. operating temperature 1,000+48/-0hrs
<b>Temperature Cycling</b>	Capacitance change : within $\pm 7.5\%$ Tan δ, IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow$ 25°C $\rightarrow$ Max. operating temperature $\rightarrow$ 25°C  5 cycle test

※ The reliability test condition can be replaced by the corresponding accelerated test condition.

### D. Recommended Soldering method :

Reflow ( Reflow Peak Temperature : 260 $\pm 5$  °C, 30sec )

 Product specifications included in the specifications are effective as of March 1, 2013.

Please be advised that they are standard product specifications for reference only.

We may change, modify or discontinue the product specifications without notice at any time.

So, you need to approve the product specifications before placing an order.

Should you have any question regarding the product specifications,  
please contact our sales personnel or application engineers.

## **- Disclaimer & Limitation of Use and Application -**

*The products listed in this Specification sheet are **NOT** designed and manufactured for any use and applications set forth below.*

*Please note that any misuse of the products deviating from products specifications or information provided in this Spec sheet may cause serious property damages or personal injury.*

*We will **NOT** be liable for any damages resulting from any misuse of the products, specifically including using the products for high reliability applications as listed below.*

*If you have any questions regarding this 'Limitation of Use and Application', you should first contact our sales personnel or application engineers.*

- ① Aerospace/Aviation equipment*
- ② Automotive or Transportation equipment (vehicles, trains, ships, etc)*
- ③ Medical equipment*
- ④ Military equipment*
- ⑤ Disaster prevention/crime prevention equipment*
- ⑥ Any other applications with the same as or similar complexity or reliability to the applications set forth above.*