

Flasher - Relay Output

FS500 Series


Solid State Flasher

Flashers



10 YEAR WARRANTY


- Solid State Circuitry--Relay Output
- Industrial Standard Octal Plug-in
- Adjustable Flash Rate
10 ... 100 FPM
- 10 A DPDT Output Contacts

Approvals:  (some models)

Description

The FS500 Series flash rate is adjustable from 10 to 100 flashes per minute. A locknut is provided to hold selected flash rate. The long-life electronic circuit combined with a quality electromechanical relay provides flexibility and reliability in most applications.

Connection




Dashed lines are internal connections.

Operation


Upon application of input voltage, the output relay is energized and the ON time begins. At the end of the ON time, the output relay de-energizes and the OFF time begins. At the end of the OFF time, the output is energized and the cycle repeats as long as input voltage is applied.

Reset: Removing input voltage resets the output and the sequence.

Function



Mechanical View



Available Models-

•FS512

•FS524

•FS590

Don't see what you need? Call us for a minimum quantity and price quote!

Ordering Table

Input	CSA	Part Number
12 V DC	*	FS512
24 V AC/DC	*	FS524
120 V AC/DC	*	FS590
230 V AC		FS599

Technical Data

Specifications

Mode of Operation
Flash Rate

ON/OFF Ratio

Input

Input Voltage
Tolerance 12 V DC & 24 V DC/AC
120 ... 230 V AC/DC

Frequency

Output

Type
Rating

Mechanical

Mounting
Termination

Protection

Isolation Voltage
Polarity

Environmental

Operating/Storage Temperature
Weight

ON/OFF recycling flasher with adjustable flash rate
Adjustable from 10 ... 100 operations per minute
(guaranteed range)
≈ 50%

12 V DC, 24 V AC/DC, 120 V AC/DC, 230 V AC
-15% ... +20%
-20% ... +10%
50 ... 60 Hz


Electromechanical relay DPDT
10 A resistive at 120/240 V AC & 28 V DC;
1/3 hp at 120/ 240 V AC

Plug-in socket
8 pin Octal plug


≥ 1500 V RMS input to output
DC units are reverse polarity protected

-20°... +60°C / -30° ... +85°C
≈ 5.8 oz (164 g)


Accessories




Panel mount kit
P/N: **BZ1**



Octal
8-pin socket
P/N: **NDS-8**



Hold down clips
P/N: **PSC8**



DIN rail P/Ns:
C103PM (Al)

See accessory pages for specifications.

FS501B01 09.10