




COIL: $\bullet$ +25 °C	
RESISTANCE	2640 OHMS $\pm$ 10%
NOMINAL VOLTAGE	27-56 VDC
MUST OPERATE	18.0 VDC
MUST RELEASE	10.9 VDC MAX, 1.8 VDC MIN

ENVIRONMENT:

VIBRATION 10 CPS TO 2000 CPS @ 20 g's

SHOCK 50 g's 11 MS. DURATION


TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE 6 MS MAX.

RELEASE 5 MS MAX.

CONTACT BOUNCE 2 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 2A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 3/9/94	CK. 2/9/94
-----------------	------------



**COMMUNICATIONS
INSTRUMENTS, INC.**

CUST. GENICOM
CUST. NO. 3SAV5534M2

TYPE "HMS" RELAY

HMS1230S07