

Thin Film MELF Resistors



FEATURES

- MELF resistor with high power rating
- AEC-Q200 qualified
- Advanced metal film technology
- Best in class pulse load capability
- Intrinsic sulfur resistance
- Material categorization:
for definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
GREEN
(5-2008)

LINKS TO ADDITIONAL RESOURCES



SMM0207 thin film MELF resistors are the perfect choice for most fields of modern professional electronics where reliability and stability is of major concern at higher power rating and higher operating voltage. The typical applications in the fields of automotive, industrial and medical equipment reflect the outstanding level of proven reliability.

APPLICATIONS

- Automotive
- Telecommunication
- Industrial
- Medical equipment

TECHNICAL SPECIFICATIONS

DESCRIPTION	SMM0207
DIN size	0207
Metric size code	RC6123M
Resistance range	0.16 Ω to 10 MΩ
Resistance tolerance	± 5 %; ± 1 %; ± 0.5 %; ± 0.25 %; ± 0.1 %
Temperature coefficient	± 100 ppm/K; ± 50 ppm/K; ± 25 ppm/; ± 15 ppm/K
Rated dissipation P_{70} ⁽¹⁾	1.0 W
Operating voltage, U_{max} . AC _{RMS} /DC	350 V
Permissible film temperature, ϑ_F max. ⁽¹⁾	155 °C
Operating temperature range ⁽¹⁾	-55 °C to 155 °C
Internal thermal resistance (typical) ⁽¹⁾	26 K/W
Permissible voltage against ambient (insulation):	
1 min; U_{ins}	500 V
Failure rate: FIT _{observed}	≤ 0.05 x 10 ⁻⁹ /h
Zero-Ohm-Resistor: OMM0207	$R_{max.} = 10 \text{ m}\Omega$; $I_{max.} = 5 \text{ A}$

Note

⁽¹⁾ Please refer to APPLICATION INFORMATION below

APPLICATION INFORMATION

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.

These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime

MAXIMUM RESISTANCE CHANGE AT RATED DISSIPATION				
OPERATION MODE		PRECISION	STANDARD	POWER
Rated dissipation, P_{70}	SMM0207	0.125 W	0.4 W	1.0 W
Operating temperature range		-10 °C to 85 °C	-55 °C to 125 °C	-55 °C to 155 °C
Permissible film temperature, ϑ_F max.		85 °C	125 °C	155 °C
	SMM0207	100 Ω to 511 kΩ	1 Ω to 1 MΩ	1 Ω to 1 MΩ
Max. resistance change at P_{70} for resistance range, $ \Delta R/R $ after:	1000 h	≤ 0.05 %	≤ 0.15 %	≤ 0.25 %
	8000 h	≤ 0.1 %	≤ 0.3 %	≤ 0.5 %
	225 000 h	≤ 0.25 %	≤ 1.0 %	-

Note

- The presented operation modes do not refer to different types of resistors, but actually show examples of different loads, that lead to different film temperatures and different achievable load-life stability (drift) of the resistance value. A suitable low thermal resistance of the circuit board assembly must be safeguarded in order to maintain the film temperature of the resistors within the specified limits. Please consider the application note "Thermal Management in Surface-Mounted Resistor Applications" (www.vishay.com/doc?28844) for information on the general nature of thermal resistance

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE				
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES
SMM0207	± 100 ppm/K	± 5 %	0.16 Ω to 0.91 Ω	E24
	± 50 ppm/K	± 1 %	1 Ω to 10 MΩ	E24; E96
		± 0.5 %	1 Ω to 2.21 MΩ	E24; E192
	± 25 ppm/K	± 0.5 %	43 Ω to 1 MΩ	E24; E192
		± 0.25 %		
		± 0.1 %		
	± 15 ppm/K	± 0.5 %	100 Ω to 511 kΩ	E24; E192
		± 0.25 %		
		± 0.1 %		
	Jumper; $I_{max.} = 5 A$	≤ 10 mΩ	0 Ω	-

PACKAGING						
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS
SMM0207 OMM0207	BP	1500	Antistatic blister tape acc. IEC 60286-3, Type 2a	12 mm	4 mm	Ø 180 mm/7"
	BS	7500				Ø 330 mm/13"

PART NUMBER AND PRODUCT DESCRIPTION

Part Number: SMM02070C5620FBS00
Part Number: OMM020700000000BS00

S	M	M	0	2	0	7	0	C	5	6	2	0	F	B	S	0	0
O	M	M	0	2	0	7	0	0	0	0	0	0	0	B	S	0	0

TYPE / SIZE	VERSION	TCR	RESISTANCE	TOLERANCE	PACKAGING
SMM0207 OMM0207	0 = neutral	E = ± 15 ppm/K D = ± 25 ppm/K C = ± 50 ppm/K B = ± 100 ppm/K 0 = jumper	3 digit value 1 digit multiplier 0000 = jumper MULTIPLIER 7 = $\times 10^{-3}$ 8 = $\times 10^{-2}$ 9 = $\times 10^{-1}$ 0 = $\times 10^0$ 1 = $\times 10^1$ 2 = $\times 10^2$ 3 = $\times 10^3$ 4 = $\times 10^4$ 5 = $\times 10^5$	B = $\pm 0.1\%$ C = $\pm 0.25\%$ D = $\pm 0.5\%$ F = $\pm 1\%$ J = $\pm 5\%$ 0 = jumper	BP BS

Product Description: SMM0207 50 562R 1 % BS

Product Description: OMM0207 0R0 BS

SMM0207	50	562R	1 %	BS
OMM0207	-	0R0	-	BS
TYPE / SIZE	TCR	RESISTANCE	TOLERANCE	PACKAGING
SMM0207 OMM0207	± 15 ppm/K ± 25 ppm/K ± 50 ppm/K ± 100 ppm/K	100R = 100 Ω 2M21 = 2.21 M Ω 0R0 = jumper	$\pm 0.1\%$ $\pm 0.25\%$ $\pm 0.5\%$ $\pm 1\%$ $\pm 5\%$	BP BS

Note

- Products can be ordered using either the PART NUMBER or the PRODUCT DESCRIPTION

DESCRIPTION

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A homogeneous film of metal alloy is deposited on a high grade ceramic body (Al_2O_3) and conditioned to achieve the desired temperature coefficient. Nickel plated steel termination caps are firmly pressed on the metallized rods. A special laser is used to achieve the target value by smoothly cutting a helical groove in the resistive layer without damaging the ceramics. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating. Four or six color code bands designate the resistance value and tolerance in accordance with **IEC 60062** ⁽¹⁾.

The result of the determined production is verified by an extensive testing procedure performed on 100 % of the individual resistors. This includes full screening for the elimination of products with a potential risk of early field failures (feasible for $R \geq 10 \Omega$) according to EN 140401-803, 2.1.2.2. Only accepted products are laid directly into the blister tape in accordance with **IEC 60286-3, Type 2a** ⁽¹⁾.

ASSEMBLY

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** ⁽¹⁾. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are completely lead (Pb)-free, the pure tin plating provides compatibility with lead (Pb)-free and lead containing soldering processes. Solderability is specified for 2 years after production or requalification, however, excellent solderability is proven after extended storage in excess of 10 years. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

MATERIALS

Vishay acknowledges the following systems for the regulation of hazardous substances:

- **IEC 62474**, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein ⁽²⁾
- The Global Automotive Declarable Substance List (**GADSL**) ⁽³⁾
- The **REACH** regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) ⁽⁴⁾ for its supply chain

The products do not contain any of the banned substances as per **IEC 62474**, GADSL, or the SVHC list, see www.vishay.com/how/leadfree.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at www.vishay.com/doc?49037.

APPROVALS

The resistors are qualified according to **AEC-Q200**.

RELATED PRODUCTS

MELF resistors of other sizes are available:

- Thin Film Micro-MELF Resistors SMM0102 (www.vishay.com/doc?20003)
- Thin Film MELF Resistors SMM0204 (www.vishay.com/doc?20004)

Resistors are available with established reliability in accordance with **EN 140401-803 Version E**. Please refer to datasheet "MELF Resistors with Established Reliability" (www.vishay.com/doc?28707).

MS1 ESCC high-reliability thin film MINI-MELF resistors are the premium choice for design and manufacture of equipment, where matured technology and proven reliability are of utmost importance. They are regularly used in communication and research satellites and fit equally well into aircraft and military electronic systems.

Approval of the MS1 ESCC products is granted by the European Space Components Coordination and registered in the ESCC Qualified Parts List, REP005. (www.vishay.com/doc?28790).



Notes

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents


⁽²⁾ The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at <http://std.iec.ch/iec62474>.

⁽³⁾ The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org

⁽⁴⁾ The SVHC list is maintained by the European Chemical Agency (ECHA) and available at <http://echa.europa.eu/candidate-list-table>




FUNCTIONAL PERFORMANCE

Derating


In accordance with IEC 60440

Non-Linearity




In accordance with IEC 60195

Current Noise

FUNCTIONAL PERFORMANCE

Single Pulse

Continuous Pulse


Maximum pulse voltage, single and continuous pulses; applicable if $\hat{P} \leq \hat{P}_{\max}$;
for permissible resistance change $\pm (0.5 \% R + 0.01 \Omega)$

Pulse Voltage

FUNCTIONAL PERFORMANCE

1.2/50 Pulse

10/700 Pulse

TESTS AND REQUIREMENTS

All tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8

EN 140401-803, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-803. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/ECA-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C

Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days).

The components are mounted for testing on printed circuit boards in accordance with EN 60115-8, 2.4.2, unless otherwise specified.


TEST PROCEDURES AND REQUIREMENTS							
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)			
			SMM0207	< 1 Ω	1 Ω to < 10 Ω	10 Ω to $\leq 1 \text{ M}\Omega$	> 1 MΩ
6.1	-	Resistance	-	$\pm 5\% ; \pm 1\% ; \pm 0.5\% ; \pm 0.25\% ; \pm 0.1\%$			
6.2	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 125 / 20) °C	$\pm 100 \text{ ppm/K}, \pm 50 \text{ ppm/K}, \pm 25 \text{ ppm/K}; \pm 15 \text{ ppm/K}$			
7.1	-	Endurance at 70 °C: precision operation mode	$U = \sqrt{P_{70} \times R} \leq U_{\max};$ 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.05\% R + 0.005 \Omega)$ $\pm (0.1\% R + 0.005 \Omega)$		-	
		Endurance at 70 °C: standard operation mode	$U = \sqrt{P_{70} \times R} \leq U_{\max};$ 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.15\% R + 0.01 \Omega)$ $\pm (0.3\% R + 0.01 \Omega)$		$\pm (0.5\% R)$ $\pm (1\% R)$	
		Endurance at 70 °C: power operation mode	$U = \sqrt{P_{70} \times R} \leq U_{\max};$ 1.5 h on; 0.5 h off; 70 °C; 1000 h 70 °C; 8000 h	$\pm (0.25\% R + 0.01 \Omega)$ $\pm (0.5\% R + 0.01 \Omega)$		$\pm (0.5\% R)$ $\pm (1\% R)$	
7.3	-	Endurance at upper category temperature	125 °C; 1000 h	$\pm (0.15\% R + 0.01 \Omega)$		$\pm (0.5\% R)$	
			155 °C; 1000 h	$\pm (0.3\% R + 0.01 \Omega)$		$\pm (1\% R)$	
10.4	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; 56 days; (93 ± 3) % RH	$\pm (0.25\% R + 0.01 \Omega)$		$\pm (1\% R)$	

TEST PROCEDURES AND REQUIREMENTS				
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)
			SMM0207	< 1 Ω 1 Ω to < 10 Ω 10 Ω to ≤ 1 M Ω > 1 M Ω
10.5	67 (Cy)	Damp heat, steady state, accelerated	$(85 \pm 2)^\circ\text{C}$ $(85 \pm 5)\%$ RH $U = 0.3 \times \sqrt{P_{70} \times R}$ $\leq 100\text{ V}$ and $U = 0.3 \times U_{\max.}$; (the smaller value is valid) 1000 h	$\pm (0.5\% R + 0.01 \Omega)$ $\pm (2\% R)$
-	1 (Ab)	Cold	-55 $^\circ\text{C}$; 2000 h	$\pm (0.1\% R + 0.01 \Omega)$
10.1	14 (Na)	Rapid change of temperature	30 min at LCT and 30 min at UCT; LCT = -55 $^\circ\text{C}$; UCT = 125 $^\circ\text{C}$; 1000 cycles	$\pm (0.25\% R + 0.01 \Omega)$
			LCT = -55 $^\circ\text{C}$; UCT = 155 $^\circ\text{C}$; 1000 cycles	$\pm (0.5\% R + 0.01 \Omega)$
8.1	-	Short time overload: standard operation mode	$U = 2.5 \times \sqrt{P_{70} \times R}$ $\leq 2 \times U_{\max.}; 5\text{ s}$	$\pm (0.03\% R + 0.01 \Omega)$
		Short time overload: power operation mode		$\pm (0.05\% R + 0.01 \Omega)$
8.2	-	Single pulse high voltage overload: standard operation mode	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ $\leq 2 \times U_{\max.};$ 10 pulses 10 $\mu\text{s}/700 \mu\text{s}$	$\pm (0.25\% R + 0.01 \Omega)$
		Single pulse high voltage overload: power operation mode		$\pm (0.5\% R + 0.01 \Omega)$
8.4	-	Periodic electric overload: standard operation mode	$U = \sqrt{15 \times P_{70} \times R}$ $\leq 2 \times U_{\max.};$ 0.1 s on; 2.5 s off; 1000 cycles	$\pm (0.15\% R + 0.01 \Omega)$
		Periodic electric overload: power operation mode		$\pm (0.3\% R + 0.01 \Omega)$
9.11	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude $\leq 1.5\text{ mm}$ or $\leq 200\text{ m/s}^2$; 7.5 h	$\pm (0.05\% R + 0.01 \Omega)$
8.5	-	Electro static discharge (human body model)	IEC 61340-3-1 (1); 3 pos. + 3 neg. discharges; 4 kV	$\pm (0.5\% R + 0.05 \Omega)$
11.1	58 (Td)	Solderability	Solder bath method; SnPb40; non-activated flux (215 ± 3) $^\circ\text{C}$; (3 ± 0.3) s	Good tinning ($\geq 95\%$ covered); no visible damage
			Solder bath method; SnAg3Cu0.5 or SnAg3.5; non-activated flux; (235 ± 3) $^\circ\text{C}$; (2 ± 0.2) s	Good tinning ($\geq 95\%$ covered); no visible damage

TEST PROCEDURES AND REQUIREMENTS							
EN 60115-1 CLAUSE	IEC 60068-2 (1) TEST METHOD	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (ΔR)			
			SMM0207	< 1 Ω	1 Ω to < 10 Ω	10 Ω to $\leq 1 \text{ M}\Omega$	> 1 $\text{M}\Omega$
11.2	58 (Td2)	Resistance to soldering heat	Reflow (IR/forced gas convection); (260 \pm 5) $^{\circ}\text{C}$; (35 \pm 5) s 3 cycles	$\pm (0.05 \% R + 0.01 \Omega)$			$\pm (0.25 \% R)$
11.3	45 (XA)	Component solvent resistance	Isopropyl alcohol; 50 $^{\circ}\text{C}$; method 2	No visible damage			
	45 (XA)	Solvent resistance of marking	Isopropyl alcohol; 50 $^{\circ}\text{C}$; method 1, toothbrush	Marking visible, no visible damage			
9.7	21 (Ue ₃)	Shear (adhesion)	45 N	No visible damage			
9.8	21 (Ue ₁)	Substrate bending	Depth 2 mm, 3 times	No visible damage, no open circuit in bent position $\pm (0.05 \% R + 0.01 \Omega)$			
12.2	-	Voltage proof	$U_{\text{RMS}} = U_{\text{ins}}$; 60 s	No flashover or breakdown			
12.4	-	Flammability	IEC 60695-11-5 (1); needle flame test; 10 s	No burning after 30 s			

Note

⁽¹⁾ The quoted IEC standards are also released as EN standards with the same number and identical contents

DIMENSIONS


DIMENSIONS AND MASS						
TYPE / SIZE	L (mm)	D (mm)	L₁ min. (mm)	D₁ (mm)	K (mm)	MASS (mg)
SMM0207 OMM0207	5.8 + 0 / - 0.3	2.2 ± 0.2	2.6	D + 0 / - 0.2	1.25 ± 0.2	77

Notes

- Color code marking is applied according to IEC 60062 ⁽¹⁾ in four, five, or six bands. Each color band appears as a single solid line, voids are permissible if at least 2/3 of the band is visible from each radial angle of view. The last color band represents the TCR for resistors with TCR ≤ 50 ppm/K and nominal tolerance ≤ 1 %. In case of transparent body coating lacquer, an interrupted band between the 4th and 5th full band indicates the TCR: in yellow color for ± 25 ppm/K and in orange color for ± 15 ppm/K
- Zero ohm jumper are marked with one centered black band

SOLDERING RECOMMENDATIONS

For recommended solder pad dimensions please refer to www.vishay.com/doc?28950.

For recommended soldering profiles please refer to www.vishay.com/doc?31090.

REVISION HISTORY	
REVISION DATE	DESCRIPTION
04-Dec-2025	Editorial changes Page 1: - added link to 3D file - added thermal resistance information - updated FIT _{observed} rate Page 11: - introduction of alternative option for TCR marking - introduction of revision history

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.