




LOC	DIST	REVISIONS						
		P	LTR	DESCRIPTION	DATE	DWN	APVD	
		B		REV PER ECO 12-010940	2-29-12	CT	DH	
		C		ECO-13-004755	26MAR2013	KG	DH	
		D		ECO-14-017030	25NOV2014	MGM	CT	



○ = SIGNAL
⊗ = GROUND
RECOMMENDED PC BOARD LAYOUT
COMPONENT SIDE SHOWN
SCALE 8:1

- △ MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- △ FINISH:
CONTACT: MATING AREA: 1.27μm MIN GOLD OVER
1.27μm MIN NICKEL
SHIELD: 1.27μm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38μm MIN BRIGHT TIN LEAD OVER
1.27μm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38μm MIN MATTE TIN OVER
1.27μm MIN NICKEL
- △ ---
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.
- △ ALL GROUNDS IN ODD NUMBERED COLUMNS ARE COMMONED.
ALL GROUNDS IN EVEN NUMBERED COLUMNS, EXCEPT FOR ROW A ARE COMMONED.



THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONING AND TOLERANCING PER QPS (130 STANDARDS)		DWN D. BELACK CHK A. TSANG APVD W. McALONIS	24JUN2009 6-24-2009 6-24-2009	NAME Fortis Zd, 3-PAIR, 10-COLUMN, RIGHT ANGLE LEFT MODULE ASSEMBLY, DIFFERENTIAL PAIR	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC 108-2409	APPLICATION SPEC 114-13267	SIZE ~13.48g	RESTRICTED TO
MATERIAL △	FINISH -	WEIGHT ~13.48g	Customer Drawing	SCALE 5:1	SHEET 1 OF 1
Customer Drawing				REV D	

2 4	2000890-2
2 3	2000890-1
FINISH	PART NUMBER