



10		9		8		7		6		5		4		3		2		19270	
BLACK		RED		MIN		MAX		RECOVERED		LENGTH FEET/METERS		4.0/1.2							
MATERIAL NUMBER	ENGINEERING NUMBER	MATERIAL NUMBER	ENGINEERING NUMBER	EXPANDED ID "D"		RECOVERED ID		WALL THK REF											
192700008	PFB-04-1BK	192700013	PFB-04-1RD	.400/10.16		.150/3.81		.060/1.53											
192700018	PFB-07-1BK	192700023	PFB-07-1RD	.750/19.05		.220/5.59		.095/2.41											
192700028	PFB-11-1BK	192700033	PFB-11-1RD	1.100/27.94		.375/9.53		.120/3.05											
192700038	PFB-15-1BK	192700043	PFB-15-1RD	1.500/38.10		.500/19.05		.140/3.56											
192700048	PFB-20-1BK	192700053	PFB-20-1RD	2.000/50.380		.750/19.05		.155/3.98											
192700058	PFB-30-1BK	192700063	PFB-30-1RD	3.540/89.92		1.18/29.97		.155/3.98											
192700068	PFB-40-1BK	192700073	PFB-40-1RD	4.72/119.89		1.57/39.88		.170/4.37											



SALES DRAWING

NOTES:

- 1. MATERIAL: POLYOLEFIN
- 2. OTHER CUT LENGTHS ARE AVAILABLE.
- 3. PARTS ARE RoHS COMPLIANT.

(A1)

CHANGED TITLE EC NO: IPG2013-0982 DRAWN: GJOJAS01 2013/01/10 CHKD: JMACNEIL 2013/01/10 APPR: JMACNEIL 2013/01/31 A1	DESCRIPTION ▽=0 ▽=0	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	 THIRD ANGLE PROJECTION	
			mm	INCH	DRAWN BY	DATE	TITLE POLYOLEFIN HEAT SHRINK TUBING 19270 SERIES MOLEX INCORPORATED			
		4 PLACES ± --- ± ---	3 PLACES ± --- ± .010	BENDERLE	2004/09/23	APPROVED BY		DATE		
		2 PLACES ± 0.25 ± .02	1 PLACE ± 0.51 ± ---	R DEROSS	2004/09/23					
		ANGULAR ± ---°		R DEROSS	2004/09/23	DOCUMENT NO.		SHEET NO.		
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-19270-001		1 OF 1		
				SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				