

## Polyester Modular Enclosures - NEMA 4X

### PJ Accessories

#### PJ Series Inner Panel

- 14 gauge steel panels are finished in white baked powder coating.
- Aluminum panels are 0.080" (2.03 mm) type 5052 H-32 aluminum, unpainted. A2420 and larger panels are 0.125".
- Fiberglass inner panels are Finished in white
- Hardware to mount inner panel is included with PJ Series Enclosures.

| Steel Part No. | Aluminum Part No. | Fiberglass Part No. | Fiberglass Thickness | Panel  |       | For Use With PJ Series |       |
|----------------|-------------------|---------------------|----------------------|--------|-------|------------------------|-------|
|                |                   |                     |                      | Length | Width | A                      | B     |
| 14R0505        | 14A0505           | 14F0505             | 0.125                | 4.88   | 4.88  | 6.10                   | 6.10  |
| 14R0705        | 14A0705           | 14F0705             | 0.125                | 6.75   | 4.88  | 8.00                   | 6.13  |
| 14R0907        | 14A0907           | 14F0907             | 0.125                | 8.75   | 6.88  | 10.14                  | 8.26  |
| 14R1109        | 14A1109           | 14F1109             | 0.125                | 10.75  | 8.88  | 12.14                  | 10.26 |
| 14R1311        | 14A1311           | 14F1311             | 0.187                | 12.75  | 10.88 | 14.13                  | 12.25 |
| 14R1513        | 14A1513           | 14F1513             | 0.187                | 14.75  | 12.88 | 16.28                  | 14.40 |
| P1868          | A1868             | F1868               | 0.187                | 16.88  | 14.88 | 18.40                  | 16.40 |
| P2068          | A2068             | F2068               | 0.250                | 18.44  | 14.44 | 20.00                  | 16.00 |
| 18P2117        | A2420             | F2420               | 0.250                | 21.00  | 17.00 | 24.00                  | 20.00 |
| 18P2121        | A2424             | F2424               | 0.250                | 21.00  | 21.00 | 24.00                  | 24.00 |
| 18P2721        | A3024             | F3024               | 0.250                | 27.00  | 21.00 | 30.00                  | 24.00 |

#### Moulded Polycarbonate Flange For PJU Series (sold in Pairs)



| Part No.    | PJU Flange Fits |
|-------------|-----------------|
| PJFPUWM6    | 6x6, 8x6        |
| PJFPUWM108  | 10x8            |
| PJFPUWM1210 | 12x10           |
| PJFPUWM1412 | 14x12           |
| PJFPUWM1614 | 16x14           |
| PJFPUWM1816 | 18x16           |
| PJFPUWM2016 | 20x16           |

#### Moulded Polycarbonate Feet For PJU Series (sold in sets of 4)



| Part No.  | PJU Feet Fits       |
|-----------|---------------------|
| PJW4NUFS  | 6x6 through 14x12   |
| PJW4NULFS | 16x14 through 20x16 |

#### Stainless Mounting Feet For PJ Series (sold in sets of 4)



| Part No. | 304 SS PJ Feet Fits |
|----------|---------------------|
| PJW4NFS  | 6x6 through 20x16   |
| PJW4NLS  | 24x20 through 30x24 |

#### PJ/PJU Series Swing Panel



#### Use with PJ Series Raised Lid Enclosures

| Part No. | Panel Dimensions |       |
|----------|------------------|-------|
|          | Height           | Width |
| PJSP108  | 9.50             | 7.50  |
| PJSP1210 | 11.50            | 9.50  |
| PJSP1412 | 13.50            | 11.50 |
| PJSP1614 | 15.13            | 13.00 |
| PJSP1816 | 17.25            | 15.38 |
| PJSP2016 | 18.88            | 14.94 |
| PJSP2420 | 23.25            | 19.38 |
| PJSP2424 | 23.38            | 23.25 |
| PJSP3024 | 29.25            | 23.38 |

#### Use with PJU Series Enclosures

| Part No.  | Panel Dimensions |       |
|-----------|------------------|-------|
|           | Height           | Width |
| PJSPU108  | 9.64             | 7.87  |
| PJSPU1210 | 11.64            | 9.86  |
| PJSPU1412 | 13.64            | 11.86 |
| PJSPU1614 | 15.64            | 13.86 |
| PJSPU1816 | 17.90            | 15.99 |
| PJSPU2016 | 19.65            | 15.55 |

- Hinged aluminum panel.
- Mounts at front of enclosure body.
- Field installed with no drilling required.