

## GPS RADIONOVA<sup>®</sup> M10372 RF Antenna Module

Antenova's GPS RADIONOVA<sup>®</sup> M10372 RF Antenna Module is a single package solution to combine RF and antenna on the same module. The M10372 is a highly integrated GPS RF Antenna Module suitable for L1-band GPS and A-GPS systems. The device is based on the high performance CSR SiRFstarIV<sup>™</sup> GPS architecture combined with Antenova's high efficiency antenna technology, and is designed to provide an optimal radiation pattern for GPS reception.

All front-end and receiver components are contained in a single package laminate base module, providing a complete GPS receiver for optimum performance. The M10372 operates on a single 1.8V positive bias supply with low power consumption and available low power modes for further power savings. The M10372 is supported by SiRF stand alone software and is compatible with UART, SPI and I<sup>2</sup>C host processor interfaces. Custom versions of M10372 can also incorporate an antenna switch for optional external active antenna connection.




Providing a true drop in solution with the antenna and RF in a single package, GPS RADIONOVA<sup>®</sup> M10372 offers ease of integration and shorter design cycles for faster time to market.

### Applications:

- Personal Navigation Devices (PNDs)
- Portable Media Players (PMPs)
- Asset Tracking / Personal Safety
- Ultra Mobile Devices (UMDs)

### Features:

- Low cost single package RF Antenna Module
- CSR SiRFstarIV<sup>™</sup> GPS Chipset Architecture
- Low 5mm height for thin devices
- Low current consumption
- Optional external antenna support
- Resistant to de-tuning




## electrical

|                        |                               |
|------------------------|-------------------------------|
| Frequency:             | 1575 MHz                      |
| Supply Voltage         | 1.8V                          |
| Supply Current:        | 30mA                          |
| Hibernate Current:     | 30 µA                         |
| COM Interface:         | UART / SPI / I <sup>2</sup> C |
| Output Protocol:       | SiRF Binary / NMEA 0183       |
| Operating Temperature: | -30°C to +85°C                |


## mechanical

|              |                            |
|--------------|----------------------------|
| Dimensions : | 28 x 13 x 5mm              |
| Mounting:    | Planar mount / low profile |
| Connector:   | 30pin board-to-board       |
| Groundplane: | 40 x 30mm min              |


Typical RF Antenna Module Placement




Front View





Back View



Side View



Typical Sensitivity Pattern



Note: Radiation pattern measured on Antenova M2M's standard test board. Tuning may be needed in product integration to adjust radiation pattern.



Certificate No: 4598

antenova  
m2m

Antenova Limited • Far Field House • Albert Road • Stow-cum-Quy • Cambridge • CB25 9AR • UK  
t: +44 (0)1223 810600 f: +44 (0)1223 810650  
sales@antenova-m2m.com • www.antenova-m2m.com

Patent Pending. Covered by US. Patent Publication No. US 2011/0037661 A1. UK Patent Applied for No. 0806335.6.  
Version 5, released 28 January 2013  
The information provided in this document was correct at the time of going to print