

C1005X7R1C473K050BC

Applications



Commercial Grade



Please refer to Part No. CGA2B2X7R1C473K050BA for automotive use.


Feature

General

General (Up to 50V)

Series

C1005 [EIA CC0402]




Size	
Length(L)	1.00mm +/-0.05mm
Width(W)	0.50mm +/-0.05mm
Thickness(T)	0.50mm +/-0.05mm
Terminal Width(B)	0.10mm Min.
Terminal Spacing(G)	0.30mm Min.

Electrical Characteristics	
Capacitance	47nF +/-10%
Rated Voltage	16Vdc
Temperature Characteristic	X7R(+/-15%)
Dissipation Factor	5% Max.
Insulation Resistance	2127MΩ Min.


Other	
Soldering Method	Reflow
AEC Q200	No
Packing	Punched (Paper)Taping [180mm Reel]
Package Quantity	10000 Pcs Min.

C1005X7R1C473K050BC


Characteristic Graphs




C1005X7R1C473K050BC




C1005X7R1C473K050BC



C1005X7R1C473K050BC




C1005X7R1C473K050BC



C1005X7R1C473K050BC(DC Bias = 0V)

C1005X7R1C473K050BC(DC Bias = 8V)



C1005X7R1C473K050BC(100kHz)

C1005X7R1C473K050BC(500kHz)

C1005X7R1C473K050BC(1MHz)