


			DESIGNED FOR USE WITH RD-316/U (DOUBLE BRAID)		REVISIONS																																																																		
			CABLE ENTRY DIAMETER MINIMUM		REV	DESCRIPTION	DATE	APPROVED																																																															
			FERRULE		.137	02_0	REVISED	3/1/96	3/4/96																																																														
			HOUSING		.066																																																																		
CONTACT		.023																																																																					
<table><tr><td>ELECTRICAL</td><td>MECHANICAL</td><td>ENVIRONMENTAL</td></tr><tr><td>Nominal Impedance (Ohms) 50</td><td>Interface Dimensions MIL-STD-348A, Fig. 310.1</td><td>Temperature Rating -65°C to + 165°C</td></tr><tr><td>Frequency Range (GHz) DC to 12.4</td><td>Recommended Mating</td><td>Vibration MIL-STD-202, Method 204, Condition D.</td></tr><tr><td>Volt Rating (VRMS MAX) @ Sea Level 250</td><td>Torque 7 to 10 in-lbs</td><td>Shock MIL-STD-202, Method 213, Condition I.</td></tr><tr><td>VSWR 1.30 : 1</td><td>Mating Characteristics:</td><td>Thermal Shock MIL-STD-202, Method 107, Condition B,</td></tr><tr><td>Insertion Loss (dB MAX) .06 √f(GHz)</td><td>Insertion (MAX lbs) N/A</td><td>Except High Temp shall be +85°C</td></tr><tr><td>RF Leakage (dB MIN) -[60-f(GHz)]</td><td>Withdrawal (MIN oz) N/A</td><td>Moisture Resistance MIL-STD-202, Method 106</td></tr><tr><td>Corona, 70,000 Ft (VRMS MIN) 190</td><td>Force to Engage and Disengage (in-lbs MAX) 2.0</td><td>Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray</td></tr><tr><td>Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750</td><td>Center Contact Captivation</td><td></td></tr><tr><td>Contact Resistance (Milliohms MAX)</td><td>Axial (lbs) 6.0</td><td></td></tr><tr><td>Center Contact 2.0</td><td>Radial (in-oz) N/A</td><td></td></tr><tr><td>Outer Contact 2.0</td><td>Cable Retention</td><td></td></tr><tr><td>Cable to Housing 0.5</td><td>Axial Force (lbs MIN) 25.0</td><td></td></tr><tr><td>RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500</td><td>Torque (in-oz MIN) N/A</td><td></td></tr><tr><td>IR.(Megohms MIN) 10,000</td><td>Weight (Grams) TBD</td><td></td></tr></table>			ELECTRICAL	MECHANICAL	ENVIRONMENTAL	Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.1	Temperature Rating -65°C to + 165°C	Frequency Range (GHz) DC to 12.4	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition D.	Volt Rating (VRMS MAX) @ Sea Level 250	Torque 7 to 10 in-lbs	Shock MIL-STD-202, Method 213, Condition I.	VSWR 1.30 : 1	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B,	Insertion Loss (dB MAX) .06 √f(GHz)	Insertion (MAX lbs) N/A	Except High Temp shall be +85°C	RF Leakage (dB MIN) -[60-f(GHz)]	Withdrawal (MIN oz) N/A	Moisture Resistance MIL-STD-202, Method 106	Corona, 70,000 Ft (VRMS MIN) 190	Force to Engage and Disengage (in-lbs MAX) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray	Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Center Contact Captivation		Contact Resistance (Milliohms MAX)	Axial (lbs) 6.0		Center Contact 2.0	Radial (in-oz) N/A		Outer Contact 2.0	Cable Retention		Cable to Housing 0.5	Axial Force (lbs MIN) 25.0		RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500	Torque (in-oz MIN) N/A		IR.(Megohms MIN) 10,000	Weight (Grams) TBD		<table><tr><td>HOUSING COUPLING NUT</td><td>STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303</td><td>PASSIVATE PER QQ-P-35</td></tr><tr><td>DIELECTRIC</td><td>TFE FLUOROCARBON PER ASTM-D-1457</td><td>N/A</td></tr><tr><td>CENTER CONTACT</td><td>BRASS PER ASTM-B-16 HALF HARD</td><td>GOLD PLATE PER MIL-G-45204</td></tr><tr><td>RETAINING RING</td><td>BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H</td><td>N/A</td></tr><tr><td>GASKET</td><td>SILICONE RUBBER PER ZZ-R-765</td><td>N/A</td></tr><tr><td>FERRULE</td><td>COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM</td><td>NICKEL PLATER PER QQ-N-290</td></tr><tr><td>COMPONENT</td><td>MATERIAL</td><td>FINISH</td></tr></table>			HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35	DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A	CENTER CONTACT	BRASS PER ASTM-B-16 HALF HARD	GOLD PLATE PER MIL-G-45204	RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A	GASKET	SILICONE RUBBER PER ZZ-R-765	N/A	FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	NICKEL PLATER PER QQ-N-290	COMPONENT	MATERIAL	FINISH
ELECTRICAL	MECHANICAL	ENVIRONMENTAL																																																																					
Nominal Impedance (Ohms) 50	Interface Dimensions MIL-STD-348A, Fig. 310.1	Temperature Rating -65°C to + 165°C																																																																					
Frequency Range (GHz) DC to 12.4	Recommended Mating	Vibration MIL-STD-202, Method 204, Condition D.																																																																					
Volt Rating (VRMS MAX) @ Sea Level 250	Torque 7 to 10 in-lbs	Shock MIL-STD-202, Method 213, Condition I.																																																																					
VSWR 1.30 : 1	Mating Characteristics:	Thermal Shock MIL-STD-202, Method 107, Condition B,																																																																					
Insertion Loss (dB MAX) .06 √f(GHz)	Insertion (MAX lbs) N/A	Except High Temp shall be +85°C																																																																					
RF Leakage (dB MIN) -[60-f(GHz)]	Withdrawal (MIN oz) N/A	Moisture Resistance MIL-STD-202, Method 106																																																																					
Corona, 70,000 Ft (VRMS MIN) 190	Force to Engage and Disengage (in-lbs MAX) 2.0	Corrosion - MIL-STD-202, Method 101, Condition B, 5% salt spray																																																																					
Dielectric Withstanding Voltage (VRMS MIN) @ Sea Level 750	Center Contact Captivation																																																																						
Contact Resistance (Milliohms MAX)	Axial (lbs) 6.0																																																																						
Center Contact 2.0	Radial (in-oz) N/A																																																																						
Outer Contact 2.0	Cable Retention																																																																						
Cable to Housing 0.5	Axial Force (lbs MIN) 25.0																																																																						
RF High Potential @ Sea Level (VRMS MIN @ 5 MHz) 500	Torque (in-oz MIN) N/A																																																																						
IR.(Megohms MIN) 10,000	Weight (Grams) TBD																																																																						
HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER QQ-P-35																																																																					
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A																																																																					
CENTER CONTACT	BRASS PER ASTM-B-16 HALF HARD	GOLD PLATE PER MIL-G-45204																																																																					
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A																																																																					
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A																																																																					
FERRULE	COPPER OR BRASS ALLOY ROCKWELL F65 MAXIMUM	NICKEL PLATER PER QQ-N-290																																																																					
COMPONENT	MATERIAL	FINISH																																																																					
<table><tr><td>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON</td><td>DRAWN BY <i>ADavis</i> DATE 11/17/92</td><td rowspan="2">AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599</td></tr><tr><td>FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°</td><td>CHECKED BY APPD BY <i>ICornell</i> 12/15/92</td></tr><tr><td rowspan="3">These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.</td><td>USE ASS'Y PROCEDURE</td><td rowspan="3">TITLE OSM LOW COST STRAIGHT CABLE PLUG CRIMP ATTACHMENT</td></tr><tr><td>408-04661 NO. AP. (28-001)</td><td>SIZE B CODE IDENT NO. 26805</td></tr><tr><td>SCALE 4 : 1</td><td>2831-7316-02</td></tr></table>			UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY <i>ADavis</i> DATE 11/17/92	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599	FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	CHECKED BY APPD BY <i>ICornell</i> 12/15/92	These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSM LOW COST STRAIGHT CABLE PLUG CRIMP ATTACHMENT	408-04661 NO. AP. (28-001)	SIZE B CODE IDENT NO. 26805	SCALE 4 : 1	2831-7316-02	REV 02_0																																																								
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON	DRAWN BY <i>ADavis</i> DATE 11/17/92	AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599																																																																					
FRAC. DEC. ANGLES ± 1/64 ±.005 ± 1°	CHECKED BY APPD BY <i>ICornell</i> 12/15/92																																																																						
These drawings and specifications are the property of M/A-COM Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.	USE ASS'Y PROCEDURE	TITLE OSM LOW COST STRAIGHT CABLE PLUG CRIMP ATTACHMENT																																																																					
	408-04661 NO. AP. (28-001)		SIZE B CODE IDENT NO. 26805																																																																				
	SCALE 4 : 1		2831-7316-02																																																																				
SHEET 1 OF 1																																																																							